



PIN RECEPTACLES
 for .015" - .020" diameter pins (#11 contact)
 and .015" - .022" diameter pins (#21 contact)
 (see specific contact range on page 217)



0548	8975	3016	9548
0548-0-15-XX-21-XX-10-0 Solder mount in .036 min. mounting hole	8975-0-15-XX-21-XX-10-0 Solder mount in .036 min. mounting hole	3016-0-15-XX-21-XX-10-0 Solder mount in .036 min. mounting hole	9548-0-15-XX-21-XX-10-0 Solder mount in .036 min. mounting hole

8637	1407	0553/8553
8637-0-15-XX-21-XX-10-0 Solder mount in .037 min. mounting hole	1407-0-15-XX-11-XX-10-0 Solder mount in .040 min. mounting hole	X553-X-15-XX-X1-XX-10-0 Hex press-fit in .041 plated thru hole

Basic Part Number	Length L	Depth N
0553-1	.140	.124
0553-2	.170	.154
0553-3	.282	.266
8553-0	.245	.229

0566	0442	0554
0566-X-15-XX-21-XX-10-0 Solder mount in .039 min. mounting hole	0442-0-15-XX-11-XX-10-0 Solder mount in .040 min. mounting hole	0554-0-15-XX-21-XX-10-0 Solder mount in .040 min. mounting hole

Basic Part Number	Length L
0566-1	.083
0566-2	.138

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES TOLERANCES ON:
 LENGTHS: ±.005
 DIAMETERS: ±.002
 ANGLES: ± 2°

ORDER CODE: XXXX - X - 15 - XX - XX - XX - 10 - 0

BASIC PART # →

SPECIFY SHELL FINISH:

- 01 200µ" TIN/LEAD OVER NICKEL
- ◇ 80 200µ" TIN OVER NICKEL (RoHS)
- ◇ 15 10µ" GOLD OVER NICKEL (RoHS)

SPECIFY CONTACT FINISH:

- 02 100µ" TIN/LEAD OVER NICKEL
- ◇ 84 100µ" TIN OVER NICKEL (RoHS)
- ◇ 27 30µ" GOLD OVER NICKEL (RoHS)

SELECT CONTACT
 #11 or #21 CONTACT (DATA ON PAGE 217)