

Automation Technology > Power supplies > Power supply SITOP > Expansion modules > Redundancy module

6EP1964-2BA00 SITOP PSE202U 10A

Technical / CAx data

Technical Data CAx data




SITOP PSE202U 10A REDUNDANCY MODULE INPUT/OUTPUT: 24 V DC FIT FOR DECOUPLING OF 2 SITOP POWER SUPPLY MODULES WITH 5 A MAX. OUTPUT CURRENT EACH

Technical specifications

Product	SITOP PSE202U
Input	
Input	DC voltage
Supply voltage / at DC	24...24 V
Input voltage / at DC	19...29 V
Output	
Output	Controlled, isolated DC voltage
Rated voltage V_{out} DC	24 V
Output voltage	V_{in} - approx. 0.5 V
Product feature / output voltage adjustable	No
Status display	Green LED for "both Input voltages > switching threshold"; red LED: for "at least one input voltage < switching threshold"
Rated current value I_{out} rated	10 A
Current range	10 A
<ul style="list-style-type: none"> Note 	max. aggregate current 10 A
Efficiency	
Closed-loop control	
Protection and monitoring	
Safety	
Potential separation	yes, SELV acc. to EN 60950-1 (relay contact)
Protection class	Class III

CE mark	Yes
UL/CSA approval	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259
CB approval	No
Verification of suitability / C-Tick	No
Marine approval	-
Degree of protection (EN 60529)	IP20
EMC	
Emitted interference	EN 55022 Class B
Noise immunity	EN 61000-6-2
Operating data	
Ambient temperature / in operation	-20...+70 °C
• Note	with natural convection
Ambient temperature / on transport	-40...+85 °C
Ambient temperature / in storage	-40...+85 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation
Mechanics	
Connection technology	screw-type terminals
Connections / Supply input	Input, output and ground: removable screw terminal, each 1 x 0.5 ... 2.5 mm ² single-core/finely stranded
Connections / Auxiliary	Relay contact: 1 screw terminal each for 0.5 ... 2.5 mm ² single-core/finely stranded
Width / of the housing	30 mm
Height / of the housing	80 mm
Depth / of the housing	100 mm
Installation width	30 mm
Mounting height	180 mm
Weight, approx.	0.125 kg
Product feature / of the housing / housing for side-by-side mounting	Yes
Type of mounting / wall mounting	No
Type of fixing / cap rail mounting	Yes
Type of mounting / S7-300 rail mounting	No
Installation	Snaps onto DIN rail EN 60715 35x7.5/15
Electrical accessories	Removable spring-type terminal 6EP1971-5BA00
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)



letzte Änderung:

Jun 1, 2012

© Siemens AG 2012 - Corporate Information - Privacy Policy - Terms of Use