SIEMENS

Product data sheet

3RT2025-1AC20



CONTACTOR, AC-3, 7.5KW/400V, 1NO+1NC, AC 24V 50/60HZ, 3-POLE, SZ S0 SCREW TERMINAL

General technical data:		
product brand name		SIRIUS
Size of the contactor	_	S0
Product extension / auxiliary switch		Yes
Protection class IP / on the front		IP20
Protection against electrical shock		finger-safe
Degree of pollution		3
Installation altitude / at a height over sea level / maximum	m	2,000
Ambient temperature		
during storage	°C	-55 +80
during operating	°C	-25 +60
Shock resistance		
• at rectangular impulse		
• at AC		7,5g / 5 ms, 4,7g / 10 ms
• at sine pulse		
• at AC		11,8g / 5 ms, 7,4g / 10 ms
Impulse voltage resistance / rated value	kV	6
Insulation voltage / rated value	V	690
Mechanical operating cycles as operating time		
• of the contactor / typical		10,000,000

of the contactor with added auxiliary switch block / typical		10,000,000
 of the contactor with added electronics-compatible auxiliary switch block / typical 		5,000,000
Main circuit:		
Number of NC contacts / for main contacts		0
Number of NO contacts / for main contacts	-	3
Operating current	-	
• at AC-1 / at 400 V		
• at 40 °C ambient temperature / rated value	А	40
• at 60 °C ambient temperature / rated value	А	35
• at AC-2 / at 400 V / rated value	А	17
• at AC-3 / at 400 V / rated value	А	17
• at AC-4 / at 400 V / rated value	А	15.5
Operating current	_	
with 1 current path / at DC-1		
• at 24 V / rated value	А	35
• at 110 V / rated value	А	4.5
• with 2 current paths in series / at DC-1		
• at 24 V / rated value	А	35
• at 110 V / rated value	А	35
• with 3 current paths in series / at DC-1		
• at 24 V / rated value	А	35
• at 110 V / rated value	А	35
• with 1 current path / at DC-3 / at DC-5		
• at 24 V / rated value	А	20
• at 110 V / rated value	А	2.5
• with 2 current paths in series / at DC-3 / at DC-5		
• at 24 V / rated value	А	35
• at 110 V / rated value	А	15
• with 3 current paths in series / at DC-3 / at DC-5		
• at 24 V / rated value	А	35
• at 110 V / rated value	А	35
Service power		
• at AC-2 / at 400 V / rated value	kW	7.5
• at AC-3 / at 400 V / rated value	kW	7.5
• at AC-4 / at 400 V / rated value	kW	7.5
Active power loss / per conductor / typical	W	0.9
Off-load operating frequency		
• at AC	1/h	5,000

• at DC	1/h	1,500
Frequency of operation / at AC-1 / according to IEC 60947-6-2	1/h	1,000
Frequency of operation / at AC-2 / according to IEC 60947-6-2	1/h	1,000
Frequency of operation / at AC-3 / according to IEC 60947-6-2	1/h	1,000
Frequency of operation / at AC-4 / according to IEC 60947-6-2	1/h	300
Frequency of operation / at AC-4 / according to IEC 60947-6-2	1/n	300

Control circuit:		
Type of voltage / of the controlled supply voltage		AC
Control supply voltage / 1		
• at 50 Hz / for AC / rated value	V	24
• at 60 Hz / for AC / rated value	V	24
Operating range factor control supply voltage rated value / of the magnet coil		
• at 50 Hz / for AC		0.8 1.1
• at 60 Hz / for AC		0.85 1.1
Apparent pull-in power / of the solenoid / for AC	V·A	68
Apparent holding power / of the solenoid / for AC	V·A	7.9
Inductive power factor		
with the pull-in power of the coil		0.82
with the pull-in power of the coil		0.25
Closing delay		
• at AC	ms	9 38
Opening delay		
• at AC	ms	4 16
Arcing time	ms	10 10

Auxiliary circuit

Contact reliability / of the auxiliary contacts		1 faulty switching per 100 million (17 V, 1 mA)
Number of NC contacts / for auxiliary contacts / instantaneous switching		1
Number of NO contacts / for auxiliary contacts / instantaneous switching		1
Operating current / of the auxiliary contacts	-	
• at AC-12 / maximum	А	10
• at AC-15		
• at 230 V	А	10
• at 400 V	А	3
• at DC-12		
• at 48 V	А	6
• at 60 V	А	6
• at 110 V	А	3

• at 220 V	А	1
• at DC-13		
• at 24 V	А	10
• at 48 V	А	2
• at 60 V	А	2
• at 110 V	А	1
• at 220 V	А	0.3

Short-circuit:		
Design of the fuse link		
• for short-circuit protection of the auxiliary switch / required		fuse gL/gG: 10 A
 for short-circuit protection of the main circuit 		
 with type of assignment 1 / required 		gL/gG LV HRC 3NA, DIAZED 5SB, NEOZED 5SE: 63 A
 at type of coordination 2 / required 		gL/gG LV HRC 3NA, DIAZED 5SB, NEOZED 5SE: 25A
Installation/mounting/dimensions:		
mounting position		+/-180° rotation possible on vertical mounting surface; can be tilted forward and backward by +/- 22.5° on vertical mounting surface
Type of mounting	-	screw and snap-on mounting onto 35 mm standard mounting rail according to DIN EN 50022
Type of fixing/fixation / series installation		Yes
Width	mm	45
Height	mm	85
Depth	mm	97
Distance, to be maintained, to the ranks assembly / sidewards	mm	0
Distance, to be maintained, to earthed part / sidewards	mm	6

Connections:

screw-type terminals
screw-type terminals
2x (1 2.5 mm²), 2x (2.5 10 mm²)
2x (1 2.5 mm²), 2x (2.5 6 mm²), 1x 10 mm²
2x (16 12), 2x (14 8)
2x (0.5 1.5 mm²), 2x (0.75 2.5 mm²)

 with 	conductor	end	processing
	contactor	onia	proceeding

• for AWG conductors / for auxiliary contacts

2x (0.5 ... 1.5 mm²), 2x (0.75 ... 2.5 mm²)

2x (20 ... 16), 2x (18 ... 14)

				ZX (20 10), ZX (10 14)	
Certificates/appro	vals:				
General Product A	pproval			Declaration of C	onformity
	SP CSA	GOST		EG-Konf.	
Test Certificates					
Special Test Certificate	<u>Type Test</u> Certificates/Test <u>Report</u>				
Shipping Approval					
ABS		GL	Lloyd's Register	PRS	RINA
Shipping Approval	other				
RMRS	Confirmation	DE VDE			
UL/CSA ratings:					
yielded mechanical	performance (hp)				
 for single-phase s 	squirrel cage motors				
• at 110/120 V /	rated value		hp	1	
• at 230 V / rated	d value		hp	3	
• for three-phase se	quirrel cage motors				
• at 200/208 V /	rated value		hp	3	
• at 220/230 V /	rated value		hp	5	
• at 460/480 V /	rated value		hp	10	
• at 575/600 V /	rated value		hp	15	
Operating current (F	LA) / for three-phas	e squirrel cage motors			
• at 480 V / rated v	alue		А	14	
• at 600 V / rated v	alue		А	17	
Contact rating desig	nation / for auxiliary	/ contacts / according to		A600 / Q600	
Sicherheitsreleva	nte Kenngrößen:				
B10 value / with high	h demand rate				
 according to SN 3 	31920			1,000,000	
T1 value / for proof t	est interval or servio	ce life			

• according to IEC 61508

а

20

Proportion of dangerous failures		
with low demand rate / according to SN 31920	%	40
• with high demand rate / according to SN 31920	%	73
Failure rate (FIT value) / with low demand rate		
according to SN 31920	FIT	100
Product function		
• mirror contact to IEC 60947-4-1		Yes
positively driven operation to IEC 60947-5-1		No

Further information:

Information- and Downloadcenter (Catalogs, Brochures,...) http://www.siemens.com/industrial-controls/catalogs

Industry Mall (Online ordering system)


http://www.siemens.com/industrial-controls/mall


Cax online generator:


http://www.siemens.com/cax


Service&Support (Manuals, Certificates, Characteristics, FAQs,...) http://support.automation.siemens.com/WW/view/en/3RT2025-1AC20/all


Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...) http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3RT2025-1AC20











last change:

Jul 26, 2012