

## Cable tie - WT-UV HF 3,6X200 BK - 3240833

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable binders for quick and permanent fastening, UV-resistant and weatherproof (ISO 4892\_QUV-B 600 h)

Image shows WT-UV HF 2,5x98 BK version

### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	100 pc
Weight per Piece (excluding packing)	1.0 g
Custom tariff number	39269097
Country of origin	Croatia

### Technical data

#### Dimensions

Length (b)	200 mm
Width (a)	3.6 mm
Cable diameter	2 mm ... 50 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C
Ambient temperature (assembly)	-10 °C ... 60 °C
Optimum ambient temperature (storage/transport)	23 °C 50 % Polyamide 6.6 has pronounced hygroscopic properties. It absorbs or releases water in accordance with the level of humidity within its environment. Its properties are ideal when the percentage of water is 2 - 3%. The packaging, which is tailored specifically to the product concerned, contains the optimum level of moisture. To ensure that the ideal properties are maintained, the following points should be observed during storage: Keep product stored inside sealed original packaging, carry out any product processing soon after breaking open the packaging, avoid direct sunlight, avoid direct heat.

#### General

Color	black
Type	Internal teeth

## Cable tie - WT-UV HF 3,6X200 BK - 3240833

### Technical data

#### General

Components	free from silicone and halogen
Flammability rating according to UL 94	V2
Material	PA 6.6
RoHS compliant	Yes

#### Standards and Regulations

Order No.	3240833
Product key	BG4133
Resistance to UV radiation	yes
Flammability rating according to UL 94	V2

### Classifications

#### eCl@ss

eCl@ss 4.0	27140702
eCl@ss 4.1	27140702
eCl@ss 5.0	27140702
eCl@ss 5.1	27140702
eCl@ss 6.0	27140702
eCl@ss 7.0	27140702
eCl@ss 8.0	27140702

#### ETIM

ETIM 3.0	EC000046
ETIM 4.0	EC000046
ETIM 5.0	EC000046

#### UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	27121703