

Safety module - IB IL 24 PSDO 8-PAC - 2985631

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Safety-oriented digital output module, IP20 degree of protection, for the INTERBUS-Safety and the PROFIsafe system. The module has four safe digital outputs with two-channel occupancy or eight safe digital outputs with single-channel occupancy

Product description

The safety module is an output module from the Inline product range, designed for use in an INTERBUS-Safety or PROFIsafe system. The safety module can be used as part of an Inline station at any point within an INTERBUS-Safety or PROFIsafe Inline system. The transmission speed of the safety module can be set to 500 kbaud or 2 Mbaud using a switch. Only one transmission speed must be used uniformly within a station. The module has four safe digital outputs for two-channel assignment or eight safe digital outputs for single-channel assignment. The outputs can be parameterized according to the application and enable the integration of actuators in the safe INTERBUS system (INTERBUS-Safety) and in the PROFIsafe system. Depending on the installation and parameterization, in these systems the safety module can achieve the following safety integrity:

- Up to category 4 according to standard EN 954-1
- Up to SIL 3 according to standards EN 61508 and EN 62061
- Up to PL e according to standard EN ISO 13849-1

Why buy this product

- PL e according to EN ISO 13849-1
- SIL 3 according to IEC 61508/EN 61508
- SIL CL 3 according to IEC 62061/DIN EN 62061

Key commercial data

Packing unit	0
Minimum order quantity	1
Catalog page	Page 45 (AX-2011)
GTIN	 4 046356 131605
Custom tariff number	85389091
Country of origin	GERMANY

Technical data

Interface

Fieldbus system	INTERBUS
Name	Local bus
Connection method	Inline data jumper
Transmission speed	500 kbaud/2 Mbaud, can be selected
Transmission speed	500 kBit/ / 2 MBit/s

Digital outputs

Output name	Digital outputs
-------------	-----------------

Safety module - IB IL 24 PSDO 8-PAC - 2985631

Technical data

Digital outputs

Connection method	Spring-cage connection
Connection method	2, 3, 4-wire
Number of outputs	4 (with two-channel assignment)
Number of outputs	8
Protective circuit	Overload protection, short-circuit protection of outputs
Output voltage	24 V DC (US - 1 V)
Nominal output voltage	24 V DC
Output current	max. 6 A (Total current of all outputs, -25 °C ... 50 °C)
Output current	max. 4 A (Total current of all outputs, >50 °C ... 55 °C)
Maximum output current per channel	2 A
Maximum output current per module	3 A (See technical data)
Maximum output current per group	3 A
Nominal load, inductive	(see safety data)
Nominal load, lamp	(see safety data)
Nominal load, ohmic	(see safety data)

Power supply for module electronics

Supply voltage	24 V DC (via voltage jumper)
Supply voltage range	19.2 V DC ... 30 V DC
Communications power UL	7.5 V (via voltage jumper)
Current consumption	max. 230 mA (from the local bus)

General data

Width	48.8 mm
Height	119.8 mm
Depth	71.5 mm
Note on dimensions	Housing dimensions
Weight	200 g
Note on weight specifications	with male connectors
Mounting type	DIN rail
Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Permissible humidity (operation)	10 % ... 85 % (Take suitable measures against increased air humidity within the permitted temperature range.)
Permissible humidity (storage/transport)	10 % ... 85 % (Take suitable measures against increased air humidity within the permitted temperature range.)
Air pressure (operation)	80 kPa ... 108 kPa (up to 2000 m above sea level)
Air pressure (storage/transport)	66 kPa ... 108 kPa (up to 3500 m above mean sea level)
Degree of protection	IP20
Protection class	III, IEC 61140, EN 61140, VDE 0140-1
Test section	5 V supply, incoming remote bus/7.5 V supply (bus logics) 500 V AC 50 Hz 1 min
Test section	5 V supply, outgoing remote bus/7.5 V supply (bus logics) 500 V AC 50 Hz 1 min
Test section	7.5 V supply (bus logics)/24 V supply (I/O) 500 V AC 50 Hz 1 min

Safety module - IB IL 24 PSDO 8-PAC - 2985631

Technical data

General data

Test section	24 V supply (I/O) / functional earth ground 500 V AC 50 Hz 1 min
Diagnostics messages	Short-circuit / overload of the digital outputs Error message in diagnostics code (bus) and display by means of the LED on the motor

Inline potential routing

Communications power UL	7.5 V DC (see safety data)
Current consumption from UL	max. 230 mA (see safety data)
Main circuit supply UM	24 V DC
Supply voltage range UM	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current consumption from UM	Typ. 30 mA (all outputs set including actuator current)
Current consumption from UM	max. 6.03 A
Segment supply voltage US	24 V

Classifications

eclass

eCl@ss 4.0	27250308
eCl@ss 4.1	27250308
eCl@ss 5.0	27250308
eCl@ss 5.1	27242904
eCl@ss 6.0	27242604
eCl@ss 7.0	27242604

etim

ETIM 2.0	EC001433
ETIM 3.0	EC001617
ETIM 4.0	EC001599

unspsc

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	43201404

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / PROFIBUS / UL Recognized / cUL Recognized / PROFIBUS / cULus Recognized

Safety module - IB IL 24 PSDO 8-PAC - 2985631

Approvals

Ex Approvals

Approvals submitted

Approval details

UL Recognized

cUL Recognized

PROFIBUS

UL Recognized

cUL Recognized

PROFIBUS

cULus Recognized

Accessories

Accessories

Marking

Labeling field - IB IL FIELD 2 - 2727501

Labeling field, width: 12.2 mm



Safety module - IB IL 24 PSDO 8-PAC - 2985631

Accessories

Labeling field - IB IL FIELD 8 - 2727515

Labeling field, width: 48.8 mm



Insert strip - ESL 62X10 - 0809492

Insert strip, Sheet, white, Unlabeled, Can be labeled with: Office-Drucksysteme, Plotter: Laser printer, Mounting type: Insert, Lettering field: 62 x 10 mm



Insert strip - ESL 62X46 - 0809502

Insert strip, Sheet, white, Unlabeled, Can be labeled with: Office-Drucksysteme, Plotter: Laser printer, Mounting type: Insert, Lettering field: 62 x 46 mm



Plug/Adapter

Connector set - IB IL 24 SDO 8-PLSET/CP - 2916927



Connector set (yellow), color coded, for safe SDO boards.

User manual - UM DE IB IL 24 SDO 8-PAC - 2888835

User Manual, German, for INTERBUS Safety output modules



Safety module - IB IL 24 PSDO 8-PAC - 2985631

Accessories

User manual - UM EN IB IL 24 SDO 8-PAC - 2888864



User Manual, English for PLCopen-certified INTERBUS Safety function blocks

User manual - UM QS EN IB IL 24 PSDX - S7 - 2910648



User manual, English

User manual - UM QS DE IB IL 24 PSDX - S7 - 2910651



User manual, german
