

EL-GFX-DTC

Dual Channel K, J and T type Thermocouple Data Logger with Graphic Screen

ORDERING INFORMATION

Standard Data Logger EL-GFX-DTC
(Data Logger, 2 x Batteries, USB cover, Mounting Clip, 2 x TC probes, Micro USB cable)

Replacement Battery BAT 3V6 ½AA
(2 Required)

FEATURES

- Rugged and robust construction
- Dual channel, compatible with K, J and T type Thermocouples
- Logging rates between 2 seconds and 12 hours
- Stores over 250,000 readings
- On screen menu and graphing to start, stop, review and restart the logger in the field
- Micro USB interface for PC based set-up and data download
- Immediate, delayed, push-button or temperature triggered start mode
- Graphic LCD shows real-time readings, graph and current status
- User set audible alarm
- Highly visible confidence/alarm LEDs
- Supplied with user replaceable ½ AA batteries



The EL-GFX-DTC standalone USB data logger measures and stores up to 252,928 temperature readings from two J, K, or T-type thermocouple inputs at a resolution of 0.1°C. Using the Windows control software (available as a free-download from www.easylogusb.com), users can quickly set up the data logger and view downloaded data by connecting the device to the PC's USB port using the supplied cable.

The data logger features a high-contrast graphic LCD and three-input buttons which allows users to start, stop and restart the data logger using on-screen menus. This menu also provides real-time analysis of data either as a data summary (showing highest & lowest readings and alarm conditions) or as a graph that updates as new data is added. Multiple data logging sessions can be stored on the device ready for upload to a PC at a later date.

The two replaceable ½AA batteries typically allow logging for up to one year.

Specifications		Minimum	Typical	Maximum	Unit
Probe measurement range	K-type	-200 (-328)		+1350 (+2462)	°C (°F)
	J-type	-200 (-328)		+1190 (+2174)	°C (°F)
	T-type	-200 (-328)		+390 (+734)	°C (°F)
Internal resolution			0.1 (0.1)*		°C (°F)
Accuracy (overall error)			±0.5 (±0.9)**		°C (°F)
Logging rate		Every 2 seconds		Every 12 hour	Time
Operating temperature range***		-10 (-14)		+40 (+104)	°C (°F)
2 x ½AA 3.6V Lithium Battery Life			1†		Year

* Above 999.9°C/F display becomes 1°C. Internal resolution remains at 0.1°C/F.

** Quoted accuracy is for the data logger only when measuring within the specified operating temperature. Thermocouple error is not included and should also be taken into consideration.

*** Operating temperature applies to the data logger module only. Please consult the probe manufacturer for operating temperature of thermocouple.

† At 25 °C and 10 minute logging rate with no alarm LEDs or sounder and minimal LCD use.

EL-GFX-DTC

Dual Channel K, J and T type Thermocouple Data Logger with Graphic Screen

EL-WIN-USB (CONTROL SOFTWARE)

Lascar's Easylog USB control software is available to download from www.easylogusb.com. Easy to install and use, the control software runs under Windows XP, Vista and Windows 7. The software is used to set-up the data logger as well as download, graph and export data to Excel. Each stored logging session is saved as a separate file.

The software allows the following parameters to be configured:

- Logger name
- Measurement parameter (°C or °F)
- Logging Rate (customisable between 2 seconds and 12 hours)
- High and low temperature alarms
- Immediate, delayed, push-button or temperature triggered start mode
- Disable or enable LEDs and sounder with delayed activation
- Display and backlight behaviour after button press



The latest version of the control software may be downloaded free of charge from www.easylogusb.com

DIMENSIONS

All dimensions in mm (inches)













SHOWN ACTUAL SIZE

EL-GFX-DTC

Dual Channel K, J and T type Thermocouple Data Logger with Graphic Screen

MENU BUTTON FUNCTIONS AND LED SCREEN INDICATION

  	<p>START</p> <ul style="list-style-type: none"> Loggers can be started immediately on a button press, delayed to a specific time or delayed to specific temperature reading 		<p>MUTE ALARM</p> <ul style="list-style-type: none"> Audible alarm can be muted if required
		<p>SUMMARY DATA</p>   <ul style="list-style-type: none"> Summary screen displays max/min log and last log. Reset function clears summary if required 	
 		<p>LOCK MENU BUTTONS</p>  <ul style="list-style-type: none"> 'Locked' mode can be unticked during PC set-up if required When in locked mode, the logger can only be stopped and re-started using a PC loaded with the unit's configuration software 	


BATTERY REPLACEMENT

We recommend that you replace the batteries every 12 months, or prior to logging critical data.

The EL-GFX-DTC does not lose its stored readings when the batteries are discharged or when the batteries are replaced; however, the data logging process will be stopped. If the batteries are changed within a 2 minute window the EL-GFX-DTC will retain its settings (internal clock and logging mode). This will allow logging to be restarted without additional connection to a PC via USB.

Only use 2 x 3.6V ½AA lithium batteries. Do not mix battery types and do not mix new and old batteries. Before replacing the batteries, unplug the EL-GFX-DTC from the PC.

TEMPERATURE ACCURACY



EL-GFX-DTC

Dual Channel K, J and T type Thermocouple Data Logger with Graphic Screen

WARNING

Handle lithium batteries carefully, observe warnings on battery casing. Dispose of in accordance with local regulations.

CAUTION

The K-Type thermocouple probes supplied with the EL-GFX-DTC are not electrically isolated from the thermocouple junction, to give a faster response.

However depending upon application it may be necessary to use electrically isolated thermocouple probes to avoid ground loops, and/or situations where the probes may come into contact with conductors that are at different electrical potentials.

Where doubt exists Lascar recommends that electrically isolated probes are always used.

Module House
Whiteparish, Salisbury
Wiltshire SP5 2SJ
UK
T +44 (1794) 884567
F +44 (1794) 884616
E sales@lascar.co.uk

4258 West 12th Street
Erie
PA 16505
USA
T +1 (814) 835 0621
F +1 (814) 838 8141
E us-sales@lascarelectronics.com

8th Floor, China Aerospace Centre
143 Hoi Bun Road
Kwun Tong, Kowloon
HONG KONG
T +852 2797 3219
F +852 2343 6187
E saleshk@lascar.com.hk



www.lascarelectronics.com

