

MBC150 SERIES MEDICAL 150W AC/DC



FEATURES

- 110 W convection cooled
- -20 to 50 deg C full load operation
- 2 x MOPP Isolation
- 90-264 VAC input
- **2**" x 4" x 1.3" (50.8 x 101.6 x 33.6 mm)
- Fan output, 12 Vdc @ 0.5A standard
- No minimum load required
- Conducted EMI EN 55022-B, FCC Part 15 Level B
- Medical Safety Agency Approvals

APPLICATIONS

- Dialysis
- Monitoring
- O Pumps

- Surgical Devices
- O Home Health
- O Portable Devices



TECHNICAL DATA:

Input

| PARAMETER | DESCRIPTION/CONDITION | DESCRIPTION/CONDITION | | |
|-------------------------------|--------------------------------------------|-----------------------|--|--|
| Input Voltage Range | Universal Input | 90 - 264 Vac | | |
| | Oniversal input | 120 – 390 Vdc | | |
| Input Frequency Range | 47-63 Hz | | | |
| Input Surge Current | 230 Vac (cold start) | 65 A max. | | |
| Safety Ground Leakage Current | 264 Vac 50 / 60 Hz | < 250 μA max | | |
| Input Current | 120 Vac @ Full load 230 Vac @ Full load | 1.7 A 0.85 A | | |

Output

| PARAMETER | DESCRIPTION/CONDITION | | |
|----------------------------------|------------------------------------------------------------------------|-------------------------------|--|
| Voltage Adjustment | V1 | ± 3% | |
| Transient Response | Main output 50 to 100% load change, 50 Hz, 50% duty cycle, 0.1A / uSec | < 10%, recovery time < 5 mSec | |
| Over Voltage Protection | V1 | 110 to 150% rated max | |
| Over Current Protection | Rated output current | 110% Typical | |
| Short Circuit Protection | Automatic recovery | | |
| Efficiency | >86% | | |
| Rise Time | < 100 mSec | | |
| Set Point Accuracy (Main Output) | ± 1% | | |

Ordering Information

| PRODUCT FAMILY | VOLTS (VDC) | MAX LOAD CONVECTION (1) | MAX LOAD 300 LFM (1) | MINIMUM LOAD (A) | RIPPLE & NOISE (4) | CONNECTOR | TOTAL REGULATION |
|-------------------|----------------|-------------------------|-----------------------------|---------------------|--------------------|----------------|------------------|
| MBC150-1005G | 5.0 | 16.0 A | 16 A | 0 | 1% | JST | ± 2.5% |
| MBC150-1005G-2 | 5.0 | 16.0 A | 16 A | 0 | 1% | JST | ± 2.5% |
| MBC150-1T05G | 5.0 | 16.0 A | 20 A | 0 | 1% | Screw Terminal | ± 2.5% |
| MBC150-1T05G-2 | 5.0 | 16.0 A | 20 A | 0 | 1% | Screw Terminal | ± 2.5% |
| MBC150-1012G | 12 | 8.33 A | 12.5 A | 0 | 1% | JST | ± 2.5% |
| MBC150-1012G-2 | 12 | 8.33 A | 12.5 A | 0 | 1% | JST | ± 2.5% |
| MBC150-1T12G | 12 | 8.33 A | 12.5 A | 0 | 1% | Screw Terminal | ± 2.5% |
| MBC150-1T12G-2 | 12 | 8.33 A | 12.5 A | 0 | 1% | Screw Terminal | ± 2.5% |
| MBC150-1015G | 15 | 6.67 A | 10.0 A | 0 | 1% | JST | ± 2.5% |
| MBC150-1015G-2 | 15 | 6.67 A | 10.0 A | 0 | 1% | JST | ± 2.5% |
| MBC150-1T15G | 15 | 6.67 A | 10.0 A | 0 | 1% | Screw Terminal | ± 2.5% |
| MBC150-1T15G-2 | 15 | 6.67 A | 10.0 A | 0 | 1% | Screw Terminal | ± 2.5% |
| MBC150-1024G | 24 | 4.17 A | 6.25 A | 0 | 1% | JST | ± 2.5% |
| MBC150-1024G-2 | 24 | 4.17 A | 6.25 A | 0 | 1% | JST | ± 2.5% |
| MBC150-1T24G | 24 | 4.17 A | 6.25 A | 0 | 1% | Screw Terminal | ± 2.5% |
| MBC150-1T24G-2 | 24 | 4.17 A | 6.25 A | 0 | 1% | Screw Terminal | ± 2.5% |
| MBC150-1048G | 48 | 2.08 A | 3.13 A | 0 | 1% | JST | ± 2.5% |
| MBC150-1048G-2 | 48 | 2.08 A | 3.13 A | 0 | 1% | JST | ± 2.5% |
| MBC150-1T48G | 48 | 2.08 A | 3.13 A | 0 | 1% | Screw Terminal | ± 2.5% |
| MBC150-1T48G-2 | 48 | 2.08 A | 3.13 A | 0 | 1% | Screw Terminal | ± 2.5% |
| Vfan (all models) | 12 | 0.5 A ⁽³⁾ | 0.5 A ⁽³⁾ | | | | 20% |

MBC150 Series 2 www.power-one.com



Notes:

- 1. Combined power from main output and Vfan should not exceed total power rating.
- 2. Fan output tolerance is \pm 20%.
- 3. Peak current for fan output is 1A.
- 4. Ripple is 2% up to 20% load and less than 1% above 20% load. Output noise measurement is made with a 20 MHz bandwidth using a 6" twisted pair, terminated with a 10 uF tantalum capacitor in parallel with a 0.1 uF ceramic capacitor.
- 5. Class 1 models have Earthing tab J4. Class 2 models (-2 suffix) have no Earthing tab.
- 6. Specifications are for nominal input voltage, 25°C and max load unless otherwise stated.
- 7. Air flow over length of supply recommended (either direction) for forced air rating.
- 8. Derate output power per chart below.
- 9. Specifications subject to change without notice.
- 10. Warranty 2 years.

General Specifications

| PARAMETER | DESCRIPTION/CONDITION | DESCRIPTION/CONDITION | | | |
|---------------------|------------------------------------------------------|------------------------------------------------------------|--|--|--|
| Hold Up Time | 120 Vac | 6 mSec | | | |
| | 230 Vac | 10 mSec | | | |
| MTBF | >200 khrs | Bellcore TR-332 | | | |
| Switching Frequency | PFC converter variable 35 to 250 kHz, 90 kHz typical | Resonant converter: Variable 35 to 250 kHz, 90 kHz typical | | | |
| Isolation Voltage | Input to Output Min 5900 Vdc | Input to Ground 2120 Vdc | | | |
| Weight | 150 g (0.33 lbs) | | | | |

Environmental

| PARAMETER | DESCRIPTION/CONDITION | |
|--------------------------------|------------------------------|------------------------------------------|
| On a ratio a Tarana a rationa | Operating | -20 to +70°C. See derating charts below. |
| Operating Temperature | Storage | -40 to +85°C |
| Altitude | Operating 10,000 ft. | Non-operation 40,000 ft. |
| Humidity | 95% | Non-condensing |
| Conducted Emissions | EN55022, FCC part 15 Level B | |
| Radiated Emissions | EN55022, FCC part 15 Level B | To be controlled in end system |
| Electromagnetic Susceptibility | EN61000-4 | 2, 3, 4, 5 Level 3 |
| Harmonic Current | EN61000-3-2, Class D | |

Safety

| PARAMETER | DESCRIPTION/CONDITION | |
|---------------|-----------------------|--|
| EN / UL / CSA | 60601-1 3rd Edition | |

Figure 1 Output Power Vs. Temperature





Figure 2 Dimension Drawing (Top and Side View)



MECHANICAL OUTLINE DIMENSIONS
DIMENSIONS UNIT: INCH [M.M]
GEN. TOLERANCE:+/-0.020 [0.50]

Mechanical

| INPUT = J1 | EARTHING TAB = J4 | DC OUTPUT = J2 | | FAN= J3 |
|------------------------------------------------------------|---------------------------------------|-----------------------------------------------------------------------|----------------------------|--------------------------------------------------------------------|
| Pin 1: AC Line Pin 2: Removed Pin 3: AC Neutral | Molex: 19705-4301 | Pin 1 = V1 Pin 2 = V1 | Pin 3 = RTN Pin 4 = RTN | Pin 1 = +12 V @ 0.5 A Pin 2 = Fan return (isolated from DC output) |
| Mating Connector: Molex: 09-50-3031 Pins: 08-50-0106 | Mating Connector: Molex: 190030001 | Mating Connector: JST VHR-4M, Pins: SVH-41T-P1.1 AWG #20 to #16 | | Mating Connector: Tyco: 640440-2 |

Copyright © 2010 Power-One Inc. All rights reserved. Words and logos that are identified as trademarks and/or service marks are, unless noted otherwise, the trademarks and service marks of Power-One Inc. in the U.S. and other countries. All other product or service names are the property of their respective holders. Power-One products are protected under numerous U.S. and foreign patents and pending applications, maskwork rights, and copyrights. Power-One reserves the right to make changes to any products and services at any time without notice. Power-One assumes no responsibility or liability arising out of the application or use of any information, product, or service described herein except as expressly agreed to in writing by Power-One Inc.

NUCLEAR AND MEDICAL APPLICATIONS - Power-One products are not designed, intended for use in, or authorized for use as critical components in life support systems, equipment used in hazardous environments, or nuclear control systems without the express written consent of the respective divisional president of Power-One, Inc.

TECHNICAL REVISIONS - The appearance of products, including safety agency certifications pictured on labels, may change depending on the date manufactured. Specifications are subject to change without notice.