






CONNECTORS J1-J6

MALE END VIEW



SPECIFICATIONS

HOUSING/COLOR	NYLON/YELLOW
RECEPTACLE	BRASS/NICKEL (J1-J6)
CONTACT CARRIERS/COLOR	NYLON/BLACK (J1-J6)
CONTACT CARRIER MATERIAL/COLOR	NYLON or PBT/GRAY (P1)
CONTACT MATERIAL/PLATING	BRASS/GOLD (P1, J1-J6)
COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL (P1)
SEALING RING	VITON O-RING (J1-J6)
ELECTRICAL DATA	
OPERATING VOLTAGE [V]	10-48 VDC
OPERATING CURRENT [A]	3.0 AMPS PER PORT, 9.0 AMPS TOTAL
MECHANICAL DATA	
PROTECTION CLASS to DIN 40050	IP 67 - ONLY WHEN ALL RECEPTACLES ARE COVERED WITH PLUGS OR CONNECTED
OPERATING TEMPERATURE	-40°C to +105°C (-40°F to +221°F)



SOURCE DRAWING - FOR REFERENCE ONLY



VZ 3 CLOSURE CAPS (INCLUDED)

RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		TURCK INC High Technology Sensors and Automation Controls 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com	
	MATERIAL SEE SPECIFICATIONS	DRFT RJP	DATE 10/03/96	DESCRIPTION VB 60.5-CS19	
FINISH SEE SPECIFICATIONS	ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY	DSGN	SCALE 1=2.0	IDENTIFICATION NO. U0220	
		UNIT OF MEASUREMENT MILLIMETER [INCH]		REV C	
C	UPDATE SOURCE DRAWING TO CURRENT TITLE BLOCK & STANDARDS	RDS	08/01/11	35946	
REV	DESCRIPTION	BY	DATE	ECO NO.	
		DO NOT SCALE THIS DRAWING		FILE: U0220	SHEET 1 OF 1