

0359	0358	0360	0343
0359-0-15-XX-34-XX-10-0 Press-fit in .090 mounting hole	0358-0-15-XX-34-XX-10-0 Press-fit in .090 mounting hole	0360-0-15-XX-34-XX-10-0 Press-fit in .090 mounting hole	0343-0-15-XX-34-XX-10-0 Press-fit in .090 mounting hole

0356	6659	0347	0329
0356-0-15-XX-34-XX-10-0 Solder mount in .102 min. mounting hole Also available on 24mm wide carrier tape: 1,100 parts per 13" reel. Order as: 0356-0-57-XX-34-XX-10-0	6659-0-15-XX-34-XX-10-0 Solder mount in .102 min. mounting hole	0347-0-15-XX-34-XX-10-0 Solder mount in .120 min. mounting hole	0329-0-15-XX-34-XX-10-0 Solder mount in .075 min. mounting hole. "knock out" bottom.

0814	5059	8360	9359
0814-0-15-XX-34-XX-04-0 Solder mount in .082 min. mounting hole	5059-0-15-XX-34-XX-04-0 Press-fit in .090 mounting hole	8360-0-15-XX-34-XX-10-0 Press-fit in .087 mounting hole	9359-0-15-XX-34-XX-10-0 Press-fit in .090 mounting hole

<p>SPECIFICATIONS</p> <p>SHELL MATERIAL: Brass Alloy 360, 1/2 Hard</p> <p>CONTACT MATERIAL: Beryllium Copper Alloy 172, HT</p> <p>DIMENSION IN INCHES TOLERANCES ON: LENGTHS: ±.005 DIAMETERS: ±.002 ANGLES: ± 2°</p>	<p>ORDER CODE: XXXX - X - 15 - XX - 34 - XX - XX - 0</p> <p>BASIC PART # →</p> <p>SPECIFY SHELL FINISH:</p> <ul style="list-style-type: none"> 01 200μ" TIN/LEAD OVER NICKEL ◇ 80 200μ" TIN OVER NICKEL (RoHS) ◇ 15 10μ" GOLD OVER NICKEL (RoHS) <p style="text-align: center;">CONTACT</p> <p>#34 CONTACT (DATA ON PAGE 224)</p>	<p>SPECIFY CONTACT FINISH:</p> <ul style="list-style-type: none"> 01 200μ" TIN/LEAD OVER NICKEL ◇ 80 200μ" TIN OVER NICKEL (RoHS) ◇ 27 30μ" GOLD OVER NICKEL (RoHS)
--	--	---