

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://download.phoenixcontact.com)



Sensor/Actuator cable, 4-position, PVC, Yellow RAL 1021, Plug angled M12-SPEEDCON, A-coded, on Socket angled M8, Cable length: 1.5 m







## Key commercial data

Packing unit	1 PCE
GTIN	4 046356 798228
Custom tariff number	85444290
Country of origin	UNITED STATES

### Technical data

### **Dimensions**

Length of cable	1.5 m
-----------------	-------

#### Ambient conditions

Ambient temperature (operation)	-25 °C 90 °C (Plug / socket)
Degree of protection	IP65
	IP67
	IP68

### General

Rated current at 40°C	4 A
Rated voltage	30 V
Number of positions	4
Contact resistance	$\leq 5~\text{m}\Omega$
Insulation resistance	$\geq$ 100 M $\Omega$
Standards/regulations	M12 plug-in connector IEC 61076-2-101



## Technical data

### General

	M8 plug-in connector IEC 61076-2-104
Coding	A - standard
Surge voltage category	II
Pollution degree	3
Insertion/withdrawal cycles	≥ 100
Torque	0.4 Nm (M12 plug-in connector)
	0.2 Nm (M8 plug-in connectors)
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material of grip body	TPU, hardly inflammable, self-extinguishing
Material, knurls	Zinc die-cast, nickel-plated
Sealing material	NBR
Status display	No

#### Line characteristics

Cable type	PVC yellow 105 °C
Cable type (abbreviation)	542
UL AWM style	2517 (105°C/300 V)
AWG signal line	24
Core diameter including insulation	1.12 mm ±0.03 mm
Wire colors	brown, blue, black, white
Overall twist	4 wires, twisted
External sheath, color	yellow
External cable diameter D	4.4 mm ± 0.2 mm
Minimum bending radius, flexible installation	8 x D
Cable weight	25 kg/km
Outer sheath, material	PVC
Material conductor insulation	PVC
Conductor material	Tin-plated Cu litz wires
Nominal voltage, cabel	300 V
Other resistance	UV resistant
Ambient temperature (operation)	-30 °C 105 °C (cable, fixed installation)

## Classifications

## eCl@ss

eCl@ss 4.0	27060306



## Classifications

## eCl@ss

eCl@ss 4.1	27060306
eCl@ss 5.0	27061801
eCl@ss 5.1	27061801
eCl@ss 6.0	27061801
eCl@ss 7.0	27061801

### **ETIM**

ETIM 3.0	EC001855
ETIM 4.0	EC001855
ETIM 5.0	EC001855

## **UNSPSC**

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	31251501

## Approvals

Approvals
-----------

Approvals

UL Listed / cUL Listed / cULus Listed

Ex Approvals

Approvals submitted

## Approval details

UL Listed (II)	
Nominal current IN	4 A



## Approvals

Nominal voltage UN	125 V

cUL Listed (1)	
Nominal current IN	4 A
Nominal voltage UN	125 V

cULus Listed • 🐠 😘

## Accessories

Accessories

Fuse

Fuse clip - SAC-M12-EXCLIP-M - 1558988



Fuse clip for the pin side of various M12 sensor/actuator connectors prevents plug-in connections being interrupted without using a tool

Protection and sealing elements

Sealing cap - PROT-M12 FS-PA-CHAIN - 1430873

M12 sealing cap made of plastic with fixing band, for sensor cables, for free M12 sockets





## Accessories

Screw plug - PROT-M 8 MS-PA-CHAIN - 1430860

M8 sealing cap made of plastic with fixing band for sensor cables, for M8 sockets



#### **Tools**

Torque screwdriver - TSD 02 SAC - 1208487



Torque screwdriver, with preset torque of 0.2 Nm and 4 mm hexagonal drive for M8 connectors

#### Tool - SAC BIT M8-D10 - 1208461



Nut for assembling sensor/actuator cables with M8 connector and for M8 connectors with QUICKON fast connection technology, for 4 mm hexagonal drive

## Torque screwdriver - TSD 04 SAC - 1208429



Torque screwdriver, with preset torque of 0.4 Nm and 4 mm hexagonal drive for M12 connectors

### Torque screwdriver - TSD-M 1,2NM - 1212224



Torque screw driver, accuracy as per EN ISO 6789 standard, adjustable from 0.3 - 1.2 Nm



### Accessories

Adapter insert - TSD-M SAC-BIT ADAPTER - 1212600



Adapter bit for TSD-M...torque tools, E6.3-1/4" drive with 4 mm hexagon to accommodate SAC bits

#### Tool - SAC BIT M12-D15 - 1208432



Nut for assembling sensor/actuator cables with M12 connector and for M12 connectors with QUICKON fast connection technology, for 4 mm hexagonal drive


## Drawings

#### Schematic diagram



Pin assignment M12 plug, 4-pos., A-coded, view plug side

## Dimensioned drawing




M12 x 1 male plug, angled

#### Schematic diagram



Pin assignment M8 socket, 4-pos., view female side


#### Dimensioned drawing



Socket M8 x 1, straight



## Circuit diagram



Contact assignment of M12 plugs / M8 sockets

© Phoenix Contact 2013 - all rights reserved http://www.phoenixcontact.com