



PIN RECEPTACLES
 for .015" - .018" diameter pins (#09 contact)
 for .015" - .020" diameter pins (#11 contact)
 and .015" - .022" diameter pins (#21 contact)
 (see specific contact range on pages 216 & 217)



<h3>0467</h3> <p>0467-0-15-XX-21-XX-04-0 Press-fit in .037 mounting hole</p>	<h3>0552</h3> <table border="1"> <thead> <tr> <th>Basic Part Number</th> <th>Length L</th> <th>Depth N</th> </tr> </thead> <tbody> <tr> <td>0552-1</td> <td>.136</td> <td>.120</td> </tr> <tr> <td>0552-2</td> <td>.170</td> <td>.150</td> </tr> </tbody> </table> <p>0552-X-15-XX-X1-XX-10-0 Solder mount in .040 min. mounting hole Also available on 16mm wide carrier tape: 1,500 parts per 13" reel. Order as: 0552-X-57-XX-X1-XX-10-0</p>	Basic Part Number	Length L	Depth N	0552-1	.136	.120	0552-2	.170	.150	<h3>5522</h3> <p>5522-0-15-XX-09-XX-10-0 Solder mount in .040 min. mounting hole</p>
Basic Part Number	Length L	Depth N									
0552-1	.136	.120									
0552-2	.170	.150									

<h3>0569</h3> <p>0569-0-15-XX-X1-XX-10-0 Solder mount in .040 min mounting hole</p>	<h3>6023</h3> <p>6023-0-15-XX-21-XX-10-0 Solder mount in .040 min mounting hole</p>	<h3>6214</h3> <p>6214-0-15-XX-21-XX-10-0 Solder mount in .040 min mounting hole</p>	<h3>2086</h3> <p>2086-0-15-XX-21-XX-04-0 Press-fit in .040 mounting hole</p>
--	--	--	---

<h3>0461</h3> <table border="1"> <thead> <tr> <th>Basic Part Number</th> <th>Length A</th> </tr> </thead> <tbody> <tr> <td>0461-0</td> <td>.400</td> </tr> <tr> <td>0461-1</td> <td>.275</td> </tr> <tr> <td>0461-2</td> <td>.180</td> </tr> <tr> <td>0461-3</td> <td>.125</td> </tr> <tr> <td>0461-4</td> <td>.060</td> </tr> <tr> <td>0461-5</td> <td>.440</td> </tr> </tbody> </table> <p>0461-X-15-XX-X1-XX-04-0 Solder mount in .020 min. mounting hole</p>	Basic Part Number	Length A	0461-0	.400	0461-1	.275	0461-2	.180	0461-3	.125	0461-4	.060	0461-5	.440	<h3>8579</h3> <table border="1"> <thead> <tr> <th>Basic Part Number</th> <th>Length L</th> </tr> </thead> <tbody> <tr> <td>8579-0</td> <td>.234</td> </tr> <tr> <td>8579-1</td> <td>.295</td> </tr> </tbody> </table> <p>8579-X-15-XX-X1-XX-10-0 Solder mount in .040 min. mounting hole Also available on 24mm wide carrier tape: 1,200 parts per 13" reel. Order as: 8579-0-57-XX-X1-XX-10-0</p>	Basic Part Number	Length L	8579-0	.234	8579-1	.295
Basic Part Number	Length A																				
0461-0	.400																				
0461-1	.275																				
0461-2	.180																				
0461-3	.125																				
0461-4	.060																				
0461-5	.440																				
Basic Part Number	Length L																				
8579-0	.234																				
8579-1	.295																				

<p>SPECIFICATIONS</p> <p>SHELL MATERIAL: Brass Alloy 360, 1/2 Hard</p> <p>CONTACT MATERIAL: Beryllium Copper Alloy 172, HT</p> <p>DIMENSION IN INCHES TOLERANCES ON: LENGTHS: ±.005 DIAMETERS: ±.002 ANGLES: ± 2°</p>	<p>ORDER CODE: XXXX - X - 15 - XX - XX - XX - XX - 0</p> <p>BASIC PART # →</p> <p>SPECIFY SHELL FINISH:</p> <ul style="list-style-type: none"> 01 200µ" TIN/LEAD OVER NICKEL ◇ 80 200µ" TIN OVER NICKEL (RoHS) ◇ 15 10µ" GOLD OVER NICKEL (RoHS) <p>SPECIFY CONTACT FINISH:</p> <ul style="list-style-type: none"> 02 100µ" TIN/LEAD OVER NICKEL ◇ 84 100µ" TIN OVER NICKEL (RoHS) ◇ 27 30µ" GOLD OVER NICKEL (RoHS) <p>SELECT CONTACT</p> <p>#09, #11 or #21 CONTACT (DATA ON PAGES 216 & 217)</p>
--	--

