



**75869-105LF - Quickie® : Double Row, 26 Positions, 2.54 mm (0.1 in.), Vertical, Shrouded Header 0.76 µm (30 µin.) Gold or GXT™ Plating**



[www.fci.com](http://www.fci.com)

## Mating Half

 71600-626LF

## Specifications

<b>Approvals / Certifications</b>	
UL File Number	E66906
CSA File Number	LR46923
Approvals / Certifications	UL and CSA Approved
<b>Mechanical</b>	
Retention force	20N min.
<b>Dimensional</b>	
Length (Tail)	3.05 mm (0.12 in.)
<b>Electrical</b>	
Current rating	3 amp Continuous
Resistance (Insulation)	10000 M-ohms
Voltage rating	500V AC rms
<b>General</b>	
Number of contacts (Total)	26
Number of rows	2
Orientation	Vertical
Attachment type (Board)	Through Mount
Mating half	Quickie® IDC series 71600 and Dubox CTW series 65239 and 65548
<b>Mounting</b>	
Solder process	Wave
<b>Other Features</b>	
Packaging (Type)	Tube
Type	Low Profile
<b>Physical</b>	
Color (Housing)	Blue
Material (Contact)	Phosphor Bronze
Plating (Contact area)	0.76 µm (30 µin.) Gold or 0.76 µm (30 µin.) GXT™
Plating (Tail)	3.81 µm (150 µin.) Tin
Underplating (Contact)	1.27 µm (50 µin.) Nickel
Flammability rating	UL 94V-0
Temperature (Range)	-65°C to +125°C