




Have a Question?
 Chat with a Product Information Specialist

What can we help you find?

- [Products](#)
- [Industries](#)
- [Resources](#)
- [About TE](#)
- [My Account](#)
- [Innovation](#)
- [Support Center](#)

5352268-1 Product Details

- [Share](#)
- [Print](#)
- [Email](#)



5352268-1

TE Internal Number: 5352268-1

Active

[View 3D PDF](#)

2mm Hard Metric PCB Mount Connectors (Z-PACK 2mm HM)

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Connector
- Connector Assembly
- Connector Style = Receptacle
- Type = Type B, 22 Column
- Interface Type = 2mm HM

[View all Features](#)

Quick Links

- [Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

- [Add to My Part List](#)
 - [Request Sample](#)
 - [Find Similar Products](#)
- [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [Z-PACK 2mm HM TYPE B 110 POS. 22 COLUMNS VERTICAL FE...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- [Z-PACK 2mm HM Interconnection System for Board-to-Bo...](#) (PDF, English)

Instruction Sheets:

- None Available

CAD Files: (CAD Format & Compression Information)

- [2D Drawing](#) (DXF, Version A)
- [3D Model](#) (IGES, Version A)
- [3D Model](#) (STEP, Version A)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Connector
- Connector Type = Connector Assembly
- [PCB Mounting Orientation](#) = Vertical

Mechanical Attachment:

- [Board Mount](#) = Free Board

Electrical Characteristics:

- [Shielded](#) = No

Termination Features:

- [Interface Type](#) = 2mm HM
- Termination End Plating = Tin over Nickel

Dimensions:

- [Module Length](#) (mm [in]) = 44.00 [1.732]

Body Features:

- Type = Type B, 22 Column

Contact Features:

- [Contact Configuration](#) = Signal
- [Feedthrough Post Length](#) (mm [in]) = 3.30 [0.130]
- [CompactPCI](#) = No
- [Contact Plating, Mating Area, Material](#) = Performance-Based

Housing Features:

- Connector Style = Receptacle
- [Mating Alignment](#) = Without
- [Housing Color](#) = Gray
- [Housing Material](#) = Polyester GF
- [UL Flammability Rating](#) = UL 94V-0

Configuration Features:

- [Number of Rows](#) = 5
- [Number of Positions](#) = 110
- [Crosstalk Version](#) = Standard
- [Rows Loaded](#) = A, B, C, D, E

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

Other:

- [Brand](#) = AMP

- [Grounding Contact = Without](#)
- [Contact Base Material = Phosphor Bronze](#)

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

