



## STANDARD RECTANGULAR CONNECTORS



✓ Active

↓ **PRODUCT DRAWING**  
Japanese

↓ **3D PDF**

TE CONNECTIVITY (TE)

### DYNAMIC D-3200 HDR ASSY 5P V

[Dynamic Series](#) | [Dynamic 3000 Series](#)

1-316132-5

TE Internal Number: 1-316132-5

Always EU RoHS/ELV Compliant

Product Type **Connector**

Mating Alignment **With**

Mating Alignment Type **Keyed**

Mating Retention **With**

Mating Retention Type **Latch**

#### Product Drawings

[DYNAMIC D-3200S 5.08PITCH \(V\) 5 POS. HDR CONN. ASS'Y](#)

PDF (**TIFF AVAILABLE**)  
Japanese

[DYNAMIC D-3200S 5.08PITCH \(V\) 5 POS. HDR CONN. ASS'Y](#)

PDF (**TIFF AVAILABLE**)  
Japanese

#### CAD Files

[3D PDF](#)

PDF  
English

[Customer View Model](#)

3D\_IGS.ZIP  
English

[Customer View Model](#)

3D\_STP.ZIP  
English

[Customer View Model](#)

2D\_DXF.ZIP  
English

#### Catalog Pages/Data Sheets

[D3000 Series Dynamic Connectors Continued](#)

PDF  
English

[1-1773732-4\\_DYNAMIC\\_SERIES\\_CATALOG\\_ENGLISH](#)

PDF  
English

#### Product Specifications

##### Product Specification

[Dynamic Connector D-3000 Series](#)

TIF  
Japanese

[Dynamic Connector D-3000 Series](#)

PDF  
Japanese

##### Qualification Test Report

[DYNAMIC D-3000 SERIES CONNECTOR](#)

PDF  
Japanese

---

## Product Environmental Compliance

TE Material Declaration

[MD\\_1-316132-5\\_02032016725\\_dmtec](#)

PDF  
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

---

Product Type Features	Product Type	<b>Connector</b>
	PCB Mounting Orientation	<b>Vertical</b>
	Sealed	<b>No</b>
	Connector System	<b>Wire-to-Board</b>
	Shielded	<b>No</b>
	Insertion Force	<b>High</b>
	Connector Style	<b>Plug</b>
	Glow Wire Rating	<b>Standard Part - Not Glow Wire</b>
	Strain Relief	<b>Without</b>
	Series Number	<b>3000</b>
	Shrouded	<b>Yes</b>
	Connector Type	<b>Header</b>
	Applies To	<b>Printed Circuit Board</b>

---

Configuration Features	Number of Positions	<b>5</b>
	Number of Rows	<b>1</b>
	Preloaded	<b>Yes</b>
	Keying	<b>X</b>
	Selectively Loaded	<b>No</b>

---

Electrical Characteristics	Operating Voltage	<b>600 VAC [ 600 VDC ]</b>
	UL Voltage Rating	<b>250 VAC [ 250 VDC ]</b>

---

Body Features	Header Type	<b>Shrouded</b>
	Sealable	<b>No</b>

---

Contact Features	Contact Plating Material	<b>Tin</b>
	Contact Current Rating (A)	<b>15</b>
	Contact Style	<b>Straight</b>
	Contact Transmits (Typical)	<b>Power, Signal (Data)</b>

Contact Termination (Typical)	Power/Signal (Data)
Shunts/Shorting Bars	<b>Without</b>
Contact Layout	<b>Inline</b>
Tail Plating Thickness	<b>2 µm [ 78.74 µin ]</b>
Multiple Contact Types	<b>Without</b>
Contact Type	<b>Tab</b>
Tail Plating Material	<b>Tin</b>

---

Termination Features	Termination Method to PC Board	<b>Through Hole - Solder</b>
----------------------	--------------------------------	------------------------------

---

Mechanical Attachment	Mating Alignment	<b>With</b>
	Mating Alignment Type	<b>Keyed</b>
	Mating Retention	<b>With</b>
	Mating Retention Type	<b>Latch</b>
	PCB Mount Retention	<b>With</b>
	PCB Mount Retention Type	<b>Retention Leg</b>
	Contact Retention	<b>Without</b>
	PCB Mount Alignment	<b>Without</b>
	Lock Type	<b>Latch</b>
Panel Mount Retention Type	<b>Screw Mount</b>	

---

Housing Features	Centerline	<b>5.08 mm [ .2 in ]</b>
	Housing Material	<b>Polyester GF</b>
	Housing Color	<b>Black</b>

---

Dimensions	PCB Thickness (Recommended)	<b>1.6 mm [ .063 in ]</b>
	Tail Length	<b>3.8 mm [ .149 in ]</b>
	Width	<b>9.35 mm [ .368 in ]</b>
	Length	<b>34.32 mm [ 1.35 in ]</b>
	Height	<b>21.6 mm [ .85 in ]</b>

---

Usage Conditions	Operating Temperature Range	<b>-55 – 105 °C [ -67 – 221 °F ]</b>
------------------	-----------------------------	--------------------------------------

---

Operation/Application	Assembly Integration Feature	<b>Without</b>
	Halogen Free	<b>Yes</b>
	For Use With	<b>Receptacle Housing</b>

---

Industry Standards	UL Flammability Rating	<b>UL 94V-0</b>
	CSA File Number	<b>LR7189</b>
	VDE Tested	<b>No</b>
	CSA Rating	<b>Certified</b>
	UL Rating	<b>Recognized</b>
	Agency/Standard	<b>CSA, UL</b>
	UL File Number	<b>E28476</b>




Packaging Features	Packaging Quantity	<b>14</b>
	Packaging Method	<b>Tube, Tube/Box</b>

Product Compliance

[Statement of Compliance PDF](#)

[VIEW ALL PRODUCT COMPLIANCE](#)

## CUSTOMERS ALSO BOUGHT

<p>RECTANGULAR BACKSHELLS &amp; CLAMPS</p>  <p><b>SCHELLENSET 8MM</b> 5-1106302-9</p> <p><a href="#">Save to List</a></p> <p><a href="#">Find Similar Products</a></p>	<p>STANDARD RECTANGULAR CONNECTORS</p>  <p><b>DYNAMIC D3200 HDR V ASSY 6P</b> 1-178140-5</p> <p><a href="#">Save to List</a></p> <p><a href="#">Find Similar Products</a></p>	<p>STANDARD RECTANGULAR CONNECTORS</p>  <p><b>DYNAMIC S/ROW HDR H 5P ASSY</b> 1-178295-3</p> <p><a href="#">Save to List</a></p> <p><a href="#">Find Similar Products</a></p>	<p>STANDARD RECTANGULAR CONNECTORS</p>  <p><b>DYNAMIC D3200 HDR V ASSY 3P</b> 1-178136-5</p> <p><a href="#">Save to List</a></p> <p><a href="#">Find Similar Products</a></p>
---	--	--	--