




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
A	RELEASED FOR PRODUCTION	12/17/01	MCCORMICK
B	ECN 3129: UPDATE DWG FORMAT	12/21/07	D.GRIFFIN
.	.	.	.
.	.	.	.



VIEW  
SCALE 2:1


2X UHF JACK



NOTES:

**MATERIAL:**  
BODY NICKEL PLATED BRASS  
INSULATOR: DELRIN

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONS ARE IN INCHES [mm]  
TOLERANCES TO BE:  
.X ±.1 [2.5] ANGLES ±2°  
.XX ±.01 [.25]  
.XXX ±.005 [.13]  
OVERALL CABLE LENGTH TOL:  
≤ 60 [1524] +3 [76.2] / -0  
> 60 [1524] +5% / -0%



APPROVALS	DATE
DRAWN BY MCCORMICK	12/05/01
CHECKED BY D.PARHAM	12/05/01
APPROVED BY R.CARRICK	12/05/01

CONFIGURATION DETAILS OF  
UNDIMENSIONED FEATURES  
MAY VARY

	45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		
	CATEGORY COAXIAL		
PRODUCT DESCRIPTION UHF JACK TO UHF JACK ADAPTOR			
SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. BA406Z	REV. <b>B</b>
SCALE: NONE   CAD FILE: BA406Z.SLDDRW			SHEET 1 OF 1