




FSN-11A-15 Product Details

[Share](#) [Print](#) [Email](#)


FSN-11A-15
(1-1437130-3)

TE Internal Number: 1-1437130-3

Active

FLEXSTRIP® Jumpers

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- 1.27 mm Centerline
- Nomex Insulation Material
- Insulation Length = 25.40 mm
- Pin Arrangement (Left) = A
- Pin Arrangement (Right) = A

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)
[Request Sample](#)
[Find Similar Products](#)
[Buy Product](#)

Documentation & Additional Information

<p>Product Drawings:</p> <ul style="list-style-type: none"> • flexstrip**jumpers (PDF, English) <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> • None Available <p>Product Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> • None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> • None Available <p>CAD Files:</p> <ul style="list-style-type: none"> • None Available 	<p>Additional Product Images:</p> <ul style="list-style-type: none"> • Product View • Product View <p>Related Products:</p> <ul style="list-style-type: none"> • Tooling
--	---

[List all Documents](#)

Feedback

Product Features (Please use the Product Drawing for all design activity)

<p>Electrical Characteristics:</p> <ul style="list-style-type: none"> • Current Rating (A) = 1.6 • Impedance (Ω) = 95 • Voltage Rating (VAC) = 200 <p>Dimensions:</p> <ul style="list-style-type: none"> • Insulation Length (mm [in]) = 25.40 [1.000] <p>Body Features:</p> <ul style="list-style-type: none"> • Insulation Material = Nomex <p>Housing Features:</p> <ul style="list-style-type: none"> • Centerline (mm [in]) = 1.27 [0.050] 	<p>Configuration Features:</p> <ul style="list-style-type: none"> • Pin Arrangement (Left) = A • Pin Arrangement (Right) = A • Number of Conductors = 15 <p>Industry Standards:</p> <ul style="list-style-type: none"> • RoHS/ELV Compliance = RoHS compliant, ELV compliant • Lead Free Solder Processes = Wave solder capable to 260°C, Wave solder capable to 240°C, Wave solder capable to 265°C • RoHS/ELV Compliance History = Always was RoHS compliant <p>Environmental:</p> <ul style="list-style-type: none"> • Operating Temperature (°C [°F]) = -40 - +125 [-40 - +257] <p>Other:</p> <ul style="list-style-type: none"> • Brand = TE Connectivity
---	--

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [AODA Accessibility Policy](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed



