

MODEL: BU-P2249-C-XX

Test Lead, BNC (M) on Each End, RG-58C/U



• Materials:

- Cable: Cable is RG 58C/U, complies to Mil-M17/155-00001 Jacket is non-contaminating PVC Center conductor is 20 AWG (19x33) tinned copper Shield is tinned copper braid (95% coverage)
- Male BNC: Body is tarnish resistant nickel plated brass Center Contact is Gold plated brass Insulator is PTFE
- Strain Relief is Molded PVC that is bonded to the BNC.
- Ratings: Impedance: 50 Ohms Capacitance per foot: 30.8 pf Power Loss/100 Ft. @ 1 MHz: .40 dB Hands free testing to 1400 VRMS Operating Temperature: -40°C to 85°C
- Ordering: The "XX" in the part number represents the length in Inches. Standard lengths are: 6", 12", 24", 36", 48", 60", 72", 120", 144" 180", 240", 300", and 600"
- RoHS Compliant, CE Compliant

Mueller Electric Company 1208 Massillon Rd. Ste. N-1500 Akron, OH 44306-4524