
Type TN Lab Grade Low TC Precision Film Resistors

Low TC of 5 ppm/°C, 10 ppm/°C, or 20 ppm/°C from 0°C to +70°C Tolerance of ±0.025%, ±0.05%, ±0.1%, to ±1%, Values from 1 Kohm to 1 Meg

Type TN Lab Grade Low TC Film Resistors were specifically developed for use in 0°C to +70°C applications which require a low temperature coefficient and a high degree of precision. These resistors combine the outstanding characteristics of Caddock's Tetrinox® resistance system with a space efficient, non-inductive, radial-lead design. These resistors are intended for precision analog designs where the system is not exposed to full military or space grade operating conditions. For full military or space grade operating conditions, we recommend Caddock's Type TK Low TC Precision Radial-Lead Film Resistors. For lab grade applications which require higher voltage ratings (up to 1,400 volts) and power ratings (up to 0.75 Watt), we recommend Caddock's Type TF Low TC Ultra-Precision Film Resistors.

The performance features of the Type TN Lab Grade Low TC Precision Film Resistors are:

- Low Temperature Coefficient 5, 10, or 20 ppm/°C.
- Ultra-Precision Tolerances from ±0.025% to ±1%.
- Resistance Range from 1 K to 1 Meg.
- Non-Inductive Design.
- Radial-Lead Design conserves board space.



Type TN Lab Grade Low TC Precision Film Resistors

Model	Temperature	Wattage	Max.	Dielect.	Resistance			
No.	Coefficient ppm/°C	@ +70°C	Working Voltage	Strength	Min.	Max.	Dimensions	Comments
TN130	5, 10, or 20	0.3	200	400	1 K	1 Meg	Ref. Case "A" Dwg.	
TN130V	5, 10, or 20	0.3	200	400	1 K	1 Meg	Ref. Case "C" Dwg.	With Standoff
TN137	5. 10. or 20	0.3	200	400	1 K	1 Mea	Ref. Case "B" Dwg.	

Temperature Coefficient Identification: 5 ppm/°C White Stripe; 10 ppm/°C No Stripe; 20 ppm/°C Green Stripe

ALL DIMENSIONS IN INCHES Case "A" Case "B" AND (MILLIMETERS) Model TN130 Model TN137 .095 ±.005 .290 → ±.010 .305 → $(2.41 \pm .13)$ ±.010 (7.37 (7.75 ±.26) .290 ±.010 1.50 +.125 -.000 1.50 +.125 (7.37 ±.26) +3.18) .025 ±.002 (38.10 ^{+3.18}) -0.00) (38.10 -0.00)(.64 ±.05) DIA., LEADWIRE OFFSET .012 (.31) FROM .200 ±.015 .150 ± .015 (5.08 ±.38) (CENTERED) $(3.81 \pm .38)$ CENTERLINE (CENTERED) Case "C" Model TN130V .095 ±.005 (2.41 ±.13) 290 **Ordering Information:** +.010(7.37 TN 130 - 10.0 K - 0.025% - 10 ppm/°C .030 ±.004 ±.26) .290 ±.010 10.0 K $(.76 \pm .10)$ $(7.37 \pm .26)$ Tolerance Model Number .250 ±.050 .025 ±.002 Resistor Value .090 (6.35 ±1.27) (.64 ±.05) DIA., (2.29)LEADWIRE .200 ±.015 OFFSET


012 (.31) FROM CENTERLINE

Specifications:

Resistance Tolerance: ±0.025%, ±0.05%, ±0.10% or ±1.0%.

Absolute Temperature Coefficient: 5ppm/°C, 10ppm/°C, or 20ppm/°C referenced to +25°C, ΔR taken at 0°C and +70°C.

Load Life Stability at +70°C:



Shelf Life (Typical): 25 ppm/year.

Storage Temperature: -55°C to +105°C.

Encapsulation: Transfer Molded.

Leadwire: Tinned Copper.

Derating Curve:

.105 ±.005

 $(2.67 \pm .13)$

 $.305 \pm .010$

(7.75 ±.26)

025 + 002

.64 ±.05) DIA. LEADWIRE


OFFSET

.012 (.31) FROM

CENTERLINE

Temperature

Coefficient



Applications Engineering 17271 North Umpqua Hwy. Roseburg, Oregon 97470-9422 Phone: (541) 496-0700 Fax: (541) 496-0408

(5.08 ±.38) (CENTERED)

ELECTRONICS. INC.

e-mail: caddock@caddock.com • web: www.caddock.com For Caddock Distributors listed by country see caddock.com/contact/dist.html

Sales and Corporate Office 1717 Chicago Avenue Riverside, California 92507-2364 Phone: (951) 788-1700 Fax: (951) 369-1151