




## FST-21A-15 Product Details



### FST-21A-15

(2-1437186-9)

TE Internal Number: 2-1437186-9

Active

### FLEXSTRIP® Jumpers

Always EU RoHS/ELV Compliant (Statement of Compliance)

#### Product Highlights:

- 2.54 mm Centerline
- Fluoropolymer Insulation Material
- Insulation Length = 25.40 mm
- Pin Arrangement (Left) = A
- Pin Arrangement (Right) = A

[View all Features](#)

### Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [FLEXSTRIP PIN CONFIGURATIONS, GENERIC](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Product Images:

- [Product View](#)
- [Product View](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

Feedback

### Product Features (Please use the Product Drawing for all design activity)

#### Electrical Characteristics:

- Current Rating (A) = 3
- Impedance ( $\Omega$ ) = 106
- Voltage Rating (VAC) = 300

#### Dimensions:

- [Insulation Length \(mm \[in\]\)](#) = 25.40 [1.000]

#### Body Features:

- [Insulation Material](#) = Fluoropolymer

#### Housing Features:

- [Centerline \(mm \[in\]\)](#) = 2.54 [0.100]

#### Configuration Features:

- [Pin Arrangement \(Left\)](#) = A
- [Pin Arrangement \(Right\)](#) = A
- [Number of Conductors](#) = 15

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 260°C, Wave solder capable to 240°C, Wave solder capable to 265°C
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

#### Environmental:

- [Operating Temperature \(°C \[°F\]\)](#) = -40 - +150 [-40 - +302]

#### Other:

- [Brand](#) = TE Connectivity

### Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)
- [AODA Accessibility Policy](#)

### Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

### Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

### Keep Me Informed



