



ENGLISH

Datasheet

Stock No: 404-522

RS Pro 0.89mm Transparent PTFE Cable Sleeve



Product Details

PTFE Sleevings

Clear PTFE sleeving, used in areas of high temperature, or where avoidance of contamination is desired. PTFE has excellent physical and chemical properties. The chemical resistance is very wide-ranging, with few limitations.

Tensile Strength: 26 → 36 MPa

Impact resistance: 185J/m (23°C) → 107J/m (-54°C)

Specific Gravity: 2.14 → 2.21 g/cm³

Elongation: min 200%

Coefficient of Friction (dynamic): 0.1

Note

This product is Compliant with ROHS 2002/95/EC the Restriction of use of certain Hazardous Substances in electrical and electronic equipment. The product adheres to AMS 3655A.

Standard Sleevings



ENGLISH

Specifications:

Sleeve Diameter	0.89mm
Colour	Transparent
Material	PTFE
Sleeve Length	5m
Minimum Cable Diameter	0.89mm
Minimum Operating Temperature	-65°C
Maximum Operating Temperature	+250°C
Wall Thickness	0.3mm