

Proportional Hall effect thumbsticks



The TS Series Thumbstick is a proportional two axes joystick in a miniature package. Featuring non-contacting Hall effect technology for long life performance, the TS Series Thumbstick is available with multiple linear output options including single and dual (redundant) outputs. It is similar in size and operation to "gamepad" controls, but in a rugged industrial package. Typical applications include pendant and remote controls as well as joystick handle and arm rest integration.



KEY FEATURES


- ☐ 1 or 2 axes
- USB outputs available
- Non-contact Hall effect technology
- Submersible to 1m (3.28ft) per IP68
- Pressure washable to IP69K
- Redundant outputs available
- ☐ Rear or drop-in mounting available





Proportional Hall effect thumbsticks

OPTION SELECTION



MECHANICAL (FOR X, Y AXES)

Operating Force - 3.1N±0.5N (0.70lbf±0.11lbf)⁴

Maximum Vertical Load - 200N (45lbf)⁴

Maximum Horizontal Load - 150N (33.7lbf)⁴

Mechanical Angle of Movement - 50°

Expected Life - 1 million cycles

Mass/weight - 18.25g ± 5.0g (0.64oz±0.18oz)

Lever Action (Centering) - Spring centering

ENVIRONMENTAL

 Operating Temperature
 -40°C to +85°C (-40°F to +185°F)

 Storage Temperature
 -40°C to +85°C (-40°F to +185°F)

 Sealing
 IP68, IP69K⁵

 EMC Immunity Level
 EN61000-4-3

 EMC Emissions Level
 EN61000-6-3:2001

 ESD
 EN61000-4-2

ELECTRICAL SENSOR

 Resolution
 1.22mV

 Supply Voltage Range
 5.00V±0.01V

 Reverse Polarity Max
 -10V

 Overvoltage Max
 20V

 Output Impedance
 2Ω

 Return to Center Voltage Tolerance
 ±200mV initial

NOTES:



Mounting accessories.


Standard hardware includes:


- For the Drop-in option 4 push in connectors, drop-in bezel and an O-ring.
- For the Rear mount option: 4x1/2 FH SS Phil Screws and a rear mount bezel.
- 1-1 Wires are thick, robust, and best suited for stand alone applications.
- 1-2 Wires are thin and best suited for tightly constrained wire routing.
- 2 Contact factory for PWM configuration.
- Only available on dual output.
- 4 Force applied to the top of the castle cap.
- 5 All options are IP68 and IP69K rated, however Drop-in mounting does not prevent panel ingress.
- All values are nominal

Note: The company reserves the right to change specifications without notice.

Proportional Hall effect thumbsticks

DIMENSIONAL DRAWINGS






MOUNTING OPTIONS DROP-IN OPTION CUTOUT DIMENSIONS REAR MOUNT OPTION CUTOUT DIMENSIONS 4 x 1/2 FH SS PHIL SCREW Ø2.87 (0.113) 4 x PUSH IN CONNECTORS Ø2.87 (0.113) Ø25.65 (1.01) CHAMFERED FOR #4 FLAT HEAD SCREW (4 PLACES) 24.64 (0.97) 24.64 (0.97) Φ 1.00 (0.04) x 45° CHAMFER O-RING REAR MOUNT BEZEL 24.64 (0.97) 24.64 (0.97) Note: Maximum panel thickness is 2.032mm (0.08in)


Note: Dimensions are in mm/(inch)



Proportional Hall effect thumbsticks

CONFIGURATION OPTIONS





Proportional Hall effect thumbsticks

CONFIGURATION OPTIONS - continued

ADDITIONAL OUTPUT OPTIONS

PLUG-AND-PLAY SOLUTIONS:

USB

Featuring USB 1.1 HID compliant interface, CH Products' USB joysticks are recognized as standard HID "game controller" devices. Adhering to the HID specification, CH Products' USB joysticks are plug-and-play with most versions of Windows and Linux. Joystick button and axes assignments are dependent upon the controlled application.

FEATURES


- USB 1.1 HID compliant "game controller" device
- Easy to install and operate
- Functions determined by controlled application

SUPPLIED WIRING

USB: USB Male Type A Connector with overmolded cable (Optional ruggedized military connectors are available.)



USB Male Type A Connector



Proportional Hall effect thumbsticks

CONFIGURATION OPTIONS

ADDITIONAL OUTPUT OPTIONS

JOYBALL (CURSOR EMULATION)

The Joyball option converts multi-axis joystick ouput into a mouse, trackball, or cursor control device. The joystick's internal microprocessor converts absolute axis position into a curser velocity, which is translated as a relative trackball or mouse position. Supported protocols: USB.

APPLICATIONS

The Joyball option is ideal for vehicle applications subjected to dirt and high vibration which make operating a traditional cursor control device difficult. The Joyball option is widely used in shipboard and military applications.

FEATURES

- HID compliant "pointing device"
- Plug-and-play with USB option
- Ideal for marine GPS and navigation

SUPPLIED WIRING

USB: USB Male Type A Connector with overmolded cable.

