

115 Amps 600 Volts AC/DC

marathon™ Special Products

Product Data Sheet

141X200

Replace "x" with 1, 2, 3 or 4 for number of poles

Power Terminal Block

Wire Range

Line: (1) #2 - #14 AWGLoad: (1) #10 - 32 Screw

Electrical Ratings

- 115 Amps
- 600V per UL 1059 & CSA 22.2 No.158, class B & C requirements
- SCCR of 10,000 A (default for terminal blocks).
- CU7AL 75°C connector terminal rating with copper or aluminum wire
- Factory & Field Wiring

Agency Compliance

- UR UL Recognized Terminal Block, Evaluated to UL 1059, File No.XCFR2.E62806
- CSA certifed to C22.2 No. 158, File No. LR19766 (wire classes B & C only)
- CE compliant to IEC 60947-7-1

Material Information

- Insulator base:
 - Thermoplastic
 - Flammability rating of insulator base UL94V0
 - Insulator base temperature rating: -40°C to 125°C (UL RTI)
- Connector: aluminum, tin plated
- Terminal screws: steel, nickel plated
- Connector mounting screws: steel, zinc plated
- RoHS compliant

A Regal Brand





Termination Specifications

Line Side	Wire Size (CU Stranded)	Torque	Wires / Terminal	Wire Class (UL) 1
	2	5.6 N·m (50 lbf·in)	1	В, С
	4 - 6	5.1 N·m (45 lbf·in)	1	B, C, G, H, I (DLO)
	8	4.5 N·m (40 lbf·in)	1	B, C, G, H, I (DLO)
	10 - 14	4 N·m (35 lbf·in)	1	B, C, I (DLO)

Aluminum wire range: 2 - 12 AWG
 Solid copper wire range: 10 - 14 AWG
 Wire strip length: 9/16 in. (14mm)
 Terminal screw drive: slotted

Load Side	Termination Type	Torque	Tap Depth	Maximum Lug Width
	Listed lugs anchored with 10 - 32 screws	2.8 N·m (25 lbf·in)	0.16" (4mm)	0.50" (12.7mm)

- For use with conductors prepared with listed connectors such as single hole compression/crimp lugs or listed ring, fork or spade terminals.
- Conductor size, ampacity, temperature rating and type are dictated by the ratings of the listed lugs utilized and applicable code requirements.

¹ For information on copper stranded wire classes please visit: http://www.marathonsp.com/flexible-stranded-wire.php



Installation & Accessories

- Mounting (Panel):
 - For use with #10 fastener.
 - Recommended mounting torque: 25-30 lbf·in (2.8 3.4 N·m).
- Covers:
 - Snap-on covers available upon request
 - Catalog Number: CC141x (replace "x" with number of poles)
 - Covers are semiclear polycarbonate
 - Accessory covers are not intended to provide insulation for electrical spacings.

Drawing

