





# ES-313 ETHERNET TO SERIAL DEVICE SERVER Ethernet 2 Port RS422/485

# CONNECT, CONFIGURE, CONTROL YOUR SERIAL DEVICES



#### **Features**

- 2 port RS422/485
- Max baud rate 1,000,000 1 MegaBaud
- 10/100Base TX Ethernet port
- User friendly interface, simple to use, powerful in operation
- Web configuration and RFC2217 compliant interface
- IP-30 rated enclosure
- LED status indication
- Optional DIN rail mounting kit
- Serial Port Tunneling (individually configurable) allows serial cable replacement over any distance, no software required
- Power supply included with screw fix connector (5-30V DC)
- Simple operation for each and every operating system!
- Lifetime Warranty
- Lifetime Support





# Description


Ethernet to Serial device server providing access to two RS422/485 serial ports. Data transfer rates up to 1,000,000 baud, coupled with 1Mbit/s line drivers deliver uncompromising performance. Our ES range provides simple instant networked serial ports. RS485 - 1 twisted pair - half duplex configuration with autogating provides trouble free data transmission due to automatic control of data direction. A web interface allows secure configuration and control of the serial ports over a local network or the internet using any browser. For Windows our in-house designed 32 bit and 64 bit driver gives you local COM ports, retaining existing software applications and allowing you to connect across your network to remote devices just as if they were attached locally. Serial Port Tunnelling individually configurable allows serial cable replacement over any distance, no software required. You can access the device via TCP/IP sockets from any networked device like an Android tablet, PC or phone. On Windows OS TCP/IP sockets are handled by the Winsock API, this will differ on other OSs.

**Windows Users** - Our software drivers gives you local COM ports, allowing you to retain your existing software applications and connect to your devices over the network. COM Port can be assigned from COM1 to COM255 and the Brainboxes Ethernet to serial device remembers your COM Port assignment on reboots.

Web Interface Users (Linux/Apple OS/Android) - Alternatively access the device via TCP/IP socket from any networked device. Configure options via web interface.


Extend your reach! Remote serial devices with local control. With Brainboxes industry renowned Lifetime Warranty and Lifetime Support!

#### **Example Application**





# **Box Information**



LED Information		
Status LED	Green	Device Ready
	Flashing Yellow	Changing Settings
	Flashing between Red & Green	Querying IP
	Flashing Green/Red	User performing Hard Reset
	Flashing between Green & Red/Yellow	IP address diagnostic
	Flashing between Green & Yellow	Initialization diagnostic
Serial Port LEDs	Green light on	Port Open
	Flashing Green	Data RX / TX
Network LED	Green light on	Link Established
	Flashing Green	Data RX / TX

**Port** 

**Ports** 2 port RS422/485

**Connector** DB9 Connector - 9 Pin Male

**Power Input** 5 - 30V DC input, reverse polarity protected

**Power Consumption** 1.06W Typical, 2.6W Max

# **ES-313 Ethernet 2 Port RS422/485**



## Port Settings - RS422/485

**Baud Rate** From 110 - 1,000,000 1 MegaBaud

**Data Bits** 5,6,7 or 8

Parity Odd, Even, None, Mark or Space

Stop Bits 1 or 2

Flow Control RTS/CTS, XON/XOFF

**Tx/Rx Modes RS422 Standard:** RS422 allows one transmitter and up to 10 receivers with data transmitter rates up to 10

megabits per second for distances up to 40 feet and up to 100 Kilobits per second for distances up to 4,000

feet (1219 metres).

To achieve good long distance noise immunity, 2 wires are used to carry each signal, configured as a twisted pair of cables. The TXD pair and RXD pair are used to carry the data whilst the RTS pair and CTS pair lines are used for handshaking. Thus 2 twisted pairs are used without handshaking and 4 twisted pair cable is used with handshaking both these schemes allow full duplex data communications.

**RS485 Standard:** RS485, based on the RS422 standard allows up to 32 driver/receivers pairs on a standard load or 128 low load devices per port can be connected. Whilst only one of these should be transmitting data at any time, the rest can all simultaneously listen to the data. Handshaking is performed by software protocol. Two twisted pairs form a full duplex system.

Often only one twisted pair cable is used as the TXD and RXD lines are tied together; this is known as half duplex mode. Brainboxes RS422/485 products implement a state of the art hardware autogating circuit ensuring error free communications in half duplex configurations.

## **Port Settings - Ethernet**

**Data Rate** 10/100 Mega bits/second

Cabling Normal / Crossover auto-sensing (Auto-MDIX)

#### **Environmental**

**Operating Temperature** 0 to 55°c **Storage Temperature** -20 to 85°c

**Ambient Relative Humidity** 5 to 95% (non-condensing)

**Housing** IP-30 rated case

#### **Software**

Network Protocols ICMP, IP, TCP, DHCP, BOOTP, Telnet, HTTP, RFC2217

**Configuration Options** Windows Utility, Web Interface

OS Compatibility Microsoft Windows 7 32 bit 64 bit Editions / Windows Server 2008 32 bit 64 bit Editions / Windows Vista

32 bit 64 bit Editions / Windows Server 2003 32 bit 64 bit Editions / Windows XP 32 bit 64 bit Editions /

Microsoft Windows 2000 /Fully RFC2217 compliant / Interface for other OS's & Linux

**Connection to Network** Ethernet 10BaseT / 100BaseTX

# **Approvals**

Industry Approvals AEO C-TPAT Microsoft Certified Gold Partner WEEE RoHS EMC: CE TAA

Microsoft ApprovalsMicrosoft Certified Gold PartnerMicrosoft Signed DriversWindows 7 32 bit 64 bit Editions

















# **ES-313 Ethernet 2 Port RS422/485**



#### **Packing Information**

Packaging Installation CD including manual, Microsoft signed drivers & utilities

**Device** Ethernet 2 Port RS422/485

Accessory Items Global Power Supply - PW-800 (included), DIN-Rail Mounting Kit - MK-048

Packaged Weight 0.467 kg, 16.47 ounces

Packaged Dims 200x135x80 mm, 7.9x5.3x3.1 inches

## **Product Support**

Warranty Lifetime - online registration required

**Support** Lifetime Web, Email and Phone Support from fully qualified, friendly staff who

work in and alongside the Product Development Team



#### **Additional Information**

**OEM option** Available for bulk buy OEM

Made In Manufactured in the UK by Brainboxes Winner 2005 European Electronics Industry Awards

'Manufacturer of the Year'

**Customisable** Brainboxes operate a 'Perfect Fit Custom Design' policy for volume users. More info:

sales@brainboxes.com

# **Accessory Items**

# ORDER CODE - DIN-Rail Mounting Kit - MK-048



#### ORDER CODE - Additional Global Power Supply - PW-800



Brainboxes Ethernet to Serial Range