

MAXRACK™ OPEN FRAME SYSTEM



INDUSTRY STANDARDS

UL 1863 Listed; File Number E230874 cUL Listed per CSA C22.2 No. 182.4; File No. E230874

Cisco developer registered EIA 310-D

APPLICATION

MAXRACK™ is used for mounting and securing 19- or 23-in. rack equipment that is used in data centers, telecommunication rooms and other locations. These open frame racks are ideal for highdensity cabling applications. MAXRACK also supports the cabling and cooling needs of large core switches (CISCO Catalyst 6509 / 6513, NEXUS 7010 and NEXUS 7018) by using the combination air baffle/vertical cable manager accessory. MAXRACK, with its vast features, supports many diverse applications.

FEATURES

- Rack can be assembled to accommodate either 19- or 23-in. rack equipment
- Racks can be ganged to create rows for high density applications
- 19-in. configuration equals typical tile width of 24 in.
- Flat package to allow easy shipping and handling to job site
- Press-in nuts enable single-side easy assembly
- All structural members are grounded by special grounding and bonding washers
- Top has integrated waterfall, which ensures proper cable radius is achieved
- Top and top bracket support accomodate parallel or
- perpendicular ladder or basket tray mounting applications

 Channel uprights provided with hole patterns to support various cable management devices
- All RU positions marked with white lettering on front and rear column members
- Easy-to-follow complete installation instructions included
- Upright channels tapped 12-24 holes per EIA Universal pattern standards
- Multiple paint-free grounding points per UL double-lugged standards
- Rack accommodates vertical cable manager accessories

SPECIFICATIONS

- Top and uprights made of multi-formed .125-in. aluminum
- Base angles made of extruded aluminum
- White RŬ-marked uprights per EIA standards
- Tapped 12-24 holes per EIA Universal pattern standards

LOAD RATING

Static maximum load is 2500 lbs/1134 kg.

ACCESSORIES

Vertical Cable Managers Blanking Panels Grounding kits PDUs Shelves


BULLETIN: DMAX

Standard Product MAXRACK Open Frame System

Catalog Number	AxBxC in.	AxBxC mm	Rack Units	G (in.)	G (mm)	K (in.)	K (mm)	
M846B45	86.13 x 24.00 x 16.50	2188 x 610 x 419	45	14.00	356	6.50	165	
M8410B45	86.13 x 24.00 x 20.50	2188 x 610 x 521	45	18.00	457	10.50	267	
M8416B45	86.13 x 24.00 x 26.25	2188 x 610 x 667	45	23.75	603	16.25	413	
M8432B45	86.13 x 24.00 x 41.75	2188 x 610 x 1060	45	39.25	997	31.75	806	
M966B51	98.13 x 24.00 x 16.50	2493 x 610 x 419	51	14.00	356	6.50	165	
M9610B51	98.13 x 24.00 x 20.50	2493 x 610 x 521	51	18.00	457	10.50	267	
M9616B51	98.13 x 24.00 x 26.25	2493 x 610 x 667	51	23.75	603	16.25	413	
M9632B51	98.13 x 24.00 x 41.75	2493 x 610 x 1060	51	39.25	997	31.75	806	










$\begin{array}{l} \mathsf{MAXRACK^{\mathsf{IM}}} \ \mathsf{AIR} \ \mathsf{BAFFLE} \ \mathsf{AND} \ \mathsf{CABLE} \ \mathsf{MANAGERS} \ \mathsf{FOR} \\ \mathsf{CISCO} \ \mathsf{SWITCH} \end{array}$



MAXRACK™ Air baffle and Vertical Cable Manager accessory kits ensure CISCO switch compliance. They provide the required cold air access and provisions for high-density cabling. Baffles and cable manager uprights made of aluminum; supporting fingers made of composite. Finish is RAL 9005 black light-textured, low-gloss polyester powder paint.

Cisco developer registered.

BULLETIN: DMAX



Standard Product MAXRACK Air Baffle and Cable Managers for CISCO Switch

Catalog Number	AxBxC in./mm	Use with CISCO Switch	Use with MAXRACK
M84D12	84.13 x 12.00 x 23.68	Catalyst 6509/6513	M8416B45
	2137 x 305 x 601		
M84D18	84.13 x 18.00 x 39.37	NEXUS 7018	M8432B45
	2137 x 457 x 1000		
M96D12	96.13 x 12.00 x 23.68	Catalyst 6509/6513	M9616B45
	2442 x 305 x 601		
M96D18	96.13 x 18.00 x 39.37	NEXUS 7018	M9632B45
	2442 x 457 x 1000		



MAXRACK™ DUST COVER



Dust Cover fits over the top of the base angles, inside the uprights. Covers are made of aluminum with matching RAL 9005 black light-textured, low-gloss polyester powder paint.

BULLETIN: DMAX

Standard Product MAXRACK Dust Cover

Catalog Number	AxBxC in./mm	Fits MAXRACK Depth
MDC6	1.00 x 17.95 x 7.33 25 x 456 x 186	6-in.
MDC10	1.00 x 17.95 x 11.33 25 x 456 x 288	10-in.
MDC16	1.00 x 17.95 x 17.08 25 x 456 x 434	16-in.
MDC32	1.00 x 17.95 x 32.58 25 x 456 x 828	32-in.