




# P Series

## SD Memory Card, Industrial MLC Model

■ **Product Outline**

P series are SDHC memory cards adopting built-in industrial MLC type NAND flash memory and is suitable for industrial applications. They are adequate for the applications such as automotive use, security camera, factory automation, broadcast equipment, handy terminal, servers etc. They are formatted complying with SD card specification.

■ **Product Specification** (specifications and appearances may be changed without notice.)


Image Part Number		4GB	8GB	16GB
				
		RP-SDP04G	RP-SDP08G	RP-SDP16G
<b>Capacity</b>	Available user data area capacity <sup>1</sup>	3,955,195,904 byte	7,998,504,960 byte	16,194,174,976 byte
<b>Compliant Specification</b>	SD Physical Specification	Ver. 3.01		
	SD Speed Class	CLASS 4		
	UHS Speed Grade	not supported		
	Speed mode	High Speed, Default Speed		
<b>Backside mark</b>	Control code	D0BC		
<b>Read/Write Performance (up to)</b>	Read	22 MB/s (High Speed)		
	Write	12 MB/s (High Speed)		
<b>Absolute Ratings</b>	Supply Voltage	-0.3V to 4.6V (Min - Max)		
	Input Voltage	-0.3V to +0.3VDD (Min - Max)		
	Output Voltage	-0.3V to +0.3VDD (Min - Max)		
	Output Current	-24mA to 24 mA (Min - Max)		
<b>Environmental Specification</b>	Operating Temperature	-40°C to 85°C		
	Storage Temperature	-40°C to 85°C		
	Humidity	5% to 95%		
	Vibration	15 Gpp		
	Shock	1000 G		
	Mating Cycles	10,000 cycles		

<sup>1</sup> Free area capacity after formatted.

Absolute maximum ratings are the values of limitation, which do not damage the card. Those values do not define the operational range.

■ Products comply with EU RoHS directives.

■ Laser Mark on the Back-side (example; 4GB)



“0000” Control Code (Defined as product parts combination)  
 “00YM0000000” Serial Number  
   Y Last digit of Manufacture year  
   M Manufacture month (January->A, February->B, )  
 “4GB” Card Capacity  
 “P” Series name  
 “MADE IN JAPAN” Country of origin

■ System Reliability

- a. Powerful error detect and corrective function
- b. Static wear leveling
- c. Data recovery at power failure in writing
- d. Automatic refresh function to prevent uncorrectable error
- e. Bad block management

■ Notice and Caution

In applications where very unique product quality or reliability is and failure or malfunction of the products may directly threaten life or injury for the special usage (aeronautic or cosmic usage, military usage, combustion machine, life support applications or safety applications), please counsel with our contacts in advance. Write frequency and storage temperature will affect data retention time. Please make a backup for important data.

■ Warranty

If the product cannot be used because of failure which is determined as defect in design or in production of the product, it is replaced by same product or equivalent one within 12 months from the delivery date of product.