

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ Jumper Bars

General Information

| | |
|-------------------------------|--|
| Extended Product Type: | JB6-10 |
| Product ID: | 1SNK906310R0000 |
| EAN: | 3472599097650 |
| Catalog Description: | JB6-10 Jumper Bar - Orange |
| Long Description: | Facilitate & secure your jumper bar assembly process: - Screwless mounting, - Pre-cut poles for alternated jumpering between terminal blocks, - Insulated, - Positive locking, - Perfectly adapted to low level electrical contact (20mA, 50mV). |

Ordering

| | |
|--------------------------------|----------|
| Color: | Orange |
| Minimum Order Quantity: | 20 piece |
| Customs Tariff Number: | 85369010 |

Popular Downloads

| | |
|---|-----------------|
| Data Sheet, Technical Information: | 1SNK160029D0201 |
| Instructions and Manuals: | 1SNK160027C0201 |

Dimensions

| | |
|------------------------------------|---------|
| Product Net Width: | 6 mm |
| Product Net Height: | 57 mm |
| Product Net Length: | 26.8 mm |
| Product Net Depth / Length: | 26.8 mm |
| Product Net Weight: | 7.4 g |

Technical

| | |
|--|-------------------|
| Spacing: | 6 mm |
| Function: | Jumper Bars |
| Rated Current (I_n): | Main Circuit 41 A |
| Rated Short-time Withstand Current (I_{cw}): | for 1 s 720 A |
| Rated Voltage (U_r): | 1000 V |
| Rated Impulse Withstand Voltage (U_{imp}): | 8000 V |
| Dielectric Test Voltage: | 2200 V |

| | |
|------------------------------|--|
| Pollution Degree: | 3 |
| Power Loss: | 1.3 W |
| Degree of Protection: | acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20 |
| Insulation Material: | Polyamide |
| Suitable For: | ZDK4-22 ZDS4-22-R1 ZK2.5-SF ZK2.5-SF-R ZK2.5-S-R1 ZK4 ZK4-3P ZK4-4P ZK4-PE ZK4-PE-3P ZK4-PE-4P ZS4-PE-R2 ZS4-R2 ZS4-SF ZS4-SF-R ZS4-SF-T ZS4-SP-R1 ZS4-SP-T2-R1 ZS4-S-R1 ZS4-S-R2 ZS4-S-T-R1 ZS4-T3-R1 ZS6 ZS6-3S ZS6-3S-PE ZS6-4S ZS6-4S-PE ZS6-D1 ZS6-D1-PE Z |

Technical UL/CSA

| | |
|--|--------------------|
| Maximum Operating Voltage UL/CSA: | Main Circuit 600 V |
| Flammability According to UL94: | V0 |

Environmental

| | |
|--|---|
| Ambient Air Temperature: | Operation -55 ... +110 °C Storage -55 ... +110 °C |
| Resistance to Vibrations acc. to IEC 60068-2-6: | Compliant |
| RoHS Status: | Following EU Directive 2002/95/EC August 18, 2005 and amendment |

Certificates and Declarations (Document Number)

| | |
|----------------------------------|-----------------|
| ATEX Certificate: | 1SND162004A1708 |
| CB Certificate: | 1SND161025A0203 |
| Instructions and Manuals: | 1SNK160027C0201 |
| RoHS Information: | 1SND230499F0202 |

Classifications

| | |
|------------------------------------|---|
| Object Classification Code: | X |
| E-number: | 2925376 |
| ETIM 4: | EC000489 - Cross-connector for terminal block |
| ETIM 5: | EC000489 - Cross-connector for terminal block |
| ETIM 6: | EC000489 - Cross-connector for terminal block |

Container Information

| | |
|--|---------------|
| Package Level 1 Units: | 20 piece |
| Package Level 1 Width: | 50 mm |
| Package Level 1 Depth / Length: | 117 mm |
| Package Level 1 Height: | 50 mm |
| Package Level 1 Gross Weight: | 0.148 kg |
| Package Level 1 EAN: | 3472599097650 |
| Package Level 2 Units: | 600 piece |
| Package Level 3 Units: | 3000 piece |

