



SNA Terminal Blocks T&B Catalog Number:

UPC Number:
Status:
Description:

020640405
66201901713
Active

Violet feed through terminal block with 6 mm spacing and 30 amp UL rated current with screw clamp connection

Features

- Self-locking clamp design prevents screw loosening
- Funneled side entry for up to two ferruled or non-ferruled solid or stranded wires
- Touch-safe IP20 protection
- High quality steel offers a very high over-torque resistance
- Compensates for the flattening of copper under contact pressure
- Clamp is protected from harsh environments by a zinc bichromate surface treatment

Application

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

General

Style	Feed Through
Color	Violet
Mounting	DIN 3
Series	M 4/6
Connection Technology	Screw Clamp
UL Wire Range (AWG)	22-10
Rated IEC Wire Range (Solid) (mm ²)	0.2 - 4
Rated IEC Wire Range (Stranded) (mm ²)	0.22 - 4

Dimension Information

L x W x H (mm)	44.5 x 6 x 53
Spacing (mm)	6
L x W x H (in)	1.75 x .238 x 2.09
Spacing (inches)	0.238

Specifications

UL Current (Amps)	30
UL Voltage (VAC)	600

Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	2000
T&B Sold in UOM	Each
T&B Weight Per UOM	0.02 lbs. per 100

Certifications

Approvals	UL
-----------	----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com