

Rittal – The System.

Faster – better – worldwide.

**► Catalog 33
North American Edition 2012**

500

Rittal. Power and Vision!

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



Interior installation

System lights



Mounting kit magnet

For reliable adhesion on all carbon steel surfaces.

Packs of	Part No.
2	4140.000

LED system light in 24 V DC version

- Max. EMC capacity
- Safe, economical and low maintenance
- Integral through-wiring
- Universal attachment options
- Vertically hinged light cone

Material:

- Light body: Extruded aluminum
- Light cover: Polycarbonate (halogen-free)
- Light ends: PC-ABS

Color:

Similar to RAL 7035

Protection rating:

IP 20 to IEC 60 529

Configuration:

Light with clip, screw mounting kits, assembly parts

Also required:

- LED connection cable, see page 693 or
- Door-operated switch with LED connection cable, see page 693

Accessories:

- Mounting kit magnet, see page 692
- Door operated switch with LED connection cable, see page 693
- LED connection cable, see page 693
- Adaptor power pack, see page 693

Note:

Only intended for use in enclosures and sealed cases. When using on customer-supplied power packs, it is important to obtain the requisite approvals depending on the application.

Part No.	4140.810	4140.820	4140.830	4140.840
Rated voltage	24 V DC (± 10%)			
No. of LEDs	10	20	30	40
Protection rating	III (SELV)			
Width (B1) inches (mm)	9 (230)	13 (330)	17 (430)	21 (530)
Mounting distance CLIP (B2) inches (mm)	7 (175)	11 (275)	15 (375)	19 (475)
Mounting distance, screw attachment (B3) inches (mm)	10 (250)	14 (350)	18 (450)	22 (550)
Rated current (A) ¹⁾	0.04	0.08	0.12	0.16
Circuit-breakers	Integral on/off/door-operated switch mode			

¹⁾Maximum buying up to a total rated current strength of 2 amps.

