



RECTANGULAR CONNECTOR HARDWARE



Active

PRODUCT DRAWING
English

3D PDF

TE CONNECTIVITY (TE)

JACKSCREW-MALE-SPEC.

AMP | SP

201388-1

TE Internal Number: 201388-1

Always EU RoHS/ELV Compliant

Hardware Type **Jackscrew Kit**

Jackscrew Type **Turnable**

Jackscrew Style **Short-Short**

Product Drawings

JACKSCREW KIT, UNASSEMBLED, MALE, M SERIES

PDF (TIFF AVAILABLE)
English

JACKSCREW KIT, UNASSEMBLED, MALE, M SERIES

PDF (TIFF AVAILABLE)
English

CAD Files

Customer View Model

3D_IGS.ZIP
English

Customer View Model

3D_STP.ZIP
English

Customer View Model

2D_DXF.ZIP
English

3D PDF

PDF
English

Catalog Pages/Data Sheets

M_SERIES_PIN_AND_SOCKET_CONNECTORS

PDF
English

Instruction Sheets

Instruction Sheet (U.S.)

AMP Jack Screw Selection Chart For Series "M", COAXICON And Miniature

PDF
English

AMP Jack Screw Selection Chart For Series "M", COAXICON And Miniature

TIF
English

AMP TURNABLE JACK SCREW SPECIFICATIONS AND ASSEMBLY INSTRUCTIONS

PDF
English

AMP TURNABLE JACK SCREW SPECIFICATIONS AND ASSEMBLY INSTRUCTIONS

INSTRUCTIONS

TIF
English

FLEXIBLE FLAT CABLE (FFC) JACKSCREW ASSEMBLIES AND LATCH-TYPE HAR

PDF
English

FLEXIBLE FLAT CABLE (FFC) JACKSCREW ASSEMBLIES AND LATCH-TYPE HAR

TIF
English

75 And 104 Position Series "M" Connectors And Accessories

PDF
English

75 And 104 Position Series "M" Connectors And Accessories

TIF
English

21 & 26 POSITION SERIES "M" CONNECTORS AND ACCESSORIES

PDF
English

21 & 26 POSITION SERIES "M" CONNECTORS AND ACCESSORIES

TIF
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features	Thread Size	6-32 [M3.5 x .6]
	Strain Relief	Without
	Product Type	Hardware
Body Features	Thread Lead Type	Double
	Material	Stainless Steel, Zinc Alloy
Mechanical Attachment	Hardware Type	Jackscrew Kit
	Jackscrew Type	Turnable
	Jackscrew Style	Short-Short
	Mounting Hardware	Jackscrew Tip Male, Spirol Pin and Washer
	Jackscrew Material	Zinc Alloy
	Jackscrew Finish	Clear Chromate
Dimensions	Height	4.75 mm [.187 in]
	Length	29.97 mm [1.1799 in]
	Width	4.75 mm [.187 in]
Operation/Application	For Use With	15,16,and 42-Position Mixed Connectors, 20 and 28-Position High Voltage Connectors, 6, 14, 20, 26, 34, 41, 50, 75 and 104 Position Posted Connectors, 6, 14, 20, 26, 34, 41, 50, 75 and 104 Position Standard Connectors, Standard & Posted Connectors

Packaging Features

Packaging Quantity

100

Packaging Method

Bag

Other

Comment

Two required., Use turnable jackscrews on mating housings when mating to grounding block.

Product Compliance

[Statement of Compliance](#)
PDF

[VIEW ALL PRODUCT COMPLIANCE](#)