

## 125-800 W Fan Heater with Thermostat *FLH Series*



### Features

- Designed to prevent condensation or maintain minimum temperature in enclosures.
- Built in Thermostat. (-18 C to +38 C) (0 F to +100 F)
- Fan Auto/On switch with pilot light for Heat On indication
- 20 CFM airflow
- High temperature safety protection
- Aluminum alloy outer casing
- Connection via terminal block.



| Part No.            | Watts     | Voltage   | Hz    | Overall Dimensions     | Ship Wt. |
|---------------------|-----------|-----------|-------|------------------------|----------|
|                     |           |           |       | Height x Width x Depth | lbs      |
| <b>FLHTF125A115</b> | 125 W     | 120 V     | 60    | 5.5" x 4.0" x 5.3"     | 2.2      |
| <b>FLHTF125A230</b> | 105/125 W | 220/240 V | 50/60 | 5.5" x 4.0" x 5.3"     | 2.2      |
| <b>FLHTF200A115</b> | 200 W     | 120 V     | 60    | 5.5" x 4.0" x 5.3"     | 2.2      |
| <b>FLHTF200A230</b> | 165/200 W | 220/240 V | 50/60 | 5.5" x 4.0" x 5.3"     | 2.2      |
| <b>FLHTF400A115</b> | 400 W     | 120 V     | 60    | 7.5" x 4.0" x 5.3"     | 3        |
| <b>FLHTF400A230</b> | 335/400 W | 220/240 V | 50/60 | 7.5" x 4.0" x 5.3"     | 3        |
| <b>FLHTF800A115</b> | 800 W     | 120 V     | 60    | 7.5" x 4.0" x 5.3"     | 3        |
| <b>FLHTF800A230</b> | 670/800 W | 220/240 V | 50/60 | 7.5" x 4.0" x 5.3"     | 3        |

*Data subject to change without notice*