

MULTIPLE CONFIGURATION PCB HEADERS & RECEPTACLES





J 3D PDF

TE CONNECTIVITY (TE) 6P AMPMODU II SHRD HDR, ST, 0.38AU AMPMODU | AMPMODU Headers Ƴ ⊡ f v

280372-2 TE Internal Number: 280372-2

Always EU RoHS/ELV Compliant Applies To **Printed Circuit Board**

Connector Style Plug
Centerline 2.54 mm [.1 in]

Number of Positions **6**

Header Type Shrouded

AMPMODU II HEADER PDF English	
3D PDF PDF 3D	
Customer View Model 2D_DXF.ZIP English	
Customer View Model 3D_IGS.ZIP English	
Customer View Model 3D_STP.ZIP English	
	PDF English 3D PDF PDF 3D Customer View Model 2D_DXF.ZIP English Customer View Model 3D_IGS.ZIP English Customer View Model 3D_STP.ZIP

Product Environmental Compliance

TE Material Declaration

MD_280372-2_061620141015_dmtec PDF

English

Please review product documents or **contact us** for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features

Applies To Connector Style PCB Mounting Orientation Printed Circuit Board

Plug

Vertical

Connector Type

Header

	Row-to-Row Spacing	2.54 mm [.1 in]	
	Stabilizers	Without	
	Strain Relief	Without	
	Board Standoff	Without	
	Profile	Standard	
	Product Type	Connector	
	Gasket	Without	
Configuration Features	Number of Positions	6	
	Number of Rows	1	
	Keyed	Νο	
	Selectively Loaded	Νο	
Electrical Characteristics	Dielectric Withstanding Voltage	750 V	
Body Features	Header Type	Shrouded	
	Post Size (in)	.025	
Contact Features	Contact Protection	With	
	Contact Shape	Round	
	Contact Type	Pin	
	Contact Base Material	Brass	
	Contact Mating Area Plating Thickness (µin)	15	
	Solder Tail Contact Plating Material	Tin	
	Contact Mating Area Plating Material	Gold	
	Contact Protection Type	Shrouded	
Termination Features	Termination Post Length	3.5 mm [.138 in]	
	Termination End Plating Material	Tin	
	Termination End Plating Thickness (μ m)	2.5	
	Termination Method to PC Board	Through Hole	
Mechanical Attachment	PCB Mounting Style	Through Hole	
	PCB Mount Retention	Without	
	Mating Connector Lock Type	Detent Windows	
	Mating Connector Lock Type Panel Mount Retention	Detent Windows Without	

	Mating Alignment Mating Connector Lock Mating Alignment Type	With With Polarization
Housing Features	Centerline	2.54 mm [.1 in]
	Housing Color	Black
	Housing Material	Thermoplastic
	Housing Style	3-Sided
Dimensions	Mating Post Length	6.6 mm [.26 in]
	Shrouded End Dimension (mm)	1.65
Usage Conditions	Operating Temperature Range (°C)	-65 – 105
	High Temperature Housing	Νο
Operation/Application	High Speed Serial Data Connector	Νο
Industry Standards	UL Flammability Rating	UL 94V-0
	Approved Standards	CSA LR7189, UL E28476
Packaging Features	Packaging Quantity	1000
	Packaging Method	Вох
Product Compliance	Statement of Compliance	

CUSTOMERS ALSO BOUGHT

BLANK DIE-CUT LABELS	THROUGH-HOLE RESISTORS	MULTIPLE CONFIGURATION PCB HEADERS & RECEPTACLES	MULTIPLE CONFIGURATION PCB HEADERS & RECEPTACLES
		ALLER	
	CFR25 5% 270R CFR25J270R	8P AMPMODU II SHRD HDR, ST, 0.38AU 280373-2	MOD I INCREMENTAL ASSY 280618-2
	Save to ListFind Similar Products	Save to ListFind Similar Products	Save to List

VIEW ALL PRODUCT COMPLIANCE