




## 925713-2 Product Details



**925713-2**

TE Internal Number: 925713-2

Active

### .240, .295" Centerline, 250 v, 28 A max. (.140" MATE-N-LOK)

Always EU RoHS/ELV Compliant (Statement of Compliance)

#### Product Highlights:

- Contact
- Contact Type = Pin
- Applies To Wire/Cable
- Wire/Cable Type = Discrete Wire
- Packaging Method = Strip

[View all Features](#)

#### Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [View Housings \(10\)](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)
[Request Sample](#)
[Find Similar Products](#)
[Buy Product](#)

Documentation & Additional Information	
Documents are temporarily unavailable. We are working hard to correct the problem. Please try again later.	<b>Additional Information:</b> <ul style="list-style-type: none"> <li>• <a href="#">Product Line Information</a></li> </ul> <b>Related Products:</b> <ul style="list-style-type: none"> <li>• <a href="#">Tooling</a></li> <li>• <a href="#">Housings (10)</a></li> </ul>

Product Features (Please use the Product Drawing for all design activity)	
<b>Product Type Features:</b> <ul style="list-style-type: none"> <li>• <a href="#">Product Type</a> = Contact</li> <li>• <a href="#">Wire/Cable Type</a> = Discrete Wire</li> <li>• <a href="#">Wire Insulation Diameter (mm [in])</a> = 2.50 - 4.50 [0.098 - 0.177]</li> <li>• <a href="#">Connector Line</a> = .140 MATE-N-LOK</li> </ul> <b>Electrical Characteristics:</b> <ul style="list-style-type: none"> <li>• <a href="#">Current Rating (A)</a> = 28</li> <li>• <a href="#">Voltage (VAC)</a> = 250</li> </ul> <b>Body Features:</b> <ul style="list-style-type: none"> <li>• <a href="#">Wire Range (mm [AWG])</a> = 2.00-6.00<sup>2</sup> [14-10]</li> <li>• <a href="#">Spare Tube</a> = 725939-0</li> <li>• <a href="#">Stock Thickness (mm [in])</a> = 0.35 [0.014]</li> </ul> <b>Contact Features:</b> <ul style="list-style-type: none"> <li>• <a href="#">Contact Type</a> = Pin</li> <li>• <a href="#">Contact Base Material</a> = Phosphor Bronze</li> <li>• <a href="#">Contact Diameter (mm [in])</a> = 3.56 [0.140]</li> <li>• <a href="#">Solder Tail Contact Plating</a> = Pre-Tin</li> </ul>	<b>Industry Standards:</b> <ul style="list-style-type: none"> <li>• <a href="#">RoHS/ELV Compliance</a> = RoHS compliant, ELV compliant</li> <li>• <a href="#">Lead Free Solder Processes</a> = Not relevant for lead free process</li> <li>• <a href="#">RoHS/ELV Compliance History</a> = Always was RoHS compliant</li> </ul> <b>Conditions for Usage:</b> <ul style="list-style-type: none"> <li>• <a href="#">Applies To</a> = Wire/Cable</li> </ul> <b>Packaging Features:</b> <ul style="list-style-type: none"> <li>• <a href="#">Packaging Method</a> = Strip</li> <li>• <a href="#">Packaging Quantity</a> = 7,500</li> </ul> <b>Other:</b> <ul style="list-style-type: none"> <li>• <a href="#">Brand</a> = AMP</li> </ul>

<b>Corporate Information</b> <a href="#">About TE</a> <a href="#">Investors</a> <a href="#">News Room</a> <a href="#">Supplier Portal</a> <a href="#">Careers</a> <a href="#">Terms &amp; Conditions</a> <a href="#">Privacy Policy</a> <a href="#">AODA Accessibility Policy</a> <a href="#">AODA Multi-Year Accessibility Plan</a>	<b>Quick Links</b> <a href="#">Distributor Inventory</a> <a href="#">Product Cross Reference</a> <a href="#">Documents &amp; Drawings</a> <a href="#">Product Compliance Support Center</a> <a href="#">Site Map</a>	<b>Customer Support</b> <a href="#">Email or Chat With Us</a> <a href="#">Find a Phone Number</a> <a href="#">Knowledge Base</a> <a href="#">Manage Your Account</a>	<b>Keep Me Informed</b> 
---	---	--	-----------------------------

