




## HEADERS & RECEPTACLES



Active

PRODUCT DRAWING  
English

3D PDF

TE CONNECTIVITY (TE)

### CT P/HDR ASSY V 4P W/KINK BLUE

AMP CT | AMP CT

2-292161-4

TE Internal Number: 2-292161-4

Always EU RoHS/ELV Compliant

Centerline **2 mm [ .079 in ]**

Number of Positions **4**

PCB Mounting Orientation **Vertical**

PCB Mounting Style **Through Hole**

Number of Rows **1**

#### Product Drawings

[POST HEADER ASS'Y VERTICAL TYPE \(AMP CT CONNECTOR 2mm PITCH\)](#)

PDF  
English

#### CAD Files

[Customer View Model](#)

2D\_DXF.ZIP  
English

[3D PDF](#)

PDF  
3D

[Customer View Model](#)

3D\_IGS.ZIP  
English

[Customer View Model](#)

3D\_STP.ZIP  
English

#### Product Specifications

Product Specification

[AMP COMMON TERMINATION \(CT\), CONNECTOR, 2mm PITCH, M/T TYPE, LEAD FREE VERSION](#)

TIF  
Japanese

[AMP COMMON TERMINATION \(CT\), CONNECTOR, 2mm PITCH, M/T TYPE, LEAD FREE VERSION](#)

PDF  
Japanese

[AMP COMMON TERMINATION \(CT\), CONNECTOR, 2mm PITCH, M/T TYPE, LEAD FREE VERSION](#)

PDF  
English

#### Product Environmental Compliance

TE Material Declaration

[MD\\_2-292161-4\\_0429201490\\_dmtec](#)

PDF  
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

---

Product Type Features	PCB Mounting Orientation	<b>Vertical</b>
	Product Type	<b>Connector</b>
	Connector Type	<b>Header</b>
	Shape	<b>Rectangular</b>
	Connector System	<b>Wire-to-Board</b>
	Wire/Cable Type	<b>Discrete Wire</b>
	Strain Relief	<b>Without</b>
	Sealed	<b>No</b>
	Connector Style	<b>Header</b>
	Applies To	<b>Printed Circuit Board</b>

---

Configuration Features	Number of Positions	<b>4</b>
	Number of Rows	<b>1</b>
	Tail Orientation	<b>Inline</b>
	Backwall/Post Interruptions	<b>Without</b>

---

Electrical Characteristics	Operating Voltage	<b>125 VAC [ 125 VDC ]</b>
----------------------------	-------------------	----------------------------

---

Body Features	Header Type	<b>Partially Shrouded</b>
---------------	-------------	---------------------------

---

Contact Features	Contact Mating Area Plating Material	<b>Tin</b>
	Contact Mating Area Plating Thickness	<b>1 – 2 µm [ 39.37 – 78.73 µin ]</b>
	Contact Termination Area Plating Thickness	<b>1 – 2 µm [ 39.37 – 78.73 µin ]</b>
	Contact Style	<b>Straight</b>
	Contact Shape	<b>Round</b>
	Tail Plating Material	<b>Tin</b>
	Contact Termination Area Plating Material	<b>Tin</b>
	Contact Type	<b>Pin</b>
	Contact Transmits (Typical)	<b>Signal (Data)</b>
	Contact Current Rating (A)	<b>4</b>
	Contact Layout	<b>Inline</b>
	Contact Design	<b>Round Post</b>
	Contact Base Material	<b>Brass</b>

Termination Features	Termination Method to PC Board	<b>Through Hole - Solder</b>
Mechanical Attachment	PCB Mounting Style	<b>Through Hole</b>
	PCB Mount Alignment	<b>Without</b>
	Mating Retention	<b>Without</b>
	PCB Mount Retention	<b>With</b>
	PCB Mount Retention Type	<b>Kinked Legs</b>
	Contact Retention	<b>With</b>
	Contact Retention Type	<b>Locking Lance</b>
	Panel Mount Retention	<b>With</b>
Housing Features	Centerline	<b>2 mm [ .079 in ]</b>
	Housing Color	<b>Blue</b>
	Housing Material	<b>Nylon 66</b>
Dimensions	Tail Length	<b>3.2 mm [ .126 in ]</b>
	Mating Post Length	<b>4.5 mm [ .177 in ]</b>
	PCB Thickness (Recommended)	<b>.8 mm [ .031 – .063 in ]</b>
	Height	<b>6.8 mm [ .267 in ]</b>
	Wire/Cable Size (AWG)	<b>28 – 22</b>
	Width	<b>3.6 mm [ .141 in ]</b>
	Length	<b>9.8 mm [ .386 in ]</b>
Usage Conditions	Operating Temperature Range	<b>-40 – 221 °C [ -40 – 105 °F ]</b>
Operation/Application	For Use With	<b>Printed Circuit Board</b>
	Internal/External	<b>Internal</b>
	Pick and Place Cover	<b>Without</b>
Industry Standards	UL Flammability Rating	<b>UL 94V-0</b>
	UL File Number	<b>E28476</b>
	Agency/Standard	<b>CSA, UL</b>
	CSA File Number	<b>LR 7189</b>
Packaging Features	Packaging Method	<b>Bag/Box</b>

---

Product Compliance

[Statement of Compliance](#)  
PDF

[VIEW ALL PRODUCT COMPLIANCE](#)