Detailed Specifications & Technical Data



8422 Multi-Conductor - Two-Conductor, Low-Impedance Cable

For more Information please call

1-800-Belden1



General Description:

22 AWG stranded (16x34) high-conductivity tinned copper conductors, polyethylene insulation, cotton braid, double tinned copper braid shield (85% coverage), PVC jacket.

Physical Characteristics (Over	all)
Conductor	
AWG:	
# Conductors AWG Stranding Cond	
	Conductivity TC - Tinned Copper 0.31
Total Number of Conductors:	2
Insulation	
Insulation Material:	
Insulation Material Wall Thickness (i PE - Polyethylene .021	.) Dia. (in.) .072
Outer Shield Outer Shield Material:	
Type Outer Shield Material Coverage	e (%)
Braid TC - Tinned Copper 85	
Outer Jacket	
Outer Jacket Material:	
	hickness (in.)
PVC - Polyvinyl Chloride .022	
Overall Cable	
Overall Cabling Color Code Chart:	
Number Color 1 Clear	
2 Black	
	alter Cattor Draid
Overall Cabling Separator Materi	
Overall Nominal Diameter:	0.231 in.
Mechanical Characteristics (O	verall)
Operating Temperature Range:	-40°C To +80°C
Non-UL Temperature Rating:	80°C
Bulk Cable Weight:	30 lbs/1000 ft.
Max. Recommended Pulling Tens	
Max. Recommended Pulling Tens	sion: 93 lbs.
Min. Bend Radius/Minor Axis:	
Min. Bend Radius/Minor Axis:	sion: 93 lbs. 2.300 in.
Min. Bend Radius/Minor Axis: Applicable Specifications and Applicable Standards & Environm	sion: 93 lbs. 2.300 in. Agency Compliance (Overall) mental Programs
Min. Bend Radius/Minor Axis: Applicable Specifications and	sion: 93 lbs. 2.300 in. Agency Compliance (Overall) mental Programs
Min. Bend Radius/Minor Axis: Applicable Specifications and Applicable Standards & Environm	sion: 93 lbs. 2.300 in. Agency Compliance (Overall) mental Programs
Min. Bend Radius/Minor Axis: Applicable Specifications and Applicable Standards & Environr EU Directive 2011/65/EU (ROHS I	sion: 93 lbs. 2.300 in. Agency Compliance (Overall) mental Programs I): Yes

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

8422 Multi-Conductor - Two-Conductor, Low-Impedance Cable

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
enum/Non-Plenum	
Plenum (Y/N):	No

Electrical Characteristics (Overall)

No	m. Characteristic Impedance:
	Impedance (Ohm)
	90
No	om. Inductance:
	Inductance (µH/ft)
	.22
No	m. Capacitance Conductor to Conductor:
	Capacitance (pF/ft)
	18
۔ No	m. Capacitance Cond. to Other Conductor & Shield:
	Capacitance (pF/ft)
	32
l	52
No	om. Conductor DC Resistance:
	DCR @ 20°C (Ohm/1000 ft)
[15.9
No	minal Outer Shield DC Resistance:
	DCR @ 20°C (Ohm/1000 ft)
	3.5
Ma	IX. Operating Voltage - Non-UL:
	Voltage
	1000 V RMS
Ma	x. Recommended Current:
Ma	

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8422 060U1000	1,000 FT	31.000 LB	CHROME		2 #22 PE CBRD BRD PVC
8422 0601000	1,000 FT	33.000 LB	CHROME	С	2 #22 PE CBRD BRD PVC
8422 060500	500 FT	16.500 LB	CHROME	С	2 #22 PE CBRD BRD PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 05-14-2007

© 2014 Belden, Inc All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract,

Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



8422 Multi-Conductor - Two-Conductor, Low-Impedance Cable

negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.