


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	MATERIAL	HEIGHT "A" +/- .031	IMPRINT AREA "B" +/- .031	VERTICAL REPEAT "C" +/- .031	LABELS PER ROW	STANDARD PKG. QTY.
S075X125TAT	GMT1	1.25 [ 31.8 ]	0.38 [ 9.53 ]	1.50 [ 38.1 ]	5	5000
S075X075VATY	GMV16 OR GMV17	0.75 [ 19.0 ]	0.25 [ 6.35 ]	1.00 [ 25.4 ]		
S075X100VATY		1.00 [ 25.4 ]	0.38 [ 9.53 ]	1.25 [ 31.8 ]		
S075X125VATY		1.25 [ 31.8 ]		1.50 [ 38.1 ]		
S075X150VATY		1.50 [ 38.1 ]	0.50 [ 12.7 ]	1.75 [ 44.45 ]		

5



NOTES:  
1. MILLIMETERS ARE IN [ ].

CAD FILENAME/LAYERS 100472JY-DC-C10466/06F

PANDUIT CORP. TINLEY PARK, ILLINOIS

CUSTOMER DRAWING  
OPTIMUM SELF-LAM. S075X\*\*\*VATY AND  
S075X125TAT THERMAL TRANSFER PRINTABLE LABELS

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:  
(.X) ± .12 (.XXX) ± .025  
(.XX) ± .062 ANGLES ±

UNLESS OTHERWISE SPECIFIED,  
ALL DIMENSIONS ARE GIVEN  
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY  
RVU

MAT'L:

SCALE NTS

DATE  
8-31-06

SEE TABLE

DRAWING NO.

C10466

DWG  
A  
SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
5	10/25/11	RVU		"GMV16 OR GMV17" WAS "GMV".	6548	R		
4	9/6/11	RVU	MSAD	ADD S075X100VATY ON TABLE.	6503	R		
3	8-31-06	RVU		UPDATE ON ALL STANDARD TOLERANCES AND REMOVE NOTE 1.	5925	R		
2	8-31-06	RVU		ADDED NEW P/N: S075X125TAT.	5021	R		
1	8-31-06	RVU		REVISED TOLERANCES.	4830	R		
0	8-31-06	RVU		DRAWING RELEASE.	4671	R		

CHK'D

*[Handwritten signature]*