



Series
477


Handheld Digital Manometer

Selectable Pressure Units, $\pm 0.5\%$ Accuracy, FM Approved Intrinsically
Safe for Hazardous Locations, Class 1, Div. 1, Group A, B, C, D, T4



TEST EQUIPMENT

Manometers,
Portable



Series 477 Handheld Digital Manometers are packed with features you need to make pressure measurement and recording faster, easier and more accurate than ever. First, you can instantly select from up to nine of the most widely used pressure units without having to waste time and risk mistakes with tedious conversions. Next, a non-volatile memory function enables storage of up to 40 readings – perfect for HVAC technicians making Pitot tube traverses of airflow readings across a duct. The FM approved models are intrinsically safe for hazardous locations, Class 1, Div. 1, Group A, B, C, D, T4.

When working in poorly lighted areas, just switch on the handy backlight feature. It automatically shuts itself off after 20 minutes to minimize battery drain. Electronic zeroing means you simply touch a single key to perfectly null out any minor pressure differences. A display HOLD key freezes the current pressure for those all-too-common situations where readings fluctuate. We even included an audible alarm to warn you of overpressure plus a visual alarm warning in case ambient noise levels are too high to hear the alarm. Audible alarm also confirms a value has been stored, eliminating the need to observe display during a duct traverse.

FEATURES

- New low pressure ranges
- USB option comes with cable and software for easy data downloading
- Instant selection from up to nine english/metric units
- Stores 40 readings in memory for later reference
- Measure positive, negative or differential pressures
- Large easy-to-read 0.4" LCD display includes switchable backlight for great visibility — anywhere
- Both audible and visual overpressure alarms
- Includes + and - indicators plus low battery warning
- Operates up to 100 Hours on a single 9 V battery

See page 567 for process tubing options.

SPECIFICATIONS

Service: Air and compatible gases. FM models air and compatible combustible gases.

Wetted Materials: Consult factory.

Accuracy: $\pm 0.5\%$ FS, 60 to 78°F (15.6 to 25.6°C); $\pm 1.5\%$ FS from 32 to 60°F and 78 to 104°F (0 to 15.6°C and 25.6 to 40°C).

Pressure Hysteresis: $\pm 0.1\%$ of full-scale.

Pressure Limits: See chart.

Temperature Limits: 0 to 140°F (-17.8 to 60°C).

Compensated Temperature Limits: 32 to 104°F (0 to 40°C).

Storage Temperature Limits: -4 to 176°F (-20 to 80°C).

Display: 0.42" (10.6 mm) 4 digit LCD.

Response Time: 1 s.

Resolution: See chart.

Power Requirements: 9 V alkaline battery, installed non-functional, user replaceable.

Weight: 10.2 oz (289 g).

Connections: Two barbed connections for use with 1/8" (3.18 mm) or 3/16" (4.76 mm) ID tubing. Two compression fittings for use with 1/8" (3.18 mm) ID x 1/4" (6.35 mm) OD tubing for 477-7-FM & 477-8-FM only.

Agency Approvals: CE, FM.

ACCESSORIES

A-402A CARRYING CASE — Tough gray nylon pouch protects any Series 477 Manometer. Double zippered for quick and easy access. With belt loop that snaps closed.

7-1/2"H x 3"W x 2-1/4"D (191 x 76 x 57 mm)

UHH-C1, Soft carrying case



OPTION

For NIST traceable calibration certificate, add suffix -NIST to model numbers. Example: 477-1-FM-NIST.

Model*	Range	Available Pressure Units								Maximum Pressure	
		bar	psi	in Hg	kPa	in w.c.	mm Hg	mbar	mm w.c.		Pa
477-000-FM	0-1.000 in w.c.			.0736	.2491	1.000	1.868	2.491	25.40	249.1	5 psig
477-00-FM	0-4.000 in w.c.		.1445	.2942	0.996	4.000	7.473	9.96	101.6	996	5 psig
477-0-FM	0-10.00 in w.c.		.3613	.7355	2.491	10.00	18.68	24.91	254.0	2491	5 psig
477-1-FM	0-20.00 in w.c.	.0498	.7225	1.471	4.982	20.00	37.36	49.82	508.0	4982	10 psig
477-2-FM	0-40.00 in w.c.	.0996	1.445	2.942	9.96	40.00	74.73	99.6	1016	9964	10 psig
477-3-FM	0-200.0 in w.c.	.4982	7.225	14.71	49.82	200.0	373.6	498.2	5080	49820	30 psig
477-4-FM	0-10.00 psi	.6895	10.00	20.36	68.95	276.8	517.1	689.5	7031	68950	30 psig
477-5-FM	0-20.00 psi	1.379	20.00	40.72	137.9	553.6	1034	1379		13790	60 psig
477-6-FM	0-30.00 psi	2.069	30.00	61.08	206.9	830.4	1551	2069		20690	60 psig
477-7-FM	0-100.0 psi	6.895	100.0	203.6	689.5	2768	5171	6895		68950	150 psig
477-8-FM	0-150.0 psi	10.34	150.0	305.4	1034	4152	7757			77570	200 psig