

ENERGIZER L91
Ultimate Lithium




Specifications



Classification:	"Cylindrical Lithium"
Chemical System:	Lithium/Iron Disulfide (Li/FeS ₂)
Designation:	ANSI 15-LF, IEC-FR6
Nominal Voltage:	1.5 Volts
Storage Temp:	-40°C to 60°C (-40°F to 140°F)
Operating Temp:	-40°C to 60°C (-40°F to 140°F)
Typical Weight:	14.5 grams (0.5 oz.)
Typical Volume:	8.0 cubic centimeters (0.5 cubic inch)
Max Discharge:	3.0 Amps Continuous
(single battery only)	5.0 Amps Pulse (2 sec on / 8 sec off)
Max Rev Current:	2 uA
Typical Li Content:	Less than 1 gram
Typical IR:	90 to 160 milliohms (depending on method)
Shelf Life:	15 years at 21°C


Industry Standard Dimensions




This battery has Underwriters Laboratories component recognition. (MH29980)



Milliamp-Hours Capacity

Constant Current Discharge to 0.9 Volts at 21°C



Milliwatt-Hours Capacity at Cold/Room Temperature

Constant Power Discharge to 1.0 Volts at 0°C and 21°C



Important Notice



This datasheet contains typical information specific to products manufactured at the time of its publication.
©Energizer Holdings, Inc. - Contents herein do not constitute a warranty.

ENERGIZER L91




Typical Discharge Curve Characteristics

Constant Current Discharge at 21°C (low and high drains)




Constant Power Performance

Typical Characteristics to 1.0 Volts (21°C)




Constant Current Performance


Typical Characteristics to 1.0 Volts (21°C)




Application Tests (21°C)




Application Tests (21°C)



Application Tests (21°C)



Industry Standard Tests (21°C)



Important Notice

This datasheet contains typical information specific to products manufactured at the time of its publication.
©Energizer Holdings, Inc. - Contents herein do not constitute a warranty.