


Plug-in unit in kit form for CompacPCI and VME64x applications




Illustration shows front panel 6 U, 4 HP



6 U

Dimension 3 / 6 U



Product illustrations are exemplary illustrations and can deviate from supplied products.

Part no.: 20848-596

Features:

- Meets IEEE 1101.10 and IEC 60297-3-102 standards
- Codable to IEC 60297-3-103
- Front panel shielded, without offset
- Suitable for insertion and extraction forces up to 700 N (per pair)
- Designed for fitting of microswitches

[Add to basket](#)



Technical information:

| Description | Height | Width |
|----------------|--------|-------|
| Front assembly | 6 U | 8 HP |

Downloads:

- 3D PDF with CAD data (DWG/DXF/PDF/STEP) ([Log in](#) Required)
- User manual, plug-in unit IEEE ([Log in](#) Required)
- User Manual ([Log in](#) Required)
- User manual, coding IEEE ([Log in](#) Required)

To gain access to the additional information you must [Log in](#).
If you do not yet have a user name, you may [Register here](#).

Delivery comprises: kit

| Item | Qty | Description |
|------|-------|---|
| | 6 U | |
| | ≥8 HP | |
| 1 | 1 | U front profile, aluminium front: anodised; -rear: pickled |
| 2 | 1 | EMC seal. Core: foam Sleeve: textile cladding with CuNi coating |
| 3 | 2 | IEL handle with integrated alignment pin for perforated strip and guide rail Lever: plastic PC, light grey, RAL 7035 Key: plastic PC, black, RAL 9005 |
| 4 | - | Printed board bracket, diecast zinc |

| | | |
|----|---|--|
| 5 | - | Countersunk screw with cross recess, M 2,5 × 8, St nickel-plated |
| 6 | 2 | Sleeve, PA, grey |
| 7 | 4 | Collar screw with cross recess M 2,5 × 12,3, St, nickel-plated |
| 8 | 2 | Countersunk screw with cross recess, M 2,5 × 6, St nickel-plated |
| 9 | 2 | Washer A 2.7, St, nickel-plated |
| 10 | 2 | Countersunk screw with cross recess, M 2,5 × 6, St nickel-plated |

Accessories:

| Part no. | Description | |
|------------------|--|----------------------|
| 20817-606 | Microswitch for handles, CompactPCI/VME64x application Qty: 10 pieces | Add to basket |