



ENGLISH

Datasheet

Stock No: 404-493

RS Pro 3.05mm Transparent PTFE Cable Sleeve



Product Details

PTFE Sleaving

Clear PTFE sleaving, used in areas of high temperature, or where avoidance of contamination is desired. PTFE has excellent physical and chemical properties. The chemical resistance is very wide-ranging, with few limitations.

Tensile Strength: 26 → 36 MPa

Impact resistance: 185J/m (23°C) → 107J/m (-54°C)

Specific Gravity: 2.14 → 2.21 g/cm³

Elongation: min 200%

Coefficient of Friction (dynamic): 0.1

Note

This product is Compliant with ROHS 2002/95/EC the Restriction of use of certain Hazardous Substances in electrical and electronic equipment. The product adheres to AMS 3655A.

Standard Sleaving



ENGLISH

Specifications:

Sleeve Diameter	3.05mm
Colour	Transparent
Material	PTFE
Sleeve Length	5m
Minimum Cable Diameter	3.05mm
Minimum Operating Temperature	-65°C
Maximum Operating Temperature	+250°C
Wall Thickness	0.38mm