

Raychem Interconnect

Raychem TFE and TFE-R are heatshrinkable tubings manufactured from a modified Teflon (Polytetrafluoroethylene), an excellent high temperature covering and insulation material with a milk-white translucence. TFE is the general purpose tubing for difficult chemical and thermal environments. TFE-R has the added advantages of thin wall, high shrink ratio, greater flexibility and

Ordering information

- Operating temperature range -67°C to +250°C
- Highly flame retarded
- · Excellent chemical resistance
- Shrink ratio 1.8:1 TFE Shrink ratio 3.2:1 TFE-R

TFE/TFE-R

High temperature, chemically inert, heat-shrinkable tubing

transparency in application. TFE and TFE-R are highly flame retarded and exhibit outstanding chemical and solvent resistance with electrical characteristics which remain stable over a wide temperature range. The operating temperature ranges from -67°C to +250°C, and up to 400°C for short periods. The major uses of these materials are for electrical insulation, protection of electronic components and the covering of hydraulic hose and couplings preventing contamination and corrosion. The high mechanical strength and extremely low coefficient of friction make it ideal for reducing damage to bearing shafts, etc.



						<u> </u>			
Inside	diameter			Wallt	hickness	Stand	ard package		
D (min Expan supplie) ded as ed	d (max Recov afterh	k) ered eating	W (no Recov heatin	m) ered after g	1.2 m length quanti	i ity		
mm	mm	mm	mm	mm	mm	m	m	Ordering descriptior	1
TFE	TFE-R	TFE	TFE-R	TFE	TFE-R	TFE	TFE-R	TFE	TFE-R
0.8	2.0	0.38	0.6	0.23	0.23	18	12	TFE-30-X	TFE-R-5/64-X
0.9	3.2	0.46	1.0	0.23	0.25	18	12	TFE-28-X	TFE-R ⁻¹ / ₈ -X
1.1	6.4	0.56	1.6	0.25	0.30	18	12	TFE-26-X	TFE-R-1/4-X
1.2	9.5	0.68	2.4	0.25	0.30	18	6	TFE-24-X	TFE-R- ³ / ₈ -X
1.4	12.7	0.81	3.7	0.30	0.38	18	6	TFE-22-X	TFE-R-1/2-X
1.5	15.9	0.99	4.5	0.30	0.38	18	6	TFE-20-X	TFE-R-5/8-X
1.9	19.0	1.24	5.7	0.30	0.38	18	6	TFE-18-X	TFE-R- ³ / ₄ -X
2.3	25.4	1.55	7.1	0.30	0.38	18	6	TFE-16-X	TFE-R-1-X
3.0	32.0	1.83	8.8	0.30	0.38	18	6	TFE-14-X	TFE-R-1 ¹ / ₄ -X
3.8	-	2.26	-	0.30	-	12	-	TFE-12-X	-
4.8	-	2.84	-	0.30	-	12	-	TFE-10-X	-
6.1	-	3.58	-	0.38	-	6	-	TFE-8-X	-
7.6	-	4.52	-	0.38	-	6	-	TFE-6-X	-
9.4	-	5.69	-	0.38	-	6	-	TFE-4-X	-
10.9	-	7.06	-	0.38	-	6	-	TFE-2-X	-
11.9	-	8.81	-	0.38	-	6	-	TFE-0-X	-
-				-					

The largest size which will recover snugly over the component to be covered

should be ordered.

With TFE-R the maximum outside diameter of the device to be encapsulated should be less than 20% of the minimum expanded inside diameter of the tubing. The wall thickness of the tubing will be less than specified if recovery is restricted during shrinkage.

Other lengths and sizes are available subject to special order.

Standard colours

Colour	Clear
Code	X

TFE/TFE-R

Temperature rating

Operating temperature range:	-67°C to +250°C	
Minimum full recovery temperature:	+340°C	

Approvals

MIL-DTL-23053/12	Def Std 59-97 Type 5A (TFE)
AMS 3584, 3585	Def Std 59-97 Type 5B (TFE-R)
	BS 3G 198 Type 21A (TFE)
	BS 3G 198 Type 21B (TFE-R)

Performance

Test	Test method	Test requirement		
Heat shock:	ASTM D2671 (4 h at 400°C)	No dripping, cracking or flowing		
Heat ageing:	ISO 188 (168 h at 350°C)	Ultimate elongation: 150% (min)		
Dielectric strength:	IEC 243	27.5 MV/m (min)		
Fluid resistance:		Inert		
	For full product performance d TFE-R RW 2054.	etails consult Raychem Specification TFE RW 2055		

Special installation instructions

For optimum performance TFE and TFE-R must be heated above their crystaline melting points, 327°C. As the tubing reaches this temperature, it turns from a milk-white translucence to a completely transparent material - at this point the heat source should be removed, as 20%-30% of shrinkage occurs as the tubing cools and returns to its original appearance.

Specifications

Raychem Specification TFE RW 2055 TFE-R RW 2054. Material Safety Data Sheet available on request. Installation instructions available on request.

Raychem and TFE/TFE-R are trademarks of Raychem Interconnect, a division of Tyco Electronics Corporation.

All of the above information, including illustrations, is believed to be reliable. Users, however, should independently evaluate the suitability of each product for their application. Tyco Electronics makes no warranties as to the accuracy or completeness of the information and disclaims any liability regarding its use. Tyco Electronics only obligations are those in the Standard Terms and Conditions of Sale for this product and in no case will Tyco Electronics be liable for any incidental, indirect or consequential damages arising from the sale, resale, use or misuse of the product. Tyco Electronics Specifications are subject to change without notifice. In addition Tyco Electronics reserves the right to make changes in materials or processing, without notification to the Buyer, which do not affect compliance with any applicable specification.

Raychem Interconnect Cheney Manor Industrial Estate Swindon, Wiltshire SN2 2QE Tel: (44)-1793-528171 Fax: (44)-1793-616652