


**71363-102 - Mini-Jump™ : 2.54 mm (0.1 in.)
Centerline, Single Row, High Body Shunt 0.38 µm
(15 µin.) Gold Plating**



ACTIVE



www.fci.com

Alternate Products

71363-102LF

Specifications

Approvals / Certifications

UL File Number	E66906
CSA File Number	LR46923
Approvals / Certifications	UL and CSA Approved

Mechanical

Durability (Mating cycles)	50
Insertion force	450gf (1lbf) max.
Withdrawal Force	30gf (0.06lbf) min.

Dimensional

Height (Housing)	9.15 mm (0.36 in.)
Dim A (in)	0.198 in.
Dim A (mm)	5.03 mm
Spacing (Center line)	2.54 mm (0.1 in.)

Electrical

Current rating	2.5 amps
Resistance (Contact)	15 milli ohms (Initial), 20 milli ohms (After test)
Resistance (Insulation)	50000 M-ohms min.
Voltage rating	800V AC rms (Sea level)

General

Number of contacts (Total)	2
Number of rows	1
Mating half	0.64 Square Pins of 3.68 mm min. Height
Series Number	71363

Other Features

Packaging (Type)	Bag
Bus Bar	No

Physical

Color (Housing)	Black
Material (Contact)	Copper Alloy
Material (Housing)	Glass-Filled Thermoplastic Polyester (UL 94 V-0)
Plating (Contact area)	0.38 µm (15 µin.) Gold
Underplating (Contact)	1.27 µm (50 µin.) Nickel
Temperature (Range)	-55°C to +120°C