MM3ZxxxST1G Series, SZMM3ZxxxST1G Series

Zener Voltage Regulators

300 mW SOD-323 Surface Mount **Tight Tolerance Portfolio**

This series of Zener diodes is packaged in a SOD-323 surface mount package that has a power dissipation of 300 mW. They are designed to provide voltage regulation protection and are especially attractive in situations where space is at a premium. They are well suited for applications such as cellular phones, hand-held portables, and high density PC boards.

Specification Features

- Standard Zener Breakdown Voltage Range 3.3 V to 36 V
- Steady State Power Rating of 300 mW
- Small Body Outline Dimensions: - 0.067" x 0.049" (1.7 mm x 1.25 mm)
- Low Body Height: 0.035" (0.9 mm)
- Package Weight: 4.507 mg/unit
- ESD Rating of Class 3 (> 16 kV) per Human Body Model
- Tight Tolerance V_Z
- SZ Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and **PPAP** Capable
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant*

Mechanical Characteristics:

CASE: Void-free, transfer-molded plastic FINISH: All external surfaces are corrosion resistant MAXIMUM CASE TEMPERATURE FOR SOLDERING PURPOSES:

260°C for 10 Seconds **LEADS:** Plated with Pb–Sn or Sn only (Pb–Free) **POLARITY:** Cathode indicated by polarity band FLAMMABILITY RATING: UL 94 V-0 **MOUNTING POSITION:** Any




ON Semiconductor®


http://onsemi.com



SOD-323 **CASE 477** STYLE 1



MARKING DIAGRAM



XX = Specific Device Code M = Date Code*

= Pb-Free Package

(Note: Microdot may be in either location)

*Date Code orientation may vary depending upon manufacturing location.

ORDERING INFORMATION

Device	Package	Shipping [†]
MM3ZxxxST1G	SOD-323 (Pb-Free)	3,000 / Tape & Reel
SZMM3ZxxxST1G	SOD-323 (Pb-Free)	3,000 / Tape & Reel
MM3ZxxxST3G	SOD-323 (Pb-Free)	10,000 / Tape & Reel

+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

DEVICE MARKING INFORMATION See specific marking information in the device marking column of the Electrical Characteristics table on page 3 of

this data sheet.

*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

MM3ZxxxST1G Series, SZMM3ZxxxST1G Series

MAXIMUM RATINGS

Rating	Symbol	Max	Unit
Total Device Dissipation FR-4 Board, (Note 1) @ $T_A = 25^{\circ}C$ Derate above 25°C	P _D	300 2.4	mW mW/°C
Thermal Resistance from Junction-to-Ambient	$R_{ hetaJA}$	416	°C/W
Junction and Storage Temperature Range	T _J , T _{stg}	-65 to +150	°C


Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. FR-4 printed circuit board, single-sided copper, mounting pad 1 cm².

ELECTRICAL CHARACTERISTICS

 $(T_A = 25^{\circ}C \text{ unless otherwise noted},$

Symbol	Parameter				
VZ	Reverse Zener Voltage @ I _{ZT}				
I _{ZT}	Reverse Current				
Z _{ZT}	Maximum Zener Impedance @ IZT				
I _{ZK}	Reverse Current				
Z _{ZK}	Maximum Zener Impedance @ I _{ZK}				
I _R	Reverse Leakage Current @ V _R				
V _R	Reverse Voltage				
١ _F	Forward Current				
VF	Forward Voltage @ I _F				
ΘVz	Maximum Temperature Coefficient of V_Z				
С	Max. Capacitance $@V_R = 0$ and $f = 1$ MHz				



MM3ZxxxST1G Series, SZMM3ZxxxST1G Series


ELECTRICAL CHARACTERISTICS (V_F = 0.9 Max @ I_F = 10 mA for all types)

Device*		Test Current Izt mA	Zener Voltage VZ		Z _{ZK} I _Z = 0.5	Z _{ZT} I _Z = IZT @ 10%	Max IR @ VR		d _{VZ} /dt (mV/k) @ I _{ZT1} = 5 mA		C pF Max @
	Device Marking		Min	Max	mA Ω Max	Mod Ω Max	μA	v	Min	Max	V _R = 0 f = 1 MHz
MM3Z2V4ST1G	T2	5.0	2.29	2.51	1000	100	50	1.0	-3.5	0	450
MM3Z2V7ST1G	Т3	5.0	2.59	2.81	1000	100	20	1.0	-3.5	0	450
MM3Z3V0ST1G	T4	5.0	2.90	3.11	1000	100	10	1.0	-3.5	0	450
MM3Z3V3ST1G	T5	5.0	3.32	3.53	1000	95	5.0	1.0	-3.5	0	450
MM3Z3V6ST1G	Т6	5.0	3.49	3.71	1000	90	5.0	1.0	-3.5	0	450
MM3Z3V9ST1G	T7	5.0	3.89	4.16	1000	90	3.0	1.0	-3.5	-2.5	450
MM3Z4V3ST1G	Т8	5.0	4.17	4.43	1000	90	3.0	1.0	-3.5	0	450
MM3Z4V7ST1G	Т9	5.0	4.55	4.75	800	80	3.0	2.0	-3.5	0.2	260
MM3Z5V1ST1G	TA	5.0	4.98	5.2	500	60	2.0	2.0	-2.7	1.2	225
MM3Z5V6ST1G	TC	5.0	5.49	5.73	200	40	1.0	2.0	-2.0	2.5	200
MM3Z6V2ST1G	TE	5.0	6.06	6.33	100	10	3.0	4.0	0.4	3.7	185
MM3Z6V8ST1G	TF	5.0	6.65	6.93	160	15	2.0	4.0	1.2	4.5	155
MM3Z7V5ST1G	TG	5.0	7.28	7.6	160	15	1.0	5.0	2.5	5.3	140
MM3Z8V2ST1G	TH	5.0	8.02	8.36	160	15	0.7	5.0	3.2	6.2	135
MM3Z9V1ST1G	ТК	5.0	8.85	9.23	160	15	0.5	6.0	3.8	7.0	130
MM3Z10VST1G	WB	5.0	9.80	10.20	160	15	0.5	6.0	4.5	8.0	130
MM3Z11VST1G	WC	5.0	10.78	11.22	160	20	0.1	8.0	5.4	9.0	130
MM3Z12VST1G	TN	5.0	11.74	12.24	80	25	0.1	8.0	6.0	10	130
MM3Z13VST1G	TQ	5.0	12.91	13.49	160	30	0.1	8.0	7.0	11	120
MM3Z15VST1G	TP	5.0	14.34	14.98	80	40	0.1	11	8.8	12.7	130
MM3Z16VST1G	TU	5.0	15.85	16.51	80	40	0.05	11.2	10.4	14	105
MM3Z18VST1G	TW	5.0	17.56	18.35	80	45	0.05	12.6	12.4	16	100
MM3Z20VST1G	U8	5.0	19.60	20.40	100	55	0.05	14.0	14.4	18	85
MM3Z22VST1G	WP	5.0	21.54	22.47	100	55	0.05	15.4	16.4	20	85
MM3Z24VST1G	WT	5.0	23.72	24.78	120	70	0.05	16.8	18.4	22	80
MM3Z27VST1G	WQ	5.0	26.19	27.53	300	80	0.05	18.9	21.4	25.3	70
MM3Z30VST1G	WV	5.0	29.19	30.69	300	80	0.05	21.0	24.4	29.4	70
MM3Z33VST1G	WR	5.0	32.15	33.79	300	80	0.05	23.2	27.4	33.4	70
MM3Z36VST1G	WU	5.0	35.07	36.87	500	90	0.05	25.2	30.4	37.4	70
MM3Z39VST1G	WN	2.0	38.22	39.78	500	130	0.05	27.3	33.4	41.2	45

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions. *Include SZ-prefix devices where applicable.


MM3ZxxxST1G Series, SZMM3ZxxxST1G Series


TYPICAL CHARACTERISTICS



PACKAGE DIMENSIONS

SOD-323 CASE 477-02 **ISSUE H**





NOTES

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982. 2. CONTROLLING DIMENSION: MILLIMETERS.

- 3.
- LEAD THICKNESS SPECIFIED PER L/F DRAWING WITH SOLDER PLATING. DIMENSIONS A AND B DO NOT INCLUDE MOLD
- FLASH, PROTRUSIONS OR GATE BURRS. DIMENSION L IS MEASURED FROM END OF 5.

RADIUS.


	MIL	LIMET	ERS	INCHES				
DIM	MIN	NOM	MAX	MIN	NOM	MAX		
Α	0.80	0.90	1.00	0.031	0.035	0.040		
A1	0.00	0.05	0.10	0.000	0.002	0.004		
A3	().15 REI	F	0.006 REF				
b	0.25	0.32	0.4	0.010	0.012	0.016		
С	0.089	0.12	0.177	0.003	0.005	0.007		
D	1.60	1.70	1.80	0.062	0.066	0.070		
Е	1.15	1.25	1.35	0.045	0.049	0.053		
L	0.08			0.003				
HE	2.30	2.50	2.70	0.090	0.098	0.105		

STYLE 1: PIN 1. CATHODE

2 ANODE

SOLDERING FOOTPRINT*

A3



*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and 💷 are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support:

Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative