



Main

Range of product	TeSys GS
Range	TeSys
Device short name	GS1G
Fuse type	UL
Fuse size	J
Product or component type	Fuse switch disconnecter body
Device application	Distribution
Poles description	3P
Network type	AC DC
Type of operating handle	Front

Complementary

Network frequency	50/60 Hz
Mounting support	Plate Rail
[Ie] rated operational current	60 A
Rated operational power in W	30 W at 400 V AC-23
Product weight	4.85 lb(US) (2.2 kg)

Environment

standards	CSA UL
product certifications	ASEFA LOVAG LROS (Lloyds register of shipping)
IP degree of protection	IP20 with terminal cover conforming to IEC 60529

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.