

M4/8.SFLT

ABB contact for United
States of America



General Information

Extended Product Type:	M4/8.SFLT
Product ID:	1SNA115667R2700
EAN:	3472591156676
Catalog Description:	M4/8.SFLT Screw Clamp Terminal Blocks - For 5 x 20 and 5 x 25 fuses - with blown fuse indicator - Grey
Long Description:	M4/8.SFLT Screw Clamp Terminal Blocks Fuse

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks » Screw Clamp Terminal Blocks

Ordering

EAN:	3472591156676
Minimum Order Quantity:	50 piece
Customs Tariff Number:	85361010

Dimensions

Product Net Width:	8.0 mm
Product Net Height:	56.5 mm
Product Net Depth:	41.0 mm
Product Net Weight:	14.00 g

Container Information

Package Level 1 Units:	50 piece
Package Level 1 Width:	101 mm
Package Level 1 Height:	47 mm
Package Level 1 Length:	265 mm
Package Level 1 Gross Weight:	0.70000 kg
Package Level 1 EAN:	3472591156676
Package Level 2 Units:	450 piece
Package Level 2 Width:	300 mm
Package Level 2 Height:	150 mm
Package Level 2 Length:	500 mm
Package Level 2 Gross Weight:	6.200 kg
Package Level 3 Units:	21600 piece
Product Packing Type:	Box

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Connecting Capacity-Main Circuit UL/CSA:	Screw Clamp / Rigid 1x 22 ... 12 AWG

Connecting Capacity UL/CSA: Screw Clamp / Rigid 22 ... 12 AWG
Flammability According to UL94: V0

Additional Information

Ambient Temperature: -5 ... +40 °C
Color: Grey
Connecting Capacity-Main Circuit: Screw Clamp / Flexible 1x 0.5 ... 4 mm²
Screw Clamp / Rigid 1x 0.5 ... 6 mm²
Connection Type: Screw clamp
Degree of Protection: acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Function: Fuse
Gauge Type: A4
IIT Publishing Status: Level 0 - Information enabled
Insulation Material: Polyamide
Mounting on DIN Rail: G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715
TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715
TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Number of Levels: 1
Pollution Degree: 3
Product Main Type: M4/8.SF
Product Name: Terminal block
Rated Cross-Section: 4 mm²
Rated Current (I_n): Main Circuit 6.3 A
Rated Impulse Withstand Voltage (U_{imp}): 4000 V
Rated Voltage (U_r): 400 V
Recommended Screw Driver: 4 mm
RoHS Date: 20050818
Spacing: 8 mm
Sub-Function: For 5x20 and 5x25 Fuses
Sub-Function 2: With blown fuse indicator by Neon 110-230V and 2 test socket screws DIA 2 mm
0.079 in
Wire Stripping Length: 9.5 mm

Certificates and Declarations (Document Number)

CSA Certificate: TBD - OK in Ag.Base
cUL Certificate: 1SND161002A0202
Declaration of Conformity - CE: 1SND225007C1006
GOST Certificate: 1SND161005A1104
RoHS Information: 1SND230023F0206

Classifications

ETIM 4.0: EC000899 - Fuse terminal block
ETIM 5.0: EC000899 - Fuse terminal block
Object Classification Code: X



