





FEMALE END VIEW	TYPICAL PANEL CUTOUT	SPECIFICATIONS	
 <p>1 = GRAY #1 2 = GRAY #2 3 = GRAY #3 4 = GRAY #4</p>		CONTACT CARRIER MATERIAL	NYLON OR TPU
		CONTACT MATERIAL/PLATING	BRASS/GOLD
		HOUSING/LOCKNUT MATERIAL	BRASS/NICKEL
		O-RING MATERIAL	NITRILE
		RATED CURRENT [A]	4.0 A
		RATED VOLTAGE [V]	250 V
		CONDUCTOR INSULATION MATERIAL	PVC
		NUMBER OF CONDUCTORS [AWG]	4x18 AWG
		TEMPERATURE RATING	-40°C to +105°C (-40°F to +221°F)
		PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP68
		MAX. PANEL THICKNESS	3.0 [.12]





CABLE LENGTH	TOLERANCE *
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER
STRIP LENGTH	TOLERANCE *
0-7mm	±0.5mm
8-29mm	±1.0mm
30-49mm	±2.0mm
50-69mm	±3.0mm
70-100mm	±4.0mm
OVER 100mm	±5.0mm
*UNLESS OTHERWISE SPECIFIED	

NOTES:

- "*" INDICATES LEAD LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.
- "/S621" DESIGNATES EUROFAST RECEPTACLE WITH 18 AWG GREY CONDUCTORS. ALL CONDUCTORS DARK GREY AND NUMBERED TO MATCH PIN-OUT.

SOURCE DRAWING - FOR REFERENCE ONLY

RELATED DOCUMENTS		3RD ANGLE PROJECTION		<div>THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.</div> <div><div>3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com</div></div>					
1. 2. 3. 4.									
MATERIAL		DRFT IK		DATE 9/23/96		DESCRIPTION FKFD 4.4-*/S621			
		APVD		SCALE 1=.8					
FINISH		ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY		UNIT OF MEASUREMENT MILLIMETER [INCH]		IDENTIFICATION NO.		REV D	
						DO NOT SCALE THIS DRAWING		FILE: 777000916	
		CONTACT TURCK FOR MORE INFORMATION							

D	DRAWING PROCESSED AS PART OF ECO 33971	CBM	04/06/11	33971
REV	DESCRIPTION	BY	DATE	ECO NO.