

Steam Valve

Series VND

2 Port Valve for Steam

2 Port Valve for Steam Max. **180°C**

**By adopting of PTFE seal,
the valve is suited for steam.**

Body material: Bronze, Stainless steel

Large valve capacity

Wide variations

2 types — N.C., N.O.

Threaded type (6A to 50A)


Flange type (32F to 50F)

With indicator (Option)

Selectable with indicator (for visual verification of operation)

**Cylinder actuation
by external pilot air**


PTFE seal



Steam Valve: 2 Port Valve For Steam

Series VND

How to Order



Symbol	Orifice dia. (mm)	Symbol			Symbol	Port size Rc
		0	2	4		
		N.C.	N.O.	N.C.		
1	ø7	—	●	●	6A	1/8
		—	●	●	8A	1/4
		—	●	●	10A	3/8
2	ø15	●	●	—	10A	3/8
		●	●	—	15A	1/2
		●	●	—	20A	3/4
3	ø20	●	●	—	25A	1
		●	●	—	32A	1 1/4
		●	●	—	32F	1/4 B Flange
4	ø25	●	●	—	40A	1 1/2
		●	●	—	40F	1/2 B Flange
		●	●	—	50A	2
5	ø32	●	●	—	50F	2B Flange
		●	●	—		
		●	●	—		
6	ø40	●	●	—		
		●	●	—		
		●	●	—		
7	ø50	●	●	—		
		●	●	—		
		●	●	—		

- VNA
- VNB
- SGC
- SGH
- VNC
- VNH
- VND**
- VCC
- TQ

Series VND



Model

Model	Port size		Orifice dia. ø (mm)	Flow characteristics Av x 10 ⁴ m ²	Weight (kg)
	Rc	Flange <small>Note)</small>			
VND10□D-6A	1/8	—	7	26	0.3
VND10□D-8A	1/4	—		28	
VND10□D-10A	—	—		31	
VND20□D-10A	3/8	—	15	120	0.6
VND20□D-15A	1/2	—		130	
VND30□D-20A	3/4	—		240	
VND40□D-25A	1	—	25	380	1.4
VND50□D-32A	1 1/4	—		440	
VND50□D-32F	—	32	32	920	5.5
VND60□D-40A	1 1/2	—			3.6
VND60□D-40F	—	40			7.2
VND70□D-50A	2	—	50	1500	5.7
VND70□D-50F	—	50			10.8

Note) The companion flange is JIS B 2210 10K (standard) or its equivalent.

Valve Specifications

Fluid (Main piping)		Steam	
Fluid temperature		-5 to 180°C <small>Note 1)</small>	
Ambient temperature		-5 to 60°C <small>Note 1)</small>	
Proof pressure		1.5 MPa	
Operating pressure range		0 to 0.97 MPa	
External pilot air	Pressure	N.C.	0.3 to 0.7 MPa
		N.O.	0.1 + 0.25 x (Operating pressure) to 0.25 + 0.25 x (Operating pressure) MPa Refer to below "Graph (1)".
	Lubrication	Not required	
	Temperature	-5 to 60°C <small>Note 1)</small>	
Mounting orientation		Unrestricted	

Note 1) No freezing


Note 2) Non-lubricant specifications are not available for this product.

Symbol


Valve size	Valve type	N.C.	N.O.
		Normally closed	Normally open
VND1			
VND 02 D			

Graph (1)

VND□ 02 D Pilot Pressure (N.O. type)



Construction



Component Parts

No.	Description	Material	Note
1	Body	Bronze*	Clear coated
2	Cover assembly	Aluminum alloy	Platinum silver painted
3	Plate assembly	Brass*	PTFE, EPR, FKM
4	Valve element	Brass*, PTFE	—
5	Piston assembly	Aluminum alloy	—
6	Return spring	Piano wire	—
7	Second plate assembly	Aluminum alloy	—

* Body option S is made of stainless steel.

Working Principle

VND□0□□ (N.C.)

When fluid is exhausted from the port 12(P1), the valve ④ connected with the piston ⑤ is closed by the return spring ⑥.

• When valve opens

When pressurized air enters through the port 12(P1), the valve piston moves upward by the pilot air that enters below the piston and the valve element opens.

• When valve closes

When fluid is exhausted from the port 12(P1), the pilot air below the piston is exhausted and the valve element is closed by the return spring.

VND□02□□ (N.O.)

In contrast with the N.C., when air is exhausted from the port 10(P2), the return spring opens the valve element. Pressurized air that enters through the port 10(P2) closes the valve element.

VNA

VNB

SGC

SGH

VNC

VNH


VND

VCC

TQ


Series VND

Port size: 6A, 8A, 10A




Model	Main port 1(A), 2(B)
VND10□D-6A	1/8
VND10□D-8A	1/4
VND10□D-10A	3/8

Port size: 10A, 15A, 20A, 25A




Model	Main port 1(A), 2(B)	A	B	C	D	E	F	G	M	N	P	Q	R	S	T	U
VND20□D-10A	3/8	63	42	28	14	73.5	81.5	4	52	26	4.5	24.3	2.3	25	34	56
VND20□D-15A	1/2	80	50	35	17.5	85	93	5	62	31	5.5	28.3	2.3	30	43	61.5
VND30□D-20A	3/4	90	60	40	20	101	109	6	72	36	6.5	33.3	2.3	35	49	74
VND40□D-25A	1															

Port size: 32A, 40A, 50A



Model	Main port 1(A), 2(B)	Pilot port 12(P1), 10(P2)	A	B	C	D	E	F	G	H	J
VND50□D-32A	1 1/4	1/8	105	77	53	26.5	121.5	20	130.5	8	55
VND60□D-40A	1 1/2	1/4	120	96	60	30	138	24	148	10	63
VND70□D-50A	2	1/4	140	113	74	37	161	24	171	12	74

Port size/Flange: 32F, 40F, 50F



Model	Applicable flange 1(A), 2(B)	Pilot port 12(P1), 10(P2)	A	B	C	D	E	F	G	H	J
VND50□D-32F	32	1/8	130	211.5	135	135	20	100	36	12	8
VND60□D-40F	40	1/4	150	227	140	147	24	105	42	12	10
VND70□D-50F	50	1/4	180	251	155	163.5	24	120	54	14	12

- VNA
- VNB
- SGC
- SGH
- VNC
- VNH
- VND**
- VCC
- TQ



Series VND

Specific Product Precautions

Be sure to read this before handling.
Refer to front matter 41 for Safety Instructions, and pages 17 to 19 for 2 Port Solenoid Valves for Fluid Control Precautions.

External Pilot

⚠ Caution

Pilot port 12(P1) and 10(P2) piping
P1 and P2 piping should be as follows according to the model.

Port	VND□□□D	VND□□O2D
12(P1)	External pilot	Bleed port
10(P2)	Bleed port	External pilot

Installing a silencer to the exhaust port and the bleed port is recommended for noise reduction and for dust entry prevention.

Piping

⚠ Caution

To use the piping with a high temperature fluid, use heat resistant fittings and tubing (Self-align fittings, PTFE tubing or Copper piping, etc.).

Adiabatic Space

⚠ Caution

There is a space between body and cover (*: approximate 1 mm) for adiabatic effect.

