#### New **Electric Rotary Table** Step Motor (Servo/24 VDC) (RoHS) Space-Low saving profile Basic type [mm] Model Н 0 LER10 42 LER30 53 0 Hollow shaft axis LER50 68 Accommodates High precision type [mm] 0 wiring and piping of workpieces. Model Η Т LER10 LERH10 49 Motor built-in LERH30 62 00 Space-saving LERH50 78 1 LER50 Shock-less/High speed actuation Max. speed: 420°/sec (7.33 rad/sec) Max. acceleration/deceleration: 3,000°/sec<sup>2</sup> (52.36 rad/sec<sup>2</sup>) Positioning repeatability: ±0.05°

Repeatability at the end:  $\pm 0.01^{\circ}$  (Pushing control/With external stopper)

### Rotation angle

 $320^\circ$  (310°), 180°, 90°. The value indicated in brackets shows the value for the LER10.

Possible to set speed, acceleration/deceleration, and position. Max. 64 points

## Energy-saving product

Automatic 40% power reduction after the table has stopped.

#### Step Motor (Servo/24 VDC) Controller/Driver

- Step data input type Series LECP6
- 64 points positioning
- Input using controller setting kit or teaching box

## Series LER

Programless type
 Series LECP1
 14 points positioning

Control panel setting



Rotating torque [N·m]

High torque

0.3

1.2

10

\* Value when an external stopper is mounted.

Basic

0.2

0.8

6.6

Size

10

30

50

Pulse input type Series LECPA

Max. speed [°/s]

Basic High torque

280

420



Positioning repeatability [°]

Basic High torque

+0.05

(End: ±0.01)\*



#### **Electric Rotary Table**





#### Easy Mounting of the Main Body



#### With External Stopper/Rotation Angle: 90°/180° Specification





#### Gateway Unit Series LEC-G

Unit linking the LECP6 series and Fieldbus network

Two methods of operation

Step data input: Operate using preset step data in the controller.

Numerical data input: The actuator operates using values such as position and speed from the PLC.



## **ONORMAL Mode for Detailed Setting**

#### Select normal mode when detailed setting is required.

Step data can be set in detail.Signals and terminal status can be monitored.

Parameters can be set.

•JOG and constant rate movement, return to origin, test operation and testing of forced output can be performed.



#### The actuator and controller are provided as a set. (They can be ordered separately.)

Confirm that the combination of the controller and the actuator is correct.

<Check the following before use.>  $\sim$ 

- 1 Check the actuator label for model number. This matches the controller.
- 2 Check Parallel I/O configuration matches (NPN or PNP).







## Programless Type Series LECP1

## No programming

Capable of setting up an electric actuator operation without using a PC or teaching box



## Pulse Input Type Series LECPA

A driver that uses pulse signals to allow positioning at any position. The actuator can be controlled from the customers' positioning unit.



#### Return-to-origin command signal

Enables automatic return-to-origin action.

#### •With force limit function (Pushing force/Gripping force operation available)

Pushing force/Positioning operation possible by switching signals.





#### Series LECP6/LECP1/LECPA

Function					
Item	Step data input type LECP6	Programless type LECP1	Pulse input type LECPA		
Step data and parameter setting	<ul> <li>Input from controller setting software (PC)</li> <li>Input from teaching box</li> </ul>	Select using controller operation     buttons	<ul><li>Input from controller setting software (PC)</li><li>Input from teaching box</li></ul>		
Step data "position" setting	<ul> <li>Input the numerical value from controller setting software (PC) or teaching box</li> <li>Input the numerical value</li> <li>Direct teaching</li> <li>JOG teaching</li> </ul>	<ul><li>Direct teaching</li><li>JOG teaching</li></ul>	<ul> <li>No "position" setting required Position and speed set by pulse signal</li> </ul>		
Number of step data	64 points	14 points	—		
Operation command (I/O signal)	Step No. [IN <sup>*</sup> ] input $\Rightarrow$ [DRIVE] input	Step No. [IN*] input only	Pulse signal		
Completion signal	[INP] output	[OUT*] output	[INP] output		

### **Setting Items**

TB: Teaching box PC: Controller setting software

Item		Contents		asy ode	Normal mode	Step data input type	Pulse input type	Programless type
				PC	TB/PC	LECP6		
	Movement MOD	Selection of "absolute position" and "relative position"	Δ			Set at ABS/INC		Fixed value (ABS)
	Speed	Transfer speed				Set in units of 1°/s		Select from 16-level
	Position	[Position]: Target position [Pushing]: Pushing start position	•	•	•	Set in units of 0.01°	No setting required	Direct teaching JOG teaching
	Acceleration/Deceleration	Acceleration/deceleration during movement			•	Set in units of 1°/s2		Select from 16-level
Step data	Pushing force	Rate of force during pushing operation	•		•	Set in units of 1%	Set in units of 1%	Select from 3-level (weak, medium, strong)
(Excerpt)	Trigger LV	Target force during pushing operation	Δ		•	Set in units of 1%	Set in units of 1%	No setting required (same value as pushing force)
	Pushing speed	Speed during pushing operation	Δ		•	Set in units of 1°/s	Set in units of 1 mm/s	
	Moving force	Force during positioning operation	Δ		•	Set to 100%	Set to (Different values for each actuator)%	
	Area output	Conditions for area output signal to turn ON	Δ		•	Set in units of 0.01°	Set in units of 0.01 mm	
	In position	[Position]: Width to the target position [Pushing]: How much it moves during pushing	Δ	•	•	Set to 0.5° or more (Units: 0.01°)	Set to (Different values for each actuator) or more (Units: 0.01 mm)	No setting required
	Stroke (+)	+ side limit of position	×	×	•	Set in units of 0.01 $^{\circ}$	Set in units of 0.01 mm	
Parameter	Stroke (-)	<ul> <li>side limit of position</li> </ul>	×	×		Set in units of 0.01 $^{\circ}$	Set in units of 0.01 mm	
setting	setting ORIG direction	Direction of the return to origin can be set.	×	×	•	Compatible	Compatible	Compatible
(Excerpt)	ORIG speed	Speed during return to origin position	×	×	•	Set in units of 1°/s	°/s Set in units of 1 mm/s	No sotting required
	ORIG ACC	Acceleration during return to origin position	×	×		Set in units of 1°/s <sup>2</sup>	Set in units of 1 mm/s	No setting required
	JOG		•	•	•	Continuous operation at the set speed can be tested while the switch is being pressed.	Continuous operation at the set speed can be tested while the switch is being pressed.	Hold down MANUAL button (( $\bigcirc$ ) for uniform sending (speed is specified value)
Test	MOVE		×	•	•	Operation at the set distance and speed from the current position can be tested.	Operation at the set distance and speed from the current position can be tested.	Press MANUAL button ((())) once for sizing operation (speed, sizing amount are specified values)
Test	Return to ORIG					Compatible	Compatible	Compatible
	Test drive	Operation of the specified step data	•	•	(Continuous operation)	Compatible	Not compatible	Compatible
	Forced output	ON/OFF of the output terminal can be tested.	×	×		Compatible	Compatible	
Monitor	DRV mon	Current position, speed, force and the specified step data can be monitored.	•	•	•	Compatible	Compatible	Not compatible
Monitor	In/Out mon	Current ON/OFF status of the input and output terminal can be monitored.	×	×	•	Compatible	Compatible	
	Status	Alarm currently being generated can be confirmed.				Compatible	Compatible	Compatible (display alarm group)
	ALM Log record	Alarm generated in the past can be confirmed.	×	×	•	Compatible	Compatible	
File	Save/Load	Step data and parameter can be saved, forwarded and deleted.	×	×	•	Compatible	Compatible	Not compatible
Other	Language	Can be changed to Japanese or English.				Compatible	Compatible	

 $\triangle$ : Can be set from TB Ver. 2.\*\* (The version information is displayed on the initial screen) \* Programless type LECP1 cannot be used with the teaching box and controller setting kit.

**SMC** 

#### System Construction/General Purpose I/O



**SMC** 



#### Series LER

#### **Electric Rotary Table**





#### **SMC Electric Actuators**









**GSMC** 

Features 10

#### **SMC Electric Actuators**



Features 11

Note) (): Long stroke

32 (64)

40 (80)

#### **Controller/Driver**



Driver







Control motor AC servo motor (100/200/400 W)



Control motor AC servo motor (100/200/400 W) CC-Link direct input type Series LECSC (Absolute type)



Control motor AC servo motor (100/200/400 W) SSCNET III type Series LECSS



Control motor AC servo motor (100/200/400 W)

### **Series Variations**

### Electric Rotary Table Series LER



Rotating torque [f		orque [N·m]	Max. speed [°/s]		Positioning repeatability [°]		Controller	Reference
туре	Basic	High torque	Basic	High torque	Basic	High torque	series	page
LER10	0.2	0.3					Series LECP6	
LER30	0.8	1.2	420	280	±0 (End: =	.05 ±0.01)*	Series LECP1	Page 1
LER50	6.6	10					Series LECPA	

\* Value when an external stopper is mounted.

#### Controller/Driver LEC





LECP6



LECPA

Turne Series		Compatible	Power	Paral	Number of	Reference	
туре	Series	motor supply voltage		Input	Output	pattern points	page
Step data input type	LECP6	Step motor (Servo/24 VDC)	24 VDC ±10%	11 inputs (Photo-coupler isolation)	13 outputs (Photo-coupler isolation)	64	Page 15
Programless type	LECP1	Step motor (Servo/24 VDC)	24 VDC ±10%	6 inputs (Photo-coupler isolation)	6 outputs (Photo-coupler isolation)	14	Page 28
Pulse input type	LECPA	Step motor (Servo/24 VDC)	24 VDC ±10%	5 inputs (Photo-coupler isolation)	9 outputs (Photo-coupler isolation)	_	Page 34

# 

Step Motor (Servo/24 VDC)

LER

#### Step Motor (Servo/24 VDC) Type



## Model Selection ..... Page 1 How to Order Page 5 Specifications Page 6

Construction	Page 7
Dimensions	Page 8
Specific Product Precautions	Page 11

#### ○ Step Motor (Servo/24 VDC) Controller/Driver

**©Electric Rotary Table** Series LER

(5)	
Page 15	Step Data Input Type/Series LECP6
	Controller Setting Kit/LEC-W2
	Teaching Box/ <b>LEC-T1</b>
	Gateway Unit/Series LEC-G
1 Page 28	Programless Controller/Series LECP1
	Step Motor Driver/Series LECPA
	Controller Setting Kit/LEC-W2
	Teaching Box/ <b>LEC-T1</b>

Specific Product Precautions LECPA

LECP6





## Series LER



#### Moment of Inertia—Angular Acceleration/Deceleration

#### LER30





#### Effective Torque—Angular Speed



#### LER30



#### LER50 12 10 LER 50K Effective torque: T (N·m) High torque 8 6 4 LER 50J 2 Basic 0 0 100 200 300 400 500 Angular speed: $\omega$ (°/s)



**(**b)

(a)

## Model Selection Series LER

Model Selection

#### Deflection Accuracy: Displacement at 180° Rotation (Guide)



Allowable Load

## **Electric Rotary Table**

Step Motor (Servo/24 VDC)





#### How to Order



Table accuracy					
Nil Basic type					
H High precision type					

#### **5** Motor cable entry



2 Size

10 30 50

#### **≜**Caution

#### [CE-compliant products]

EMC compliance was tested by combining the electric actuator LER series and the controller LEC series.

The EMC depends on the configuration of the customer's control panel and the relationship with other electrical equipment and wiring. Therefore conformity to the EMC directive cannot be certified for SMC components incorporated into the customer's equipment under actual operating conditions. As a result it is necessary for the customer to verify conformity to the EMC directive for the machinery and equipment as a whole.

#### [UL-compliant products]

When conformity to UL is required, the electric actuator and controller/driver should be used with a UL1310 Class 2 power supply.



\* Refer to the operation manual for using the products. Please download it via our website, http://www.smcworld.com

#### Max. rotating torque [N·m]

Symbol	Туре	LER10	LER30	LER50
Κ	High torque	0.3	1.2	10
J	Basic	0.2	0.8	6.6

#### 6 Actuator cable type\*

· ·	
Nil	Without cable
S	Standard cable
R	Robotic cable (Flexible cable)

\* The standard cable should be used on fixed parts. For using on moving parts, select the robotic cable.

#### 8 Controller/Driver type\*1

Nil	Without controller/driver			
6N	LECP6	NPN		
6P	(Step data input type)	PNP		
1N	LECP1	NPN		
1P	(Programless type)	PNP		
AN	LECPA	NPN		
AP	(Pulse input type)	PNP		

\*1 For details about controllers/driver and compatible motors, refer to the compatible controllers/driver below.

#### 4 Rotation angle [°]

Symbol	LER10	LER30	LER50			
Nil	310	320				
2	External stopper: 180					
3	External stopper: 90					
-						

#### Actuator cable length [m]

• · · · · · · · · · · · · · · · · · · ·						
Nil	Without cable	8	8*			
1	1.5	Α	10*			
3	3	В	15*			
5	5	С	20*			

\* Produced upon receipt of order (Robotic cable only) Refer to the specifications Note 3) on page 6.

#### 9 I/O cable length [m]\*1

Nil	Without cable
1	1.5
3	3 <sup>*2</sup>
5	5 <sup>*2</sup>

\*1 When "Without controller/driver" is selected for controller/driver types, I/O cable cannot be selected. Refer to page 21 (For LECP6), page 33 (For LECP1) or page 40 (For LECPA) if I/O cable is required.

\*2 When "Pulse input type" is selected for controller/driver types, pulse input usable only with differential. Only 1.5 m cables usable with open collector.

#### Controller/Driver mounting

 Nil
 Screw mounting

 D
 DIN rail mounting\*

 DIN rail is not included. Order it separately.

(Refer to page 16.)

#### Compatible Controllers/Driver

Туре	Step data input type	Programless type	Pulse input type
Series	LECP6	LECP1	LECPA
Features	Value (Step data) input Standard controller	Capable of setting up operation (step data) without using a PC or teaching box	Operation by pulse signals
Compatible motor	Step motor (Servo/24 VDC)	Step motor (Servo/24 VDC)	
Maximum number of step data 64 points		14 points	—
Power supply voltage		24 VDC	
Reference page Page 15		Page 28	Page 34





- Note 1) Pushing force accuracy is LER10: ±30% (F.S.), LER30: ±25% (F.S.), LER50: ±20% (F.S.).
- Note 2) The angular acceleration, angular deceleration and angular speed may fluctuate due to variations in the inertia moment. Refer to page 3 "Moment of Inertia-Angular Acceleration/

Deceleration, Effective Torque-Angular Speed" graphs for confirmation.

- Note 3) The speed and force may change depending on the cable length, load and mounting conditions. Furthermore, if the cable length exceeds 5 m, then it will decrease by up to 10% for each 5 m. (At 15 m: Reduced by up to 20%)
- Note 4) Impact resistance: No malfunction occurred when the slide table was tested with a drop tester in both an axial direction and a perpendicular direction to the lead screw. (Test was performed with the actuator in the initial state.)

Vibration resistance: No malfunction occurred in a test ranging between 45 to 2000 Hz. Test was performed in both an axial direction and a perpendicular direction to the lead screw. (Test was performed with the actuator in the initial state.)

- Note 5) The power consumption (including the controller) is for when the actuator is operating.
- Note 6) The standby power consumption when operating (including the controller) is for when the actuator is stopped in the set position during operation.
- Note 7) The maximum instantaneous power consumption (including the controller) is for when the actuator is operating. This value can be used for the selection of the power supply.

#### Table Rotation Angle Range



SMC

Note 1) Range within which the table can move when it returns to origin.

Make sure a workpiece mounted on the table does not interfere with the workpieces and facilities around the table.

Note 2) Position after return to origin.

Note 3) The number in brackets indicates when the direction of return to origin has changed.

### Specifications

#### Step Motor (Servo/24 VDC)

	Model		LER 10K	LER 10J	LER 30K	LER 30J	LER 50K	LER□50J		
	Rotation angle [°]		3	310 3		32	20			
	Max.	rotating to	rque [N⋅m]	0.3	0.2	1.2	0.8	10	6.6	
e	Max. pu	ushing torque	e [N·m] Note 1) 3)	0.15	0.1	0.6	0.4	5	3.3	
Ę	Max. moment of inertia [kg·m <sup>2</sup> ] Note 2)		0.0040	0.0018	0.027	0.012	0.10	0.04		
asic	Angular speed [°/sec] Note 2) 3)		20 to 280	30 to 420	20 to 280	30 to 420	20 to 280	30 to 420		
ä	Pushi	ng speed	[°/sec]	20	30	20	30	20	30	
su	Max. angul	ar acceleration/dece	leration [°/sec <sup>2</sup> ] Note 2)		3,000					
atio	Backl	ash [°]				±C	).5			
fica	Positi	oning repe	atability [°]			±0.	.05			
eci	Impact/V	ibration resista	nce [m/s <sup>2</sup> ] Note 4)			150	/30			
r sp	Actua	tion type			Spec	cial worm g	ear + Belt	drive		
ato	Max. o	perating freq	uency [c.p.m]			6	0			
ctu	Operating temp. range [°C]				5 tc	40				
۲	Operat	ing humidity	range [%RH]		90 or less (No condensation)					
	Weial	nt [ka]	Basic type	0.49 1		.1	1 2.2			
			High precision type	0.	0.52 1.2		.2	2.4		
	Rotat	-2/ Botation angle arm (1 pc.)		180						
r type	[°]	-3/ arm (2 pcs.)	90							
stoppe	Repeatability at the end [°]/ with external stopper		±0.01							
al	External stopper setting range [°]		tting range [°]	±2						
terr		-2/external	Basic type	0.55 1.2		.2	2.5			
Ă	Weight	arm (1 pc.)	High precision type	0.	61	1.4		2.7		
	[kg]	-3/external	Basic type	0.	57	1.2		2.6		
		arm (1 pc.)	High precision type	0.	63	1.	1.4		2.8	
suc	Motor	size		□20 □28 □42			42			
atic	Motor	type		Step motor (Servo/24 VDC)						
cific	Enco	der			Incrementa	al A/B phas	e (800 pul:	se/rotation)		
spec	Powe	r supply [\	/]			24 VD0	C±10%			
ic s	Power	consumpti	on [W] Note 5)	1	1	22		34		
ectr	standb when o	y power cons perating [W]	Note 6)	7	7	1	2	1	3	
Ť	Max. instantaneous power consumption [W] Note 7)			1	4	4	2	5	7	

## Series LER

#### Construction



Basic type



#### **Component Parts**

No.	Des	cription	Material	Note			
1	Body		Aluminum alloy	Anodized			
2	Side plate	A	Aluminum alloy	Anodized			
3	Side plate	В	Aluminum alloy	Anodized			
4	Worm scre	w	Stainless steel	Heat treated, specially treated			
5	Worm whe	el	Stainless steel	Heat treated, specially treated			
6	Bearing co	ver	Aluminum alloy	Anodized			
7	Table		Aluminum alloy				
8	Joint		Stainless steel				
9	Bearing holder		Aluminum alloy				
10	Bearing retainer		Aluminum alloy				
11	Home posi	tion bolt	Carbon steel				
12	Pulley A		Aluminum alloy				
13	Pulley B		Aluminum alloy				
14	Grommet		NBR				
15	Motor plate	•	Carbon steel				
16	Basic type	Deep groove ball bearing					
10	High precision type	Special ball bearing	—				
17	Deep groov	e ball bearing	—				
18	Deep groov	e ball bearing	—				
19	Deep groov	e ball bearing					
20	Belt		—				
21	Step motor	(Servo/24 VDC)					

#### External stopper type



#### High precision type



#### **Component Parts**

No.	Description	Material	Note	
22 Table		Aluminum alloy	Anodized	
23 Arm		Carbon steel Heat treated, electroless nickel		
24 Holder		Aluminum alloy	Anodized	
25 Adjuster bolt		Carbon steel	Heat treated, chromate treated	



Dimensions

## Electric Rotary Table Series LER

Model Selection

LER

LECP6

Specific Product Precautions

## Series LER

#### Dimensions



![](_page_24_Figure_0.jpeg)

Dimensions

## Electric Rotary Table Series LER

Model Selection

LER

LECP6

LEC-G

LECP1

LECPA

![](_page_25_Picture_0.jpeg)

## Series LER Electric Rotary Table/ Specific Product Precautions 1

Be sure to read before handling. Refer to back cover for Safety Instructions and the Operation Manual for Electric Actuator Precautions. Please download it via our website, http://www.smcworld.com

**Design/Selection** 

## **M**Warning

1. If the operating conditions involve load fluctuations, ascending/descending movements, or changes in the frictional resistance, ensure that safety measures are in place to prevent injury to the operator or damage to the equipment.

Failure to provide such measures could accelerate the operation speed, which may be hazardous to humans, machinery, and other equipment.

2. Power failure may result in a decrease in the pushing force; ensure that safety measures are in place to prevent injury to the operator or damage to the equipment.

When the product is used for clamping, the clamping force could be decreased due to power failure, potentially creating a hazardous situation in which the workpiece is released.

## **≜**Caution

- If the operating speed is set too fast and the moment of inertia is too large, the product could be damaged. Set appropriate product operating conditions in accordance with the model selection procedure.
- 2. If more precise repeatability of the rotation angle is required, use the product with an external stopper, with repeatability of  $\pm 0.01^{\circ}$  (180° and 90° with adjustment of  $\pm 2^{\circ}$ ) or by directly stopping the workpiece using an external object utilizing the pushing operation.

When using angle adjustment, the initially set rotation angle may change.

3. When using the electric rotary table with an external stopper, or by directly stopping the load externally, ensure that the [Pushing operation] is utilized.

Also, ensure that the workpiece is not impacted externally during the positioning operation or in the range of positioning operation.

Mounting

## **Warning**

1. Do not drop or hit the electric rotary table to avoid scratching and denting the mounting surfaces.

Even slight deformation can cause the deterioration of accuracy and operation failure.

2. Tighten the load mounting screws to the specified torque.

Tightening to a torque greater than the specified range may cause malfunction, and insufficient tightening may cause displacement.

#### Mounting the workpiece to the electric rotary table

The load should be mounted with the torque specified in the following table by screwing the bolt into the mounting female thread.

Model	Bolt	Max. tightening torque [N·m]	
LER□10	M4 x 0.7	1.4	
LER□30	M5 x 0.8	3.0	
LER□50	M6 x 1	5.0	

Mounting

#### **Warning**

## 3. When mounting the electric rotary table, use screws with adequate length and tighten them with adequate torque within the specified torque range.

Tightening the screws with a higher torque than recommended may cause malfunction, whilst the tightening with a lower torque can cause the displacement of the mounting position or in extreme conditions the actuator could become detached from its mounting position.

#### Through-hole mounting

![](_page_25_Figure_29.jpeg)

![](_page_25_Figure_30.jpeg)

Model	Bolt	Max. tightening torque [N·m]	
LER□10	M5 x 0.8	3.0	
LER 30	M6 x 1	5.0	
LER□50	M8 x 1.25	12.0	

#### Body tapped mounting

![](_page_25_Picture_33.jpeg)

Model	Bolt	Max. tightening torque [N·m]	Max. screw-in depth [mm]
LER□10	M6 x 1	5.0	12
LER 30	M8 x 1.25	12.0	16
LER 50	M10 x 1.5	25.0	20

- 4. The mounting face has holes and slots for positioning. Use them for accurate positioning of the electric rotary table if required.
- 5. If it is necessary to operate the electric rotary table when it is not energized, use the manual override screws.

When the product is operated with the manual override screws, check the position of the manual override screws of the product, and leave necessary space. Do not apply excessive torque to the manual override screws that could lead to damage and malfunction of the product.

![](_page_26_Picture_0.jpeg)

## Series LER Electric Rotary Table/ Specific Product Precautions 2

Be sure to read before handling. Refer to back cover for Safety Instructions and the **Operation Manual for Electric Actuator Precautions.** Please download it via our website, http://www.smcworld.com

Handling

## ▲ Caution

1. When an external guide is used, connect it in such a way that no impact or load is applied to it.

Use a free moving connector (such as a coupling).

#### 2. INP output signal

- 1) Positioning operation When the product comes within the set range by step data [In position], the INP output signal will turn on.
  - Initial value: Set to [0.50] or higher.
- 2) Pushing operation

When the effective force exceeds the [Trigger LV] value (including thrust during operation), the INP output signal will turn on.

The [Trigger LV] should be set between 40% and [Pushing force].

- a) To ensure that the clamping and external stop is achieved by [Pushing force], it is recommended that the [Trigger LV] be set to the same value as the [Pushing force].
- b) When the [Pushing force] and [Trigger LV] are set less than the specified range, the INP output signal will turn on from the pushing start position.
- 3. When the workpiece is to be stopped by the electric rotary actuator with an external stopper or directly by an external object, utilize the "pushing operation". Do not stop the table with an external stopper or external object by using in the range of the "positioning operation mode".

If the product is used in the positioning operation mode, there may be galling or other problems when the product/workpiece comes into contact with the external stopper or external object.

4. When the table is stopped by the pushing operation mode (stopping/clamping), set the product to a position of at least 1° away from the workpiece. (This position is referred to as the pushing start position.) If the pushing operations start position (stopping or clamping) is

set to the same position as the external stop position, the following alarms may be generated and operation may become unstable.

- a. "Posn failed" alarm is generated. It is not possible to reach the pushing operation start position within the target time.
- b. "Pushing ALM" alarm is generated.

The product is pushed back from a pushing start position after starting to push.

- c. "Deviation over flow" alarm is generated. Displacement exceeding the specified value is generated at the pushing start position.
- 5. There is no backlash effect when the product is stopped externally by pushing operation. For the return to origin, the origin position is set by the pushing operation.
- 6. For the specification with an external stopper, an angle adjustment bolt is provided as standard.

The rotation angle adjustment range is ±2° from the angle rotation end.

If the angle adjustment range is exceeded, the rotation angle may change due to insufficient strength of the external stopper. One revolution of the adjustment bolt is approximately equal to 1° of rotation.

7. When mounting the product, keep a 40 mm or longer diameter for bends in the cable.

#### Maintenance

### \land Danger

1. The high precision type bearing is assembled by pressing into position. It is not possible to disassemble it.

Step Motor (Servo/24 VDC) ECP6 С С С

LER

Model Selection

![](_page_27_Picture_0.jpeg)

#### Controller (Step Data Input Type) Step Motor (Servo/24 VDC) **cFL**<sup>®</sup> us Series LECP **RoHS** How to Order LECP6N ▲Caution [CE-compliant products] EMC compliance was tested by combining the electric actuator LER series and the Actuator part number controller LEC series. Controller The EMC depends on the configuration of the (Except cable specifications and actuator options) customer's control panel and the relationship Example: Enter "LER10K-2" for the Compatible motor with other electrical equipment and wiring. LER10K-2L-R16N1. Step motor Therefore conformity to the EMC directive Р cannot be certified for SMC components (Servo/24 VDC) incorporated into the customer's equipment Option under actual operating conditions. As a result Number of step data (Points) Nil Screw mounting it is necessary for the customer to verify I/O cable length [m] conformity to the EMC directive for the 6 64 D Note) DIN rail mounting Nil Without cable machinery and equipment as a whole. Note) DIN rail is not included. 1 1.5 [UL-compliant products] Parallel I/O type Order it separately. When conformity to UL is required, the 3 3 Ν NPN electric actuator and controller should be 5 5 Ρ PNP used with a UL1310 Class 2 power supply. \* When controller equipped type is selected when ordering the LE series, you do not need to order this controller. The controller is sold as single unit after the compatible actuator is set. Confirm that the combination of the controller and the actuator is correct. .ER10K-2 <Check the following before use.> NPN ① Check that actuator label for model number. This matches the controller. (2) Check Parallel I/O configuration matches (NPN or PNP). $\widehat{1}$ (2)

\* Refer to the operation manual for using the products. Please download it via our website, http://www.smcworld.com

#### **Specifications**

#### **Basic Specifications**

Item	Specifications
Compatible motor	Step motor (Servo/24 VDC)
Power supply Note 1)	Power voltage: 24 VDC±10% Current consumption: 3 A (Peak 5 A) Note 2) [Including motor drive power, control power, stop, lock release]
Parallel input	11 inputs (Photo-coupler isolation)
Parallel output	13 outputs (Photo-coupler isolation)
Compatible encoder	Incremental A/B phase (800 pulse/rotation)
Serial communication	RS485 (Modbus protocol compliant)
Memory	EEPROM
LED indicator	LED (Green/Red) one of each
Lock control	Forced-lock release terminal Note 3)
Cable length [m]	I/O cable: 5 or less Actuator cable: 20 or less
Cooling system	Natural air cooling
Operating temperature range [°C]	0 to 40 (No freezing)
Operating humidity range [%RH]	90 or less (No condensation)
Storage temperature range [°C]	-10 to 60 (No freezing)
Storage humidity range [%RH]	90 or less (No condensation)
Insulation resistance [M $\Omega$ ]	Between the housing and SG terminal 50 (500 VDC)
Weight [g]	150 (Screw mounting) 170 (DIN rail mounting)

Note 1) Do not use the power supply of "inrush current prevention type" for the controller power supply. When conformity to UL is required, the electric actuator and controller should be used with a UL1310 Class 2 power supply.

Note 2) The power consumption changes depending on the actuator model. Refer to the specifications of actuator for more details. Note 3) Applicable to non-magnetizing lock.

## Controller (Step Data Input Type)/Step Motor (Servo/24 VDC) Series LECP6

![](_page_29_Figure_2.jpeg)

#### **DIN rail mounting adapter** LEC-D0 (with 2 mounting screws)

This should be used when the DIN rail mounting adapter is mounted onto the screw mounting type controller afterwards.

**SMC** 

## Series LECP6

#### Dimensions

![](_page_30_Figure_2.jpeg)

35 <u>ø4</u>.5 for body 31 Power supply LED (Green) mounting (ON: Power supply is ON.)  $\overline{\bigcirc}$ Power supply LED (Red) (ON: Alarm is ON.) OSUC MIL CN5 parallel I/O connector ᄞ CN4 serial I/O connector 132 150 141 CN3 encoder connector CN2 motor power connector CN1 power supply connector 4.6 for body mounting

![](_page_30_Figure_4.jpeg)

#### b) DIN rail mounting (LECP6 D-D-)

![](_page_30_Figure_6.jpeg)

![](_page_30_Figure_7.jpeg)

## Controller (Step Data Input Type)/Step Motor (Servo/24 VDC) Series LECP6

#### Wiring Example 1

**Power Supply Connector: CN1** \* Power supply plug is an accessory.

#### CN1 Power Supply Connector Terminal for LECP6 (PHOENIX CONTACT FK-MC0.5/5-ST-2.5)

Terminal name	Function	Details
0V	Common supply (-)	M24V terminal/C24V terminal/EMG terminal/BK RLS terminal are common (–).
M24V	Motor power supply (+)	Motor power supply (+) supplied to the controller
C24V	Control power supply (+)	Control power supply (+) supplied to the controller
EMG	Stop (+)	Input (+) for releasing the stop
BK RLS	Lock release (+)	Input (+) for releasing the lock

#### Power supply plug for LECP6

Model Selection

Step Motor (Servo/24 VDC) LER

LECP6

LEC-G

LECP1

LECPA

![](_page_31_Figure_6.jpeg)

#### Wiring Example 2

**Parallel I/O Connector: CN5** \* When you connect a PLC, etc., to the CN5 parallel I/O connector, please use the I/O cable (LEC-CN5-□). \* The wiring should be changed depending on the type of the parallel I/O (NPN or PNP).

#### Wiring diagram

,			Power supply 24 VDC
	CN5		for I/O signal
	COM+	A1	┝────╇─┤┝─┐
	COM-	A2	<b>├</b> ─── <b>├</b>
	IN0	A3	
	IN1	A4	
	IN2	A5	
	IN3	A6	
	IN4	A7	
	IN5	A8	
	SETUP	A9	
	HOLD	A10	
	DRIVE	A11	
	RESET	A12	
	SVON	A13	
	OUT0	B1	Load
	OUT1	B2	Load
	OUT2	B3	Load
	OUT3	B4	Load
	OUT4	B5	Load
	OUT5	B6	Load
	BUSY	B7	Load
	AREA	B8	Load
	SETON	B9	Load
	INP	B10	Load
	SVRE	B11	Load
	*ESTOP	B12	Load
	*ALARM	B13	Load

#### 

,		Power supply 24 VDC
CN5		for I/O signal
COM+	A1	╞────╋─┤┝╌┐
COM-	A2	<u>}</u>
IN0	A3	
IN1	A4	
IN2	A5	
IN3	A6	
IN4	A7	
IN5	A8	
SETUP	A9	
HOLD	A10	
DRIVE	A11	
RESET	A12	
SVON	A13	
OUT0	B1	Load
OUT1	B2	Load
OUT2	B3	Load
OUT3	B4	Load
OUT4	B5	Load
OUT5	B6	Load
BUSY	B7	Load
AREA	B8	Load
SETON	B9	Load
INP	B10	Load
SVRE	B11	Load
*ESTOP	B12	Load
*ALARM	B13	Load

#### Input Signal

Name	Details	
COM+	Connects the power supply 24 V for input/output signal	
COM-	Connects the power supply 0 V for input/output signal	
IN0 to IN5	Step data specified Bit No.	
	(Input is instructed in the combination of IN0 to 5.)	
SETUP	Instruction to return to origin	
HOLD	Operation is temporarily stopped	
DRIVE	Instruction to drive	
RESET	Alarm reset and operation interruption	
SVON	Servo ON instruction	

Output Signal		
Name	Details	
OUT0 to OUT5	Outputs the step data no. during operation	
BUSY	Outputs when the actuator is moving	
AREA	Outputs within the step data area output setting range	
SETON	Outputs when returning to origin	
INP	Outputs when target position or target force is reached (Turns on when the positioning or pushing is completed.)	
SVRE	Outputs when servo is on	
*ESTOP Note)	Not output when EMG stop is instructed	
*ALARM Note)	Not output when alarm is generated	
Note) Signal of p	agative legis sireuit ON (N C)	

Note) Signal of negative-logic circuit ON (N.C.)

**SMC** 

## Series LECP6

#### Step Data Setting

#### 1. Step data setting for positioning

In this setting, the actuator moves toward and stops at the target position.

The following diagram shows the setting items and operation. The setting items and set values for this operation are stated below.

![](_page_32_Figure_5.jpeg)

◎: Need to be set.
○: Need to be adjusted as required.
-: Setting is not required.

**SMC** 

Step Data (Positioning)

Necessity	Item	Details
0	Movement MOD	When the absolute position is required, set Absolute. When the relative position is required, set Relative.
0	Speed	Transfer speed to the target position
0	Position	Target position
0	Acceleration	Parameter which defines how rapidly the actuator reaches the speed set. The higher the set value, the faster it reaches the speed set.
0	Deceleration	Parameter which defines how rapidly the actuator comes to stop. The higher the set value, the quicker it stops.
0	Pushing force	Set 0. (If values 1 to 100 are set, the operation will be changed to the pushing operation.)
_	Trigger LV	Setting is not required.
_	Pushing speed	Setting is not required.
0	Moving force	Max. torque during the positioning operation (No specific change is required.)
0	Area 1, Area 2	Condition that turns on the AREA output signal.
0	In position	Condition that turns on the INP output signal. When the actuator enters the range of [in position], the INP output signal turns on. (It is unnecessary to change this from the initial value.) When it is necessary to output the arrival signal before the operation is completed, make the value larger.

#### 2. Step data setting for pushing

The actuator moves toward the pushing start position, and when it reaches that position, it starts pushing with the set force or less.

The following diagram shows the setting items and operation. The setting items and set values for this operation are stated below.

![](_page_32_Figure_12.jpeg)

Step	Data (Pushing)	$\bigcirc$ : Need to be set. $\bigcirc$ : Need to be adjusted as required.
Necessity	Item	Details
Ø	Movement MOD	When the absolute position is required, set Absolute. When the relative position is required, set Relative.
O	Speed	Transfer speed to the pushing start position
O	Position	Pushing start position
0	Acceleration	Parameter which defines how rapidly the actuator reaches the speed set. The higher the set value, the faster it reaches the speed set.
0	Deceleration	Parameter which defines how rapidly the actuator comes to stop. The higher the set value, the quicker it stops.
O	Pushing force	Pushing force ratio is defined. The setting range differs depending on the electric actuator type. Refer to the operation manual for the electric actuator.
Ø	Trigger LV	Condition that turns on the INP output signal. The INP output signal turns on when the generated force exceeds the value. Trigger level should be the pushing force or less.
0	Pushing speed	Pushing speed during pushing. When the speed is set fast, the electric actuator and workpieces might be damaged due to the impact when they hit the end, so this set value should be smaller. Refer to the operation manual for the electric actuator.
0	Moving force	Max. torque during the positioning operation (No specific change is required.)
0	Area 1, Area 2	Condition that turns on the AREA output signal.
O	In position	Transfer distance during pushing. If the transferred distance exceeds the setting, it stops even if it is not pushing. If the transfer distance is exceeded, the INP output signal will not turn on.

## Controller (Step Data Input Type)/Step Motor (Servo/24 VDC) Series LECP6

# Model Selection

Step Motor (Servo/24 VDC)

LER

LECP6

LECP1

LECPA

ON

OFF

•

.

ON

OFF

. .

0 mm/s

ON

OFF

ON

OFF

ON

OFF

## **Signal Timing**

![](_page_33_Figure_3.jpeg)

20

## Series LECP6

#### **Options: Actuator Cable, I/O Cable**

#### Actuator cable

![](_page_34_Figure_3.jpeg)

![](_page_34_Figure_4.jpeg)

Α

B

A-5 B-6

A-6

#### I/O cable

LE	<b>C</b> -	-CN5-1	
Cable length (L) [m] ●			
	1	1.5	
	3	3	
	5	5	

![](_page_34_Figure_7.jpeg)

Connector	Insulation	Dot	Dot
pin no.	color	mark	color
A1	Light brown		Black
A2	Light brown		Red
A3	Yellow		Black
A4	Yellow		Red
A5	Light green		Black
A6	Light green		Red
A7	Gray		Black
A8	Gray		Red
A9	White		Black
A10	White		Red
A11	Light brown		Black
A12	Light brown		Red
A13	Yellow		Black

Connector	Insulation	Dot	Dot
pin no.	color	mark	color
B1	Yellow		Red
B2	Light green		Black
B3	Light green		Red
B4	Gray		Black
B5	Gray		Red
B6	White		Black
B7	White		Red
B8	Light brown		Black
B9	Light brown		Red
B10	Yellow		Black
B11	Yellow		Red
B12	Light green		Black
B13	Light green		Red
_		Shield	

Black

Red

Black

Orange Black

13

6

\* Conductor size: AWG28

![](_page_35_Figure_0.jpeg)

## Hardware Requirements

OS	IBM PC/AT compatible machine running Windows <sup>®</sup> XP (32-bit), Windows <sup>®</sup> 7 (32-bit and 64-bit).
Communication interface	USB 1.1 or USB 2.0 ports
Display	XGA (1024 x 768) or more

\* Windows® and Windows®7 are registered trademarks of Microsoft Corporation in the United States.

\* Refer to SMC website for version update information, http://www.smcworld.com

#### Screen Example

#### Easy mode screen example

![](_page_35_Figure_7.jpeg)

#### Easy operation and simple setting

- Allowing to set and display actuator step data such as position, speed, force, etc.
- Setting of step data and testing of the drive can be performed on the same page.
- Can be used to jog and move at a constant rate.

#### Normal mode screen example

![](_page_35_Picture_13.jpeg)

#### **Detailed setting**

- Step data can be set in detail.
- Signals and terminal status can be monitored.
- Parameters can be set.
- JOG and constant rate movement, return to origin, test operation and testing of forced output can be performed.

![](_page_35_Picture_19.jpeg)

LECP1

LECPA

Specific Product Precautions

## Series LEC Teaching Box/LEC-T1

![](_page_36_Picture_1.jpeg)

![](_page_36_Picture_2.jpeg)

![](_page_36_Figure_3.jpeg)

![](_page_36_Figure_4.jpeg)

\* The displayed language can be changed to English or Japanese.

#### **Specifications**

Standard functions	Switch
<ul> <li>Chinese character display</li> </ul>	Cable length [m]
• Stop switch is provided	g[]

• Stop switch is provided.

#### Option

• Enable switch is provided.

Item	Description
Switch	Stop switch, Enable switch (Option)
Cable length [m]	3
Enclosure	IP64 (Except connector)
Operating temperature range [°C]	5 to 50
Operating humidity range [%RH]	90 or less (No condensation)
Weight [g]	350 (Except cable)

**[CE-compliant products]** The EMC compliance of the teaching box was tested with the LECP6 series step motor controller (servo/24 VDC) and an applicable actuator.

**[UL-compliant products]** When conformity to UL is required, the electric actuator and controller should be used with a UL1310 Class 2 power supply.

#### Easy Mode

Function	Details
Step data	<ul> <li>Setting of step data</li> </ul>
Jog	<ul><li>Jog operation</li><li>Return to origin</li></ul>
Test	<ul><li> 1 step operation</li><li> Return to origin</li></ul>
Monitor	<ul> <li>Display of axis and step data no.</li> <li>Display of two items selected from Position, Speed, Force.</li> </ul>
ALM	<ul><li>Active alarm display</li><li>Alarm reset</li></ul>
TB setting	<ul> <li>Reconnection of axis</li> <li>Setting of easy/normal mode</li> <li>Setting step data and selection of items from easy mode monitor</li> </ul>

#### Menu Operations Flowchart

![](_page_36_Figure_17.jpeg)

## Teaching Box Series LEC

Normal Mode

Function	Details
Step data	Step data setting
Parameter	Parameters setting
Test	<ul> <li>Jog operation/Constant rate movement</li> <li>Return to origin</li> <li>Test drive (Specify a maximum of 5 step data and operate.)</li> <li>Forced output (Forced signal output, Forced terminal output)</li> </ul>
Monitor	<ul> <li>Drive monitor</li> <li>Output signal monitor</li> <li>Input signal monitor</li> <li>Output terminal monitor</li> <li>Input terminal monitor</li> </ul>
ALM	<ul> <li>Active alarm display (Alarm reset)</li> <li>Alarm log record display</li> </ul>
File	<ul> <li>Data saving Save the step data and parameters of the controller which is being used for communication (it is possible to save four files, with one set of step data and parameters defined as one file).</li> <li>Load to controller Loads the data which is saved in the teaching box to the controller which is being used for commu- nication.</li> <li>Delete the saved data.</li> </ul>
TB setting	<ul> <li>Display setting (Easy/Normal mode)</li> <li>Language setting (Japanese/English)</li> <li>Backlight setting</li> <li>LCD contrast setting</li> <li>Beep sound setting</li> <li>Max. connection axis</li> <li>Distance unit (mm/inch)</li> </ul>
Reconnect	Reconnection of axis

Menu

Step data Parameter

Monitor

TB setting

Reconnect

Test

ALM

File

#### Model Selection Menu Operations Flowchart Step data Step data no. Movement MOD Speed Position Acceleration Deceleration Pushing force Step Motor (Servo/24 VDC) Trigger LV Pushing speed LER Moving force Area 1, 2 In position Parameter **Basic setting** Basic **ORIG** setting ORIG Monitor **DRV** monitor Position, Speed, Torque Drive Output signal Step no. Input signal Last step no. Output terminal Output signal monitor Input terminal Input signal monitor **LECP6** Test JOG/MOVE Output terminal monitor Return to ORIG Test drive Input terminal monitor Forced output ALM Status Active alarm display LEC-G Status ALM Log record Alarm reset ALM Log record display File Log entry display Data saving Load to controller File deletion **TB** setting LECP1 Easy/Normal Language Backlight LCD contrast Веер Max. connection axis Password LECPA Distance unit Reconnect

#### Dimensions

![](_page_37_Figure_5.jpeg)

No.	Description	Function				
1	LCD	A screen of liquid crystal display (with backlight)				
2	Ring	ng A ring for hanging the teaching box				
3	Stop switchWhen switch is pushed in, the switch locks and stops The lock is released when it is turned to the right.					
4	Stop switch guard	A guard for the stop switch				
5	Enable switch (Option)	Prevents unintentional operation (unexpected operation) of the jog test function. Other functions such as data change are not covered.				
6	Key switch	Switch for each input				
7	Cable	Length: 3 meters				
8	Connector	A connector connected to CN4 of the controller				

**SMC** 

#### 24

Specific Product Precautions

## Gateway Unit Series LEC-G ( E BUS RoHS

#### How to Order

#### **≜**Caution

[CE-compliant products] EMC compliance was tested by combining the electric actuator LER series and the controller LEC series.

The EMC depends on the configuration of the customer's control panel and the relationship with other electrical equipment and wiring. Therefore conformity to the EMC directive cannot be certified for SMC components incorporated into the customer's equipment under actual operating conditions. As a result it is necessary for the customer to verify conformity to the EMC directive for the machinery and equipment as a whole.

**[UL-compliant products]** When conformity to UL is required, the electric actuator and controller should be used with a UL1310 Class 2 power supply.

#### Specifications

	Gatev	vay unit			
	Applicable	Fieldbus protocols	Mounting •		l
;	DN1	DeviceNet <sup>™</sup>	Nil Screw mounting		ł
-	PR1	PROFIBUS DP	D <sup>Note)</sup> DIN rail mounting		l
-	EN1	EtherNet/IP™	Note) DIN rail is not included. Order it separately.		1
	Ca	able	EC-CG1-L		
r I		Ca 1 Comm 2 Cable	able type  unication cable between branches K 0.3 m	3	
; /			L 0.5 m 1 1 m	Communication cable	
- r	Branch	connector	EC - CGD		
	Terminat	ting resistor	EC-CGR	Cable between branches 🤎	

	Model		LEC-	GMJ2□	LEC-GDN1	LEC-GPR1	LEC-GEN1		
	Applicable	Fieldbus	CC	C-Link	DeviceNet™	PROFIBUS DP	EtherNet/IP™		
	system	Version Note 1)	Ve	r. 2.0	Release 2.0	V1	Release 1.0		
	Communicat	ion speed [bps]	156 k/625 k/2.5 M/ 5 M/10 M		125 k/250 k/500 k	9.6 k/19.2 k/45.45 k/ 93.75 k/187.5 k/500 k/ 1.5 M/3 M/6 M/12 M	10 M/100 M		
	Configuratio	n file Note 2)		_	EDS file	GSD file	EDS file		
Communication specifications	I/O occupation area		4 stations occupied (8 times setting)	Input 896 points 108 words Output 896 points 108 words	Input 200 bytes Output 200 bytes	Input 57 words Output 57 words	Input 256 bytes Output 256 bytes		
	Power supply for	Power supply voltage [V] Note 6)		_	11 to 25 VDC	—	_		
	communication	Internal current consumption [mA]	_		100	—	_		
	Communication connector specifications		Connector (Accessory)		Connector (Accessory)	D-sub	RJ45		
	Terminating resistor		Not included		Not included	Not included	Not included		
Power supply voltage	ge [V] Note 6)		24 VDC±10%						
Current	Not connecte	ed to teaching box	200						
consumption [mA]	Connected to	o teaching box	300						
EMG output termina	l		30 VDC 1A						
Controller	Applicable c	ontrollers	Series LECP6, Series LECA6						
specifications	Communication	on speed [bps] Note 3)			115.2 k/	230.4 k			
	Max. number of co	onnectable controllers Note 4)		12	8 Note 5)	5	12		
Accessories			Power sup	ply connector,	communication connector	Power suppl	y connector		
Operating temperature range [°C]			0 to 40 (No freezing)						
Operating humidity range [%RH]			90 or less (No condensation)						
Storage temperature	e range [°C]		-10 to 60 (No freezing)						
Storage humidity ra	nge [%RH]		90 or less (No condensation)						
Weight [g]					200 (Screw mounting),	220 (DIN rail mounting)			

Note 1) Please note that the version is subject to change.

Note 2) Each file can be downloaded from the SMC website, http://www.smcworld.com

Note 3) When using a teaching box (LEC-T1-D), set the communication speed to 115.2 kbps.

Note 4) A communication response time for 1 controller is approximately 30 ms.

Refer to "Communication Response Time Guideline" for response times when several controllers are connected.

Note 5) For step data input, up to 12 controllers connectable.

Note 6) When conformity to UL is required, the electric actuator and controller should be used with a UL1310 Class 2 power supply.

![](_page_38_Picture_16.jpeg)

## Gateway Unit Series LEC-G

# Model Selection

Step Motor (Servo/24 VDC)

LER

LECP6

С С С

LECP1

LECPA

Specific Product Precautions

1

#### **Communication Response Time Guideline**

Response time between gateway unit and controllers depends on the number of controllers connected to the gateway unit. For response time, refer to the graph below.

![](_page_39_Figure_4.jpeg)

\* This graph shows delay times between gateway unit and controllers. Fieldbus network delay time is not included.

#### Dimensions

#### Screw mounting (LEC-G

#### Applicable Fieldbus protocol: CC-Link Ver. 2.0

![](_page_39_Figure_9.jpeg)

#### Applicable Fieldbus protocol: PROFIBUS DP

![](_page_39_Figure_11.jpeg)

#### Applicable Fieldbus protocol: DeviceNet™

![](_page_39_Figure_13.jpeg)

#### Applicable Fieldbus protocol: EtherNet/IP™

04.5 For body mounting

ig For b

SMC

■Trademark DeviceNet<sup>™</sup> is a trademark of ODVA. EtherNet/IP<sup>™</sup> is a trademark of ODVA.

## Series LEC-G

#### Dimensions

#### DIN rail mounting (LEC-G

#### Applicable Fieldbus protocol: CC-Link Ver. 2.0

![](_page_40_Figure_4.jpeg)

![](_page_40_Figure_6.jpeg)

#### **DIN rail** AXT100-DR-

\* For  $\Box$ , enter a number from the "No." line in the table below. Refer to the dimensions above for the mounting dimensions.

#### Applicable Fieldbus protocol: DeviceNet<sup>™</sup>

![](_page_40_Figure_10.jpeg)

#### Applicable Fieldbus protocol: EtherNet/IP™

![](_page_40_Figure_12.jpeg)

\* Mountable on DIN rail (35 mm)

64.2

В

#### L 12.5 (Pitch) 5.25 $\phi \phi \phi \phi \phi$ 5.5 1.25

#### L Dimension [mm]

No.	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L	23	35.5	48	60.5	73	85.5	98	110.5	123	135.5	148	160.5	173	185.5	198	210.5	223	235.5	248	260.5
No.	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40
L	273	285.5	298	310.5	323	335.5	348	360.5	373	385.5	398	410.5	423	435.5	448	460.5	473	485.5	498	510.5

■Trademark DeviceNet<sup>™</sup> is a trademark of ODVA. EtherNet/IP<sup>™</sup> is a trademark of ODVA. **SMC** 

# Programless Controller Series LECP1

How to Order

![](_page_41_Figure_2.jpeg)

#### Caution

#### [CE-compliant products]

EMC compliance was tested by combining the electric actuator LER series and the controller LEC series. The EMC depends on the configuration of the customer's control panel and the relationship with other electrical equipment and wiring. Therefore conformity to the EMC directive cannot be certified for SMC components incorporated into the customer's equipment under actual operating conditions. As a result it is necessary for the customer to verify conformity to the EMC directive for the machinery and equipment as a whole.

[UL-compliant products]

When conformity to UL is required, the electric actuator and controller should be used with a UL1310 Class 2 power supply.

The controller is sold as single unit after the compatible actuator is set. Confirm that the combination of the controller and the actuator is correct.

**RoHS** 

Model Selection

LER

LECP6

LECP1

LECPA

Specific Product Precautions

\* Refer to the operation manual for using the products. Please download it via our website, http://www.smcworld.com

#### Specifications

#### **Basic Specifications**

Item	LECP1
Compatible motor	Step motor (Servo/24 VDC)
Power supply Note 1)	Power supply voltage: 24 VDC ±10%, Max. current consumption: 3A (Peak 5A) Note 2) [Including the motor drive power, control power supply, stop, lock release]
Parallel input	6 inputs (Photo-coupler isolation)
Parallel output	6 outputs (Photo-coupler isolation)
Stop points	14 points (Position number 1 to 14(E))
Compatible encoder	Incremental A/B phase (800 pulse/rotation)
Serial communication	RS485 (Modbus protocol compliant)
Memory	EEPROM
LED indicator	LED (Green/Red) one of each
7-segment LED display Note 3)	1 digit, 7-segment display (Red) Figures are expressed in hexadecimal ("10" to "15" in decimal number are expressed as "A" to "F")
Lock control	Forced-lock release terminal Note 4)
Cable length [m]	I/O cable: 5 or less, Actuator cable: 20 or less
Cooling system	Natural air cooling
Operating temperature range [°C]	0 to 40 (No freezing)
Operating humidity range [%RH]	90 or less (No condensation)
Storage temperature range [°C]	-10 to 60 (No freezing)
Storage humidity range [%RH]	90 or less (No condensation)
Insulation resistance [M $\Omega$ ]	Between the housing and SG terminal: 50 (500 VDC)
Weight [g]	130 (Screw mounting), 150 (DIN rail mounting)

Note 1) Do not use the power supply of "inrush current prevention type" for the controller input power supply. When conformity to UL is required, the electric actuator and controller should be used with a UL1310 Class 2 power supply.

Note 2) The power consumption changes depending on the actuator model. Refer to the each actuator's operation manual etc. for details.

Note 3) "10" to "15" in decimal number are displayed as follows in the 7-segment LED.

![](_page_41_Figure_16.jpeg)

Note 4) Applicable to non-magnetizing lock.

## Series LECP1

#### **Controller Details**

![](_page_42_Figure_2.jpeg)

No.	Display	Description	Details		
1	PWR	Power supply LED	Power supply ON/Servo ON : Green turns on Power supply ON/Servo OFF: Green flashes		
2	ALM	Alarm LED	With alarm: Red turns onParameter setting: Red flashes		
3	-	Cover	Change and protection of the mode switch (Close the cover after changing switch)		
4	) — FG		Frame ground (Tighten the bolt with the nut when mounting the controller. Connect the ground wire.)		
(5)	_	Mode switch	Switch the mode between manual and auto.		
6		7-segment LED	Stop position, the value set by $(\ensuremath{\$})$ and alarm information are displayed.		
$\bigcirc$	SET	Set button	Decide the settings or drive operation in Manual mode.		
8		Position selecting switch	Assign the position to drive (1 to 14), and the origin position (15).		
9	ΜΑΝΠΑΙ	Manual forward button	Perform forward jog and inching.		
10	MANUAL	Manual reverse button	Perform reverse jog and inching.		
1	ODEED	Forward speed switch	16 forward speeds are available.		
12	SPEED	Reverse speed switch	16 reverse speeds are available.		
(13)		Forward acceleration switch	16 forward acceleration steps are available.		
14	ACCEL	Reverse acceleration switch	16 reverse acceleration steps are available.		
(15)	CN1	Power supply connector	Connect the power supply cable.		
(16)	CN2	Motor connector	Connect the motor connector.		
17	CN3	Encoder connector	Connect the encoder connector.		
(18)	CN4	I/O connector	Connect I/O cable.		

#### How to Mount

Controller mounting shown below.

![](_page_42_Figure_6.jpeg)

#### 2. Grounding

Tighten the bolt with the nut when mounting the ground wire as shown below.

![](_page_42_Figure_9.jpeg)

Note) When sizes 30 or 50 of the LER series are used, the space between the controllers should be 10 mm or more.

### ▲Caution

- •M4 screws, cable with crimping terminal and tooth lock washer are not included. Be sure to carry out grounding earth in order to ensure the noise tolerance.
- •Use a watchmaker's screwdriver of the size shown below when changing position switch 8 and the set value of the speed/acceleration switch 1 to 4.

Size End width L: 2.0 to 2.4 [mm] End thickness W: 0.5 to 0.6 [mm]

Magnified view of the end of the screwdriver

SMC

![](_page_42_Picture_16.jpeg)

## Programless Controller Series LECP1

![](_page_43_Figure_1.jpeg)

**SMC** 

#### DIN rail mounting (LEC 1 D-)

![](_page_43_Figure_3.jpeg)

![](_page_43_Figure_4.jpeg)

30

LECPA

Specific Product Precautions

## Series LECP1

#### Wiring Example 1

st When you connect a CN1 power supply connector, please use the power supply cable (LEC-CK1-1). Power Supply Connector: CN1 \* Power supply cable (LEC-CK1-1) is an accessory.

#### **CN1 Power Supply Connector Terminal for LECP1**

Terminal name	Cable color	Function	Details
٥V	Blue	Common supply (–)	M24V terminal/C24V terminal/BK RLS terminal are common (–).
M24V	White	Motor power supply (+)	Motor power supply (+) supplied to the controller
C24V	Brown	Control power supply (+)	Control power supply (+) supplied to the controller
	Diagle		Input ( ) for releasing the look

BK RLS Black Lock release (+) Input (+) for releasing the lock

#### Wiring Example 2

**Parallel I/O Connector: CN4** \* When you connect a PLC, etc., to the ON4 parallel I/O connector, please doe and the area of the parallel I/O (NPN or PNP). \* When you connect a PLC, etc., to the CN4 parallel I/O connector, please use the I/O cable (LEC-CK4-□).

#### 

![](_page_44_Figure_9.jpeg)

#### PNP

		Power supply 24 VDC
CN4		for I/O signal
COM+	1	╞────╋─┤┝╌┐
COM-	2	
OUT0	3	Load
OUT1	4	Load
OUT2	5	Load
OUT3	6	Load
BUSY	7	Load
ALARM	8	Load
IN0	9	
IN1	10	⊢́•
IN2	11	
IN3	12	⊢́∕→
RESET	13	⊢́∕–•́
STOP	14	F

Power supply cable for LECP1 (LEC-CK1-1)

#### Input Signal

Name		Details					
COM+	Conne	Connects the power supply 24 V for input/output signal					
COM-	Conne	cts the powe	er supply 0 \	/ for input/ou	utput signal		
	• Instru	uction to drive	e (input as a o	combination of	of IN0 to IN3)		
	<ul> <li>Instru</li> </ul>	ction to return	to origin (IN0 t	o IN3 all ON s	imultaneously)		
IN0 to IN3	Example - (instruction to drive for position no. 5)						
		IN3	IN2	IN1	IN0		
		OFF	ON	OFF	ON		
	Alarm reset and operation interruption						
DEGET	During operation: deceleration stop from position at which						
RESET		s	signal is input	(servo ON m	aintained)		
	While	e alarm is ac	tive: alarm r	eset			
STOP	Instructi	on to stop (afte	er maximum de	eceleration sto	p, servo OFF)		

Input Signal [IN0 - IN3] Position Number Chart O: OFF •: ON										
Position number	IN3	IN2	IN1	IN0						
1	0	0	0							
2	0	0	•	0						
3	0	0	•							
4	0	•	0	0						
5	0	•	0							
6	0	•	•	0						
7	0	•	•							
8	•	0	0	0						
9	•	0	0							
10 (A)	•	0	•	0						
11 (B)	•	0	•							
12 (C)	•	•	0	0						
13 (D)	•	•	0							
14 (E)	•	•	•	0						
Retun to origin	•	•	•							

#### **Output Signal**

**SMC** 

Name		Details					
OUT0 to OUT3	Turns on when the positioning or pushing is completed. (Output is instructed in the combination of OUT0 to 3.) Example - (operation complete for position no. 3)						
		OUT3 OFF	OUT2 OFF	OUT1 ON	OUT0 ON		
BUSY	Output	Outputs when the actuator is moving					
*ALARM Note)	Not ou	tput when al	arm is active	e or servo O	FF		

Note) Signal of negative-logic circuit (N.C.)

Output Signal [OUT0 - OUT3] Position Number Chart O: OFF O: ON								
Position number	OUT3	OUT2	OUT1	OUT0				
1	0	0	0					
2	0	0	•	0				
3	0	0	•					
4	0		0	0				
5	0		0					
6	0		•	0				
7	0		•	•				
8	•	0	0	0				
9	•	0	0	•				
10 (A)	•	0	•	0				
11 (B)	•	0	•	•				
12 (C)	•		0	0				
13 (D)	•		0					
14 (E)	•	•	•	0				
Retun to origin	•		•	•				

# Model Selection

![](_page_45_Figure_8.jpeg)

![](_page_45_Figure_9.jpeg)

![](_page_45_Figure_10.jpeg)

\* "\*ALARM" is expressed as negative-logic circuit.

#### (2) Positioning Operation

![](_page_45_Figure_13.jpeg)

#### (3) Cut-off Stop (Reset Stop)

![](_page_45_Figure_15.jpeg)

#### (4) Stop by the STOP Signal

![](_page_45_Figure_17.jpeg)

#### (5) Alarm Reset

![](_page_45_Figure_19.jpeg)

"\*ALARM" is expressed as negative-logic circuit.

![](_page_45_Picture_21.jpeg)

## Series LECP1

#### **Options: Actuator Cable**

![](_page_46_Figure_2.jpeg)

#### Options

#### [Power supply cable]

![](_page_46_Figure_5.jpeg)

White

Light brown

Light brown

Yellow

Yellow

IN1

IN2

IN3

RESET

STOP

Red

Black

Red

Black

Red

10

11

12

13

14

\* Parallel I/O signal is valid in auto mode. While the test function operates at manual mode, only the output is valid.

OUT0

OUT1

OUT2

OUT3

BUSY

Black

Red

Black

Red

Black

![](_page_46_Picture_7.jpeg)

3

4

5

6

7

Yellow

Yellow

Light green

Light green

Gray

# Step Motor Driver

## How to Order

#### **≜**Caution

- [CE-compliant products] ① EMC compliance was tested by combining the electric actuator LER series and the LECPA series. The EMC depends on the configuration of the customer's control panel and the relationship with other electrical equipment and wiring. Therefore conformity to the EMC directive cannot be
- to the EMC directive cannot be certified for SMC components incorporated into the customer's equipment under actual operating conditions. As a result it is necessary for the customer to verify conformity to the EMC directive for the machinery and equipment as a whole.
- ② For the LECPA series (step motor driver), EMC compliance was tested by installing a noise filter set (LEC-NFA). Refer to page 40 for the noise filter set. Refer to the LECPA Operation Manual for installation.

[UL-compliant products] When conformity to UL is required, the electric actuator and driver should be used with a UL1310 Class 2 power supply.

![](_page_47_Figure_7.jpeg)

## Confirm that the combination of the driver and the actuator is correct.

#### <Check the following before use.>

- ① Check the actuator label for model number. This matches the driver.
- ② Check Parallel I/O configuration matches (NPN or PNP).

![](_page_47_Figure_12.jpeg)

\* Refer to the operation manual for using the products. Please download it via our website, http://www.smcworld.com

#### Specifications

Item	LECPA
Compatible motor	Step motor (Servo/24 VDC)
	Power voltage: 24 VDC ±10%
Power supply Note 1)	Maximum current consumption: 3 A (Peak 5 A) Note 2)
	[Including motor drive power, control power, stop, lock release]
Parallel input	5 inputs (Except photo-coupler isolation, pulse input terminal, COM terminal)
Parallel output	9 outputs (Photo-coupler isolation)
Pulse signal input	Maximum frequency: 60 kpps (Open collector), 200 kpps (Differential)
Puise signal input	Input method: 1 pulse mode (Pulse input in direction), 2 pulse mode (Pulse input in differing directions)
Compatible encoder	Incremental A/B phase (Encoder resolution: 800 pulse/rotation)
Serial communication	RS485 (Modbus protocol compliant)
Memory	EEPROM
LED indicator	LED (Green/Red) one of each
Lock control	Forced-lock release terminal Note 3)
Cable length [m]	I/O cable: 1.5 or less (Open collector), 5 or less (Differential)
	Actuator cable: 20 or less
Cooling system	Natural air cooling
Operating temperature range [°C]	0 to 40 (No freezing)
Operating humidity range [%RH]	90 or less (No condensation)
Storage temperature range [°C]	-10 to 60 (No freezing)
Storage humidity range [%RH]	90 or less (No condensation)
Insulation resistance [M $\Omega$ ]	Between the housing and SG terminal: 50 (500 VDC)
Weight [g]	120 (Screw mounting), 140 (DIN rail mounting)

Note 1) Do not use the power supply of "inrush current prevention type" for the driver power supply. When conformity to UL is required, the electric actuator and driver should be used with a UL1310 Class 2 power supply.

Note 2) The power consumption changes depending on the actuator model. Refer to the specifications of actuator for more details.

Note 3) Applicable to non-magnetizing lock.

Step Motor (Servo/24 VDC)

LER

LECP6

LEC-G

LECP1

\_ECPA

## Series LECPA

#### How to Mount

![](_page_48_Figure_2.jpeg)

Note) The space between the drivers should be 10 mm or more.

#### DIN rail AXT100-DR-⊡

∗ For □, enter a number from the "No." line in the table below. Refer to the dimensions on page 36 for the mounting dimensions.

	L L		
	12.5	5.25	7.5
	(Pitch)		*  * <sup></sup>
_	a a a a a a a a a a a a a a a a a a a	+	22
	$\phi \phi $		୍ ଅ
		5.5	
		1.25	
	_	1.25	

L Dimer	nsion	[mm]													→ 1.2	25				
No.	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L	23	35.5	48	60.5	73	85.5	98	110.5	123	135.5	148	160.5	173	185.5	198	210.5	223	235.5	248	260.5
No.	21	22	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40
L	273	285.5	298	310.5	323	335.5	348	360.5	373	385.5	398	410.5	423	435.5	448	460.5	473	485.5	498	510.5

#### DIN rail mounting adapter LEC-2-D0 (with 2 mounting screws)

This should be used when the DIN rail mounting adapter is mounted onto the screw mounting type driver afterwards.

## Step Motor Driver Series LECPA

#### Dimensions

![](_page_49_Figure_3.jpeg)

**多SMC** 

A LECP1

Model Selection

LER

LECP6

LEC-G

LECPA

Specific Product Precautions

## Series LECPA

#### Wiring Example 2

Parallel I/O Connector: CN5 \* When you connect a PLC, etc., to the CN5 parallel I/O connector, please use the I/O cable (LEC-CL5-□). The wiring should be changed depending on the type of the parallel I/O (NPN or PNP).

#### 

Power supply CN5 24 VDC ±10% for I/O signal Terminal name Function Pin no. COM+ 24 V 1 ⊣⊢ COM-0 V 2 NP+ Pulse signal 3 NP-Pulse signal 4 Note 1) PP+ Pulse signal 5 PP-Pulse signal 6 SETUP Input 7 RESET 8 Input SVON Input 9 CLR 10 Input ΤL Input 11 TLOUT 12 Load Output WAREA 13 Load Output BUSY Output 14 Load 15 SETON Output Load INP Output 16 Load SVRE Output 17 Load ESTOP Note: Output 18 Load ALARM N 19 Load Output AREA Output 20 Load Round termin FG 0.5-5

Note 1) For pulse signal wiring method, refer to "Pulse Signal Wiring Details". Note 2) Output when the power supply of the driver is ON. (N.C.)

#### Input Signal

Name	Details
COM+	Connects the power supply 24 V for input/output signal
COM-	Connects the power supply 0 V for input/output signal
SETUP	Instruction to return to origin
RESET	Alarm reset
SVON	Servo ON instruction
CLR	Deviation reset
TL	Instruction to pushing operation

#### **Pulse Signal Wiring Details**

#### • Pulse signal output of positioning unit is differential output

![](_page_50_Figure_10.jpeg)

• Pulse signal output of positioning unit is open collector output Pulse signal power supply Positioning unit Inside of the driver NP+ 1 kΩ 🗍 NP ſ Current limit 120 Ω resistor R Note) PP+ 1 kΩ□|**†**≳€ PP C 120 Q Current limit resistor R Note) SMC

![](_page_50_Figure_12.jpeg)

#### **Output Signal**

Name	Details
BUSY	Outputs when the actuator is operating
SETON	Outputs when returning to origin
INP	Outputs when target position is reached
SVRE	Outputs when servo is on
*ESTOP Note 3)	Not output when EMG stop is instructed
*ALARM Note 3)	Not output when alarm is generated
AREA	Outputs within the area output setting range
WAREA	Outputs within W-AREA output setting range
TLOUT	Outputs during pushing operation
Note 3) Signal	of negative-logic circuit ON (N.C.)

Note) Connect the current limit resistor R in series to correspond to the pulse signal voltage.

Pulse signal power supply voltage	Current limit resistor R specifications
24 VDC ±10%	3.3 kΩ ±5% (0.5 W or more)
5 VDC ±5%	390 $\Omega$ ±5% (0.1 W or more)

## Step Motor Driver Series LECPA

# Model Selection

ON

OFF

38

![](_page_51_Figure_8.jpeg)

![](_page_51_Figure_9.jpeg)

\* "\*ALARM" and "\*ESTOP" are expressed as negative-logic circuit.

#### **Positioning Operation**

![](_page_51_Figure_12.jpeg)

![](_page_51_Figure_13.jpeg)

**Pushing Operation** 

Input

ΤL

Note) If pushing operation is stopped when there is no pulse deviation, the moving part of the actuator may pulsate.

![](_page_51_Figure_15.jpeg)

![](_page_51_Figure_16.jpeg)

"\*ALARM" is expressed as negative-logic circuit.

## Series LECPA

#### **Options: Actuator Cable**

![](_page_52_Figure_2.jpeg)

#### **SMC**

## Step Motor Driver Series LECPA

# Model Selection

Step Motor (Servo/24 VDC) LER

LECP6

40

### Options

2

[I/O cable] LEC-C\_L5-1 I/O cable length (L) I/O cable type For LECPA 1 L5 3 5 Pulse input usable only with differential. Only 1.5 m cables usable with open collector. L (12) 20 19 (22)

1.5 m

3 m\*

5 m\*

![](_page_53_Figure_11.jpeg)

Pin	Insulation	Dot	Dot
no.	color	mark	color
12	Light brown		Red
13	Yellow		Black
14	Yellow		Red
15	Light green		Black
16	Light green		Red
17	Gray		Black
18	Gray		Red
19	White		Black
20	White		Red
Round terminal 0.5-5	G	Green	

#### [Noise filter set] Step Motor Driver (Pulse Input Type)

## **LEC-NFA**

100 ±10

Contents of the set: 2 noise filters (Manufactured by WURTH ELEKTRONIK: 74271222)

(25)

(45)

(10)

(40)

Number of cores

AWG size

20

24

![](_page_53_Figure_16.jpeg)

\* Refer to the LECPA series Operation Manual for installation.

# Series LEC Windows®XP, Windows®7 compatible Controller Setting Kit/LEC-W2

![](_page_54_Figure_1.jpeg)

How to Order

![](_page_54_Figure_3.jpeg)

Controller setting kit (Japanese and English are available.)

#### Contents

- **1** Controller setting software (CD-ROM)
- **(2)** Communication cable
- ③ USB cable
   (Cable between the PC and the conversion unit)

#### **Compatible Controllers/Driver**

Step motor controller (Servo/24 VDC)Series LECP6Servo motor controller (24 VDC)Series LECA6Step motor driver (Pulse input type)Series LECPA

#### Hardware Requirements

OS	IBM PC/AT compatible machine running Windows <sup>®</sup> XP (32-bit), Windows <sup>®</sup> 7 (32-bit and 64-bit).
Communication interface	USB 1.1 or USB 2.0 ports
Display	XGA (1024 x 768) or more

\* Windows® and Windows®7 are registered trademarks of Microsoft Corporation in the United States.

\* Refer to SMC website for version update information, http://www.smcworld.com

#### Screen Example

#### Easy mode screen example

![](_page_54_Figure_17.jpeg)

#### Easy operation and simple setting

- Allowing to set and display actuator step data such as position, speed, force, etc.
- Setting of step data and testing of the drive can be performed on the same page.
- Can be used to jog and move at a constant rate.

#### Normal mode screen example

![](_page_54_Picture_23.jpeg)

#### **Detailed setting**

- Step data can be set in detail.
- Signals and terminal status can be monitored.
- Parameters can be set.
- JOG and constant rate movement, return to origin, test operation and testing of forced output can be performed.

## Series LEC **Teaching Box/LEC-T1**

# Model Selection

LECP6

LECP1

LECPA

Specific Product Precautions

![](_page_55_Picture_3.jpeg)

![](_page_55_Figure_4.jpeg)

#### Specifications

Item	Description
Switch	Stop switch, Enable switch (Option)
Cable length [m]	3
Enclosure	IP64 (Except connector)
Operating temperature range [°C]	5 to 50
Operating humidity range [%RH]	90 or less (No condensation)
Weight [g]	350 (Except cable)
[CE-compliant products]	

The EMC compliance of the teaching box was tested with the LECP6 series step motor controller (servo/24 VDC) and an applicable actuator.

[UL-compliant products] When conformity to UL is required, the electric actuator and driver should be used with a UL1310 Class 2 power supply.

#### Easy Mode

Option

Standard functions

 Chinese character display Stop switch is provided.

• Enable switch is provided.

Function	Details
Step data	<ul> <li>Setting of step data</li> </ul>
Jog	<ul><li>Jog operation</li><li>Return to origin</li></ul>
Test	<ul> <li>1 step operation Note 1)</li> <li>Return to origin</li> </ul>
Monitor	<ul> <li>Display of axis and step data no.</li> <li>Display of two items selected from Position, Speed, Force.</li> </ul>
ALM	<ul><li>Active alarm display</li><li>Alarm reset</li></ul>
TB setting	<ul> <li>Reconnection of axis (Ver. 1.**)</li> <li>Displayed language setting (Ver. 2.**)</li> <li>Setting of easy/normal mode</li> <li>Setting step data and selection of items from easy mode monitor</li> </ul>

#### Menu Operations Flowchart

![](_page_55_Figure_12.jpeg)

Note 1) Not compatible with the LECPA.

![](_page_55_Picture_14.jpeg)

## Series LEC

#### Normal Mode

Function	Details
Step data	Step data setting
Parameter	Parameters setting
Test	<ul> <li>Jog operation/Constant rate movement</li> <li>Return to origin</li> <li>Test drive Note 1) (Specify a maximum of 5 step data and operate.)</li> <li>Forced output (Forced signal output, Forced terminal output) Note 2)</li> </ul>
Monitor	<ul> <li>Drive monitor</li> <li>Output signal monitor Note 2)</li> <li>Input signal monitor Note 2)</li> <li>Output terminal monitor</li> <li>Input terminal monitor</li> </ul>
ALM	<ul> <li>Active alarm display (Alarm reset)</li> <li>Alarm log record display</li> </ul>
File	<ul> <li>Data saving Save the step data and parameters of the driver which is being used for communication (it is possible to save four files, with one set of step data and parameters defined as one file).</li> <li>Load to driver Loads the data which is saved in the teaching box to the driver which is being used for communication.</li> <li>Delete the saved data.</li> <li>File protection (Ver. 2.**)</li> </ul>
TB setting	<ul> <li>Display setting (Easy/Normal mode)</li> <li>Language setting (Japanese/English)</li> <li>Backlight setting</li> <li>LCD contrast setting</li> <li>Beep sound setting</li> <li>Max. connection axis</li> <li>Distance unit (mm/inch)</li> </ul>
Reconnect	Reconnection of axis

#### Menu Operations Flowchart

Menu

Step data Parameter

TB setting

Monitor

Test ALM

File

![](_page_56_Figure_4.jpeg)

#### Dimensions

![](_page_56_Figure_6.jpeg)

No.	Description	Function					
1	LCD	A screen of liquid crystal display (with backlight)					
2	Ring	A ring for hanging the teaching box					
3	Stop switch	When switch is pushed in, the switch locks and stops. The lock is released when it is turned to the right.					
4	Stop switch guard	A guard for the stop switch					
5	Enable switch (Option)	Prevents unintentional operation (unexpected operation) of the jog test function. Other functions such as data change are not covered.					
6	Key switch	Switch for each input					
7	Cable	Length: 3 meters					
8	Connector	A connector connected to CN4 of the driver					

**SMC** 

![](_page_57_Picture_0.jpeg)

These safety instructions are intended to prevent hazardous situations and/or equipment damage. These instructions indicate the level of potential hazard with the labels of "**Caution**," "**Warning**" or "**Danger**." They are all important notes for safety and must be followed in addition to International Standards (ISO/IEC)<sup>\*1</sup>, and other safety regulations.

![](_page_57_Picture_2.jpeg)

#### **Revision** history

Edition E	<ul> <li>* Addition of programless controller, LECP1 series</li> <li>* Number of pages from 32 to 44</li> </ul>	PY
Edition (	<ul> <li>* Addition of step motor driver, LECPA series</li> <li>* Addition of gateway unit, LEC-G series</li> </ul>	
	* Number of pages from 44 to 60	RQ

A Safety Instructions Be sure to read "Handling Precautions for SMC Products" (M-E03-3) before using.

## SMC Corporation

Akihabara UDX 15F, 4-14-1, Sotokanda, Chiyoda-ku, Tokyo 101-0021, JAPAN Phone: 03-5207-8249 Fax: 03-5298-5362 http://www.smcworld.com © 2013 SMC Corporation All Rights Reserved

## INFORMATION

# CC-Link Direct Input Type Step Motor Controller

## CC-Link Ver. 1.10 compliant

### 3 types of operation mode available.

#### Single numerical data instructions (Occupied number of stations: 1)

[Max. number of connectable controllers: 42 units] Can be operated by instructing the Movement MOD (movement mode) and changing another item in the preset step data.

#### Half numerical data instructions (Occupied number of stations: 2)

[Max. number of connectable controllers: 32 units] Can be operated by changing up to six items in the preset step data.

#### Full numerical data instructions (Occupied number of stations: 4)

[Max. number of connectable controllers: 16 units] Can be operated by inputting numerical data to all 12 step data items from the PLC.

#### The position and speed can be monitored by the PLC.

## Step data can be edited from the PLC. (Except single numerical data instructions)

![](_page_58_Picture_12.jpeg)

![](_page_58_Picture_13.jpeg)

Mode setting	Single numerical data instructions	Half numerical data instructions	Full numerical data instructions				
Number of numerical data modifiable items	1	6	12				
Occupied number of stations	1	2	4				
Max. number of connectable controllers	42	32	16				
Step no. instructions operation		0					
Numerical data instructions operation	0						
Monitor function of position/speed		0					
Step data editing function	0						

## Series LECPMJ

![](_page_58_Picture_16.jpeg)

## Series LECPMJ

How to Order

![](_page_59_Figure_2.jpeg)

**SMC** 

#### Specifications

		Item	LECPMJ							
Compatible motor			Step motor (Servo/24 VDC)							
Power supply Note 1)			Power voltage: 24 VDC ±10% Maximum current consumption: 3 A (Peak 5 A) <sup>Note 2)</sup> [Including motor drive power, control power, lock release]							
Co	mpatible enc	oder		Inc	crement	al A/B phase (800 pulse	e/rotatior	n)		
ns	Fieldbus					CC-Link Ver. 1.10				
atio	Communica	tion speed [bps]			15	6 k/625 k/2.5 M/5 M/10	М			
fic	Communica	tion method				Broadcast polling				
) Seci	Station type					Remote device station				
ication sp	I/O occupat	ion area	1 station ( Input 32 points/4 words (Output 32 points/4 words)		(6	2 stations ( Input 64 points/8 words ( Output 64 points/8 words)		4 stations ( Input 128 points/16 words (Output 128 points/16 words)		
In	Applicable c	ommunication cable	CC-Link dedicated cable							
m	Maximum	Communication speed [bps]	156 k	625 k		2.5 M		5 M	10 M	
ပိ	cable length	Total cable length [m]	1200	900	400			160	100	
Serial communication			RS485 (Modbus protocol)							
Ме	mory		EEPROM							
LE	D indicator		PWR, ALM, L ERR, L RUN							
Lo	ck control		Forced-lock release terminal Note 3)							
Ca	ole length [m	]	Actuator cable: 20 or less							
Cooling system			Natural air cooling							
Operating temperature range [°C]			0 to 40 (No freezing)							
Operating humidity range [%RH]			90 or less (No condensation)							
Storage temperature range [°C]			-10 to 60 (No freezing)							
Storage humidity range [%RH]			90 (No condensation)							
Insulation resistance [M $\Omega$ ]			Between the housing and FG terminal 50 (500 VDC)							
We	ight [g]		170 (Screw mounting), 190 (DIN rail mounting)							

Note 1) Do not use the power supply of "inrush current prevention type" for the controller power supply. When conformity to UL is required, the electric actuator and controller should be used with a UL1310 Class 2 power supply.

Note 2) The power consumption changes depending on the actuator model. Refer to the specifications of actuator for more details. Note 3) Applicable to non-magnetizing lock.

#### Function that can be executed in each mode

Mode setting [Occupied number of stations] Note 4)	Single numerical data instructions [1]	Half numerical data instructions [2]	Full numerical data instructions [4]					
Step no. instructions operation	0							
Numerical data instructions operation	0							
Number of numerical data modifiable items	1	12						
Monitor function of position/speed								
Step data editing function	O Note 5)							
Max. number of connectable controllers Note 6)	42	32	16					

Note 4) The modes can be set by registering the occupied number of stations with basic parameter "Option setting 1" of the controller. Note 5) It is possible to edit it from teaching box/controller setting software for "Single numerical data instructions". It is possible to edit it from teaching box/

controller setting software and PLC (CC-Link) for "Half numerical data instructions" and "Full numerical data instructions".

Note 6) Maximum number of units specified in CC-Link communication specifications.

#### Modifiable step data item in each mode

•: Numerical data modifiable items

	Step data item											
Mode setting	Movement MOD	Speed	Position	Acceleration	Pushing speed	Pushing force	Deceleration	Trigger LV	Moving force	Area 1	Area 2	In position
Single numerical data instructions	•	•				Only one item can be changed from 11 ranging from Speed to In position		from 11 items, position.				
Half numerical data instructions	•	•	•	Only one item car Acceleration/F	be changed from Pushing speed.	•	Only one item car Deceleratio	be changed from n/Trigger LV.				
Full numerical data instructions	•	•	•	•	•	•	•	•	•	•	•	•

Note 7) Step data items, except items that have been changed, reference data registered in the controller. Note 8) Refer to the LECPMJ operation manual for details of the step data items.

![](_page_60_Picture_14.jpeg)

## Series LECPMJ

#### Dimensions

![](_page_61_Figure_2.jpeg)

## SMC Corporation

Akihabara UDX 15F, 4-14-1, Sotokanda, Chiyoda-ku, Tokyo 101-0021, JAPAN Phone: 03-5207-8249 Fax: 03-5298-5362 http://www.smcworld.com © 2013 SMC Corporation All Rights Reserved