

# Series **Durable Pressure Switch**

Designed for Extended Duty, Simple and Reliable

Single Pressure Switches

ø1-1/2 [ø38.1]  $\bigcirc$ ø1-1/2 [ø38.1] ø1.500 Ø [ø38.1] 2-7/16 A. [62] 2-5/16 #8-32 SCREW [58.74] [50.8] TERMINALS A-439 A-440 A-439 A-440

Series A6 Durable Pressure Switches have been specifically designed to stand up to extended duty applications. These switches are constructed with a polyamide film diaphragm and are compatible with a variety of fluids. For ease of installation, the switches come with a 1/4<sup>"</sup> male NPT process connection and can be mounted in any orientation. The Series A6 pressure switches are compact and have great setpoint integrity, and feature simple, easy set-point field adjustment.

**A6** 

	Set Point Range psi (bar)	
Model	NC	NO
A6-153221	0.5 to 1 (0.03 to 0.07)	1.1 to 3.1 (0.08-0.21)
A6-253221	1.1 to 3 (0.08 to 0.21)	2.27 to 6.05 (0.16-0.42)
A6-353221	3.1 to 7 (0.21 to 0.48)	4.22 to 10.75 (0.29 to 0.74)
A6-453221	8 to 13 (0.55 to 0.90)	12.3 to 17.5 (0.85 to 1.21)
A6-553221	14 to 24 (0.97 to 1.66)	18.6 to 31.8 (1.28 to 2.19)
A6-653221	25 to 50 (1.73 to 3.45)	33.1 to 61 (2.28 to 4.21)
A6-753221	51 to 90 (3.52 to 6.21)	65.6 to 112.3 (4.53 to 7.75)
A6-853221	91 to 150 (6.28 to 10.35)	114.7 to 198.3 (7.94 to 13.68)

#### ACCESSORIES

Model	Description	
A-439	Weatherproof IP65 Cover	
A-440	Weatherproof IP65 w/ Fly-wire holes	

## SPECIFICATIONS

Service: Air. motor oils. transmission oils, iet fuels, and similar hydrocarbon media. (Not for water use). Wetted Materials: Base: 304 SS: Diaphragm: Polvamide film. Temperature Limits: -40 to 248°F (-40 to 120°C).

## Pressure Limits:

Operating Pressure: 150 psi (10.3 bar) for 0.5-24 psi set point ranges, 250 psi (17.2 bar) for 25-150 psi set-point ranges; Proof Pressure: 500 psi (34.5 bar): Burst Pressure: 750 psi (51.7 bar) for 0.5-24 psi set point ranges, 1250 psi (86.2 bar) for 25-150 psi set-point ranges.

Enclosure Rating: General purpose or with cover: IP65 - weatherproof.

Repeatability: ±10% of set-point. Set Point Tolerance: ±15% of range. Switch Type: 1 SPST NO. 1 SPST NC. NO and NC switch independent from each other

## Electrical Ratings:

Resistive: 15 A @ 6 VDC. 8 A @ 12 VDC, 4 A @ 24 VDC; Inductive: 1 A @ 120 VAC, 0.5 A @ 240 VAC.

Electrical Connections: #8-32 screw terminals

Process Connection: 1/4" NPT male. Mounting Orientation: Switch can be installed in any position.

Set-point Adjustment: Screw. Weight: 0.13 lb (0.06 kg). Agency Approval: CE.