
Specification



In-Line PC1 and In-Line Sealed to IP66, PC1



- Protection Category PC1
- Fuse Sizes 5 x 20mm,6.3 x 25mm and 6.3 x 32mm
- Screw Terminal (Solder to order)
- 10A, 50V (250V Inaccessible)
- UL Approved (Black versions only)
- Clear or black






- Sealed to IP66
- Protection Category PC1
- Fuse Sizes 5 x 20mm,6.3 x 25mm and 6.3 x 32mm
- Screw Terminal (Solder to order)

FX0180, FX0280, FX0380/Colour | FX0185, FX0285, FX0385/Colour |

- 10A, 50V (250V Inaccessible)
- UL Approved (Black versions only)
- Clear or black



	5 x 20mm FX0380	5 x 20mm FX0385	
	6.3 x 25mm FX0280 6.3 x 32mm FX0180	6.3 x 25mm FX0285 6.3 x 32mm FX0185	
Cable Acceptance:	1 mm ² conductor (max.)	1mm² conductor (max.) 1mm to 2.64mm overall diameter Stepped grommet: Stage 1: 1.00mm to 1.40mm Stage 2: 1.50mm to 1.90mm Stage 3: 2.0mm to 2.64mm	
Terminations:	Screw terminal (solder to order)	Screw Terminal (solder to order)	
	10A, 50V (250V where inaccessible inside equipment)	10A, 50V (250V where inaccessible inside equipment)	
Insulation Resistance:	>10 ⁵ M @ 500V d.c.	>10 ⁵ M @ 500V d.c.	
High Voltage Proof Test:	2kV (50Hz for 1 minute)	2kV (50Hz for 1 minute)	
Contact Resistance:	<10m	<10m	
Operating Temp.: (ambient air temp + fuse temp rise)	-20°C to +90°C	-20°C to +70°C	
Sealing:		Protection Classification IP66 BS60529: 1992	
,	Polybutene UL94HB rated Nylon 6 UL94V-0 rated	Polybutene UL94HB rated Nylon 6 UL94V-0 rated PVC Nitrile	
	Brass, Nickel Plated Stainless Steel	Brass, Nickel Plated Stainless Steel	
Approvals:	(Black versions only)	(Black versions only)	
Colour:	Clear - no suffix, /BK - Black	Clear - no suffix, /BK - Black	
RoHS	Compliant	Compliant	