
## **Industrial / Chemical Processing Blowers**

## **ROTRON®**

## DR 513 & CP 513

### 1.5 HP Regenerative Blower




		Part/ Model Number			
Specification		DR513R72 037217	DR513R58 037209	DR513R86 037773	CP513EZ72LR 038241
	Units				
Motor Enclosure - Shaft Mtl.	-	TEFC - CS	TEFC - CS	TEFC - CS	CHEM TEFC -SS
Horsepower	-	1.5	1.5	1.5	1.5
Voltage	AC	230/460	115/230	575	230/460
Phase - Frequency	-	Three - 60 Hz	Single - 60 Hz	Three - 60 Hz	Three - 60 Hz
Insulation Class	-	F	F	F	F
NEMA Rated Motor Amps	Amps (A)	4.6/2.3	16.8/8.4	1.8	4.6/2.3
Service Factor	- 1	1.15	1.15	1.15	1.15
Max. Blower Amps	Amps (A)	5/2.5	19/9.5	1.85	5/2.5
Locked Rotor Amps	Amps (A)	43/21	120/60	13	43/21
NEMA Starter Size	- 1	00/00	1/0	00	00/00
Shipping Weight	Lbs	76	95	76	76
	Ka	34.5	43.1	34.5	34.5

**Operating Temperaturs** - Maximum operating temperature: Motor winding temperature (winding rise plus ambient) should not exceed 140°C for Class F rated motors or 120°C for Class B rated motors. Blower outlet air temperature should not exceed 140°C (air temperature rise plus inlet temperature). Performance curve maximum pressure and suction points are based on a 40°C inlet and ambient temperature. Consult factory for inlet or ambient temperatures above 40°C.

**Maximum Blower Amps** - Corresponds to the performance point at which the motor or blower temperature rise with a 40°C inlet and/or ambient temperature reaches the maximum operating temperature.

This document is for informational purposes only and should not be considered as a binding description of the products or their performance in all applications. The performance data on this page depicts typical performance under controlled laboratory conditions. AMETEK is not responsible for blowers driven beyond factory specified speed, temperature, pressure, flow or without proper alignment. Actual performance will vary depending on the operating environment and application. AMETEK products are not designed for and should not be used in medical life support applications. AMETEK reserves the right to revise its products without notification. The above characteristics represent standard products. For product designed to meet specific applications, contact AMETEK Technical & Industrial Products Sales department.



## **Industrial / Chemical Processing Blowers**

### DR 513 & CP 513

1.5 HP Regenerative Blower

# **ROTRON®**

### **FEATURES**

- · Manufactured in the USA ISO 9001 and NAFTA compliant
- CE compliant Declaration of Conformity on file
- Maximum flow: 78 SCFM
- Maximum pressure: 88 IWG
- Maximum vacuum: 80 IWG
- Standard motor: 1.5 HP, TEFC
- Cast aluminum blower housing, impeller & cover; cast iron flanges
- UL & CSA approved motor with permanently sealed ball bearings
- · Inlet & outlet internal muffling
- Quiet operation within OSHA standards

## **MOTOR OPTIONS**

- International voltage & frequency (Hz)
- · Chemical duty, high efficiency, inverter duty or industry-specific designs
- · Various horsepowers for application-specific needs


## **BLOWER OPTIONS**

- Corrosion resistant surface treatments & sealing options
- · Remote drive (motorless) models
- Slip-on or face flanges for application-specific needs

### **ACCESSORIES**

- Flowmeters reading in SCFM
- Filters & moisture separators
- Pressure gauges, vacuum gauges, & relief valves
- Switches air flow, pressure, vacuum, or temperature
- External mufflers for additional silencing
- Air knives (used on blow-off applications)
- Variable frequency drive package





This document is for informational purposes only and should not be considered as a binding description of the products or their performance in all applications. The performance data on this page depicts typical performance under controlled laboratory conditions. AMETEK is not responsible for blowers driven beyond factory specified speed, temperature, pressure, flow or without proper alignment. Actual performance will vary depending on the operating environment and application. AMETEK products are not designed for and should not be used in medical life support applications. AMETEK reserves the right to revise its products without notification. The above characteristics represent standard products. For product designed to meet specific applications, contact AMETEK Technical & Industrial Products Sales department.



AMETEK DYNAMIC FLUID SOLUTIONS

75 North Street, Saugerties, NY 12477